



Certificate No. 02-003899/025743

TYPE APPROVAL CERTIFICATE

This is to certify that this product complies with the Rules for the classification of ships, Part 1 - General requirements, Chapter 3 - Type approval of products.

TYPE AND DESCRIPTION OF PRODUCT:

VICTAULIC GROOVED PIPE COUPLINGS

Type: Style 07 Zero-flex rigid coupling, for use on steel pipes	DN 50 – DN 300 / (2" – 12") (DN 50 – DN 250 – 34.5 bar) (DN 300 – 27 bar)
Style 07 Zero-flex rigid coupling, for use on Cu-Ni pipes	DN 25 – DN 150 / (1" – 6") 15.5 bar
Style 77 standard flexible coupling, for use on steel pipes	DN 50 – DN 300 / (2" – 12") 34.5 bar
Style 77 standard flexible coupling, for use on Cu-Ni pipes	DN 25 – DN 150 / (1" – 6") 15.5 bar

MANUFACTURER:

VICTAULIC COMPANY

4901 Kesslersville Road
Easton, Pennsylvania, 18040-6714

USA

THE PRODUCT MEETS FOLLOWING RULES/REGULATIONS:


Rules for the classification of ships, Part 8, Piping
IACS UR P2 (Rev. 10 Jan 2021), P.2.7.4, application acc. to Table 7

FURTHER DETAILS OF THE PRODUCT AND CONDITIONS FOR CERTIFICATION ARE GIVEN OVERLEAF.

APPROVAL IS VALID UNTIL: **2027-04-10**

Place and date: Split, 2023-02-10




for Marinko Popović, dipl.ing.

NOTE: This certificate is not valid for equipment, the design or manufacture of which has been varied or modified from the specimen tested. The manufacturer should notify Croatian Register of Shipping of any modification or changes to the product in order to obtain a valid certificate.

DETAILED PRODUCT DESCRIPTION:

Grooved couplings for rigid and flexible coupling of pipes. Two piece housing construction.

APPLICATION / LIMITATIONS:

Ship's piping

TYPE APPROVAL DOCUMENTATION:

Assembly: VICTAULIC GENERAL CATALOG G – 103, Rev. E 03/2020

Drawing No.: Style 07- Request Publication 06.02 Rev. Q 07/2022
Style 77- Request Publication 06.04 Rev. W 07/2022

Test reports:	Victaulic test	1	Style 07	50 mm	28.09.2006.
	Victaulic test	2	Style 77	50 mm	28.09.2006.
	Victaulic test	7	Style 07	150 mm	29.09.2006.
	Victaulic test	8	Style 77	150 mm	29.09.2006.
	Victaulic test	15	Style 07	300 mm	02.10.2006.
	Victaulic test	16	Style 77	300 mm	02.10.2006.

MARKING OF PRODUCT:

- type
- nominal size
- nominal pressure
- material
- manufacturer's name
- year of manufacture

CONDITIONS FOR CERTIFICATION:

–

PRODUCTION PLACE:

Manufacturing Locations:

Victaulic – Alburdis Facility
8023 Quarry Road
Alburdis, PA 18011 USA

Victaulic Polska Sp. z.o.o.
Ul. Niepodleglosci 8
66-530 Drezdenko, Poland

Dalian Bingshan Metal Technology Co. Ltd.
No. 9 Northeast 7th Street
Dalian Economy & Technology Developing Zone
Dalian 116600 China