


Installation Instructions

VE226 Power Drive Kit

**Kit for connecting a
VE226 Roll Grooving Tool
to a Ridgid* 700 Power Drive**



⚠ WARNING



- Read all instructions and warnings before installing this kit or operating any tools.
- Wear safety glasses, hardhat, foot protection and hearing protection.
- Save these instructions for future reference.

If you need additional copies of any literature, or if you have questions about the safe operation of this tool, contact Victaulic Tool Company, 1326 Tatamy Road, Easton, PA 18044-0031, Phone: 1-800-PICK VIC, e-mail: pickvic@victaulic.com.

*Ridgid is a registered trademark of the Ridge Tool Company



HAZARD IDENTIFICATION

Definitions for identifying the various hazard levels are provided below.



This safety alert symbol indicates important safety messages. When you see this symbol, be alert to the possibility of personal injury. Carefully read and fully understand the message that follows.


⚠ DANGER

The use of the word "DANGER" identifies an immediate hazard with a likelihood of death or serious personal injury if instructions, including recommended precautions, are not followed.

⚠ WARNING

The use of the word "WARNING" identifies the presence of hazards or unsafe practices that could result in death or serious personal injury if instructions, including recommended precautions, are not followed.

CONTENTS OF KIT



Item No.	Description	Qty.
1	Power Drive/Tool Stand	1
2	Foot Switch for Power Drive	1
3	Adapter Plate	1
4	Pins	2
5	Bolts with Flat Washers and Wing Nuts	4
6	Power Drive Trigger Lock	1
7	Power Drive Adapter	1

IMPORTANT INFORMATION


These instructions are a supplement to highlight the necessary steps that must be performed to adapt a VE226 Roll Grooving Tool for use with a Ridgid 700 Power Drive. Refer to the VE226 Operating Instructions (supplied with this kit) and the Ridgid 700 Operator's Manual for complete safety information, tool setup, grooving, troubleshooting, maintenance information, etc.

1. Select location for tool. The choice of tool location and position should take into account the following factors:
 - a.) Pipe handling support requirements
 - b.) Power supply requirements
 - c.) Pipe support and tool anchoring requirements
2. Place the power drive/tool stand on level ground. Secure the stand to a platform or the floor.


KIT INSTALLATION




1. Install adapter plate onto power drive/tool stand, as shown above.



2. Install bolts with flat washers through the four locations on the adapter plate and into the power drive/tool stand.



3. Install wing nuts onto four bolts, as shown above, and tighten.



4. Install VE226 tool onto arms of power drive/tool stand.



5. Install a pin into each hole in the arms of the power drive/tool stand, as shown above. Close the pins.

⚠ DANGER




- To prevent electric shock, make sure the power drive/foot switch is unplugged from the electrical source before attempting to remove or install any components.
- DO NOT plug power drive/foot switch into power source until instructed.

Failure to follow these instructions could result in death or serious personal injury.


⚠ WARNING

- DO NOT operate power drive without a safety foot switch. A foot switch is required to operate the tool safely.

Failure to follow this instruction could result in serious personal injury.



6. Remove existing drive adapter or threading die from power drive.



9. Locate the tapped hole in the body of the power drive.



7. Locate the drive tangs on the Ridgid 700 Power Drive.




10. Install power drive adapter into power drive by aligning the drive tangs (shown in Step 7) with the recesses in the adapter (shown in Step 8). Make sure the shaft of the adapter (shown in Step 8) faces the same side of the power drive as the tapped hole (shown in Step 9).




8. Locate the recesses in the power drive adapter.




10a. Make sure the power drive adapter engages completely into the power drive, as shown above.



11. Install power drive onto VE226 tool with the set screws of the power drive adapter shaft aligned with the flats on the tool drive shaft, as shown above. If necessary, rotate the VE226 tool drive shaft by hand for proper alignment.




14. Before tightening the three set screws, double-check that the flats on the VE226 tool drive shaft are aligned with the set screws of the power drive adapter shaft. Tighten the three set screws on the power drive adapter shaft with the hex key wrench included with the VE226 tool.



12. Align tapped hole in power drive body with the hole in the adapter plate, as shown above.



15. Tighten bolt that you installed in step 13.




13. Loosely install bolt (attached to adapter plate) through adapter plate's hole and into tapped hole in power drive body, as shown above.


⚠ WARNING

- **Make sure the power drive/foot switch is unplugged before installing the power drive trigger lock.**

Failure to follow these instructions could result in serious personal injury.



16. Install power drive trigger lock onto power drive.
Tighten two thumbscrews on underside of trigger lock.



16a. It is important that the trigger lock's tab pushes down on the topside trigger to produce correct rotation of grooving rolls.

WARNING

- **DO NOT** operate power drive without a safety foot switch. A foot switch is required to operate the tool safely.

Failure to follow this instruction could result in serious personal injury.



17. Plug power drive into footswitch, as shown above. Plug foot switch cord into a grounded electrical outlet, according to requirements in the VE226 Operating Instructions and the Ridgid 700 Operator's Manual.

18. Follow rest of steps in the VE226 Operating Instructions, starting with section B, "Tubing/Pipe Preparation" on page 6.



www.victaulic.com

Victaulic Tool Company

Tool Shipments:

1326 Tatamy Road, Easton, PA 18045-7400

Sales & Lease Payments:

P.O. Box 8588-244, Phila., PA 19171-0244

CUSTOMER CARE CENTER

Phone: 1-800-PICK-VIC (1-800-742-5842)

e-mail: pickvic@victaulic.com

FAX: 610/923-3090

WORLD HEADQUARTERS

P.O. Box 31 • Easton, PA 18044-0031

4901 Kesslersville Road • Easton, PA, USA 18040

Phone: 610/559-3300 • FAX: 610/250-8817

VICTAULIC COMPANY OF AMERICA

P.O. Box 31 • Easton, PA 18044-0031

Phone: 610/559-3300 • Fax: 610/250-8817

Fire Protection Division Customer Care Centers

■ **SOUTHEAST FIRE PROTECTION**

Phone: 877/773-8322 • Fax: 877/776-9769

■ **NORTHEAST FIRE PROTECTION**

Phone: 888/265-0805 • Fax: 888/265-0918

■ **CENTRAL FIRE PROTECTION**

Phone: 888/448-3534 • Fax: 888/448-3595

■ **WESTERN FIRE PROTECTION**

Phone: 877/487-7231 • Fax: 877/487-7232

Victaulic Tool Company

P.O. Box 31 • Easton, PA 18044-0031

Phone: 610/559-3300 • Fax: 610/923-3090

Victaulic Municipal Division

1818 Vultee Street • Allentown, PA 18103

Phone: 610/559-3488 • Fax: 610/923-3170

Victaulic Technical Services Division

1818 Vultee Street • Allentown, PA 18103

Phone: 610/559-3488 • Fax: 610/923-3170

United States Distribution Centers

■ **NORTHEAST**

7 Forge Parkway • Franklin, MA 02038

Cust.Care: 800/742-5842 • Cust. Fax: 888/265-0926

■ **NEW YORK METRO**

4901 Kesslersville Road • Easton, PA 18040

Cust.Care: 800/742-5842 • Cust. Fax: 800/437-6573

■ **SOUTHEAST**

650 Coastline Drive • Yulee, FL 32097

Cust.Care: 800/742-5842 • Cust. Fax: 888/201-3468

■ **ATLANTIC**

166 Thorn Hill Road • Warrendale, PA 15086

Cust.Care: 800/742-5842 • Cust. Fax: 888/201-3517

■ **MIDWEST**

730 Thomas Drive • Bensenville, IL 60106

Cust.Care: 800/742-5842 • Cust. Fax: 888/265-2018

■ **GREAT LAKES**

23107 Commerce Drive • Farmington Hills, MI 48335

Cust.Care: 800/742-5842 • Cust. Fax: 800/564-0119

■ **CENTRAL STATES**

5900 Deramus Avenue • Kansas City, MO 64120

Cust.Care: 800/742-5842 • Cust. Fax: 888/448-3540

■ **MID-CONTINENT**

7177 Railspur Street • Houston, TX 77078

Cust.Care: 800/742-5842 • Cust. Fax: 888/448-3537

■ **PERMIAN BASIN**

2628 Remington Road • Odessa, TX 79763

Local Tel.: 915/332-1489 • Local Fax: 915/332-4924

■ **ROCKY MOUNTAIN**

5045 Paris Street • Denver, CO 80239

Cust.Care: 800/742-5842 • Cust. Fax: 888/448-3528

■ **PACIFIC - NORTH**

22633 83rd Ave. So. • Kent, WA 98032

Cust.Care: 800/742-5842 • Cust. Fax: 888/448-3530

■ **MID-ATLANTIC**

4901 Kesslersville Road • Easton, PA 18040

Cust.Care: 800/742-5842 • Cust. Fax: 800/696-6447

■ **PACIFIC - SOUTH**

20934 So. Santa Fe Ave. • Long Beach, CA 90810

Cust.Care: 800/742-5842 • Cust. Fax: 800/448-3542

VICTAULIC COMPANY OF CANADA

65 Worcester Road • Rexdale, Ontario • Canada M9W 5N7

Phone: 416/675-5575 • FAX: 416/675-5565 • e-mail: viccanda@victaulic.com

Canadian Sales Offices and Service Centers

■ **EASTERN**

975 rue Selkirk • Pointe Claire, PQ H9R 4S4

Phone: 514/426-3500 • FAX: 514/426-2818

■ **ONTARIO - NORTH**

1070 Elisabella Street • Sudbury, ON P3A 5K2

Phone: 705/560-9595 • FAX: 705/560-9490

■ **PACIFIC**

Unit 5, 7560 Vantage Way • Delta, BC V4G 1H1

Phone: 604/940-3301 • FAX: 604/940-3360

■ **ONTARIO - SOUTH**

65 Worcester Road • Rexdale, ON M9W 5N7

Phone: 416/675-5575 • FAX: 416/675-5729

■ **WESTERN**

15353 114th Avenue • Edmonton, AB T5M 3S9

Phone: 780/452-0680 • FAX: 780/452-2430