

Price List Addendum

EFFECTIVE January 5, 2026



PL2025-GEN-LA-ADD12

KOIL-KIT™ Coil Pack

Series UH1 Flexible Pipe
with PT Port and Air Vent

Refer to publication 106.30



SERIES UH1 FLEXIBLE PIPE WITH PT PORT AND AIR VENT

Size	Length	Male Thread/ Female NPT Swivel		Male Thread/ Male NPT Union		Male Thread/ Sweat		Male Thread/ Copper Press	
		Part Code	Price Each	Part Code	Price Each	Part Code	Price	Part Code	Price Each
1/2	12	F004UH1AMF	\$125.00	F004UH1AMM	\$125.00	F004UH1AMS	\$125.00	F004UH1AMP	\$125.00
	18	F004UH1AMF	128.00	F004UH1DMM	128.00	F004UH1DMS	128.00	F004UH1DMP	128.00
	24	F004UH1BMF	130.50	F004UH1BMM	130.50	F004UH1BMS	130.50	F004UH1BMP	130.50
	36	F004UH1CMF	135.00	F004UH1CMM	135.00	F004UH1CMS	135.00	F004UH1CMP	135.00
3/4	12	F006UH1AMF	126.50	F006UH1AMM	126.50	F006UH1AMS	126.50	F006UH1AMP	126.50
	18	F006UH1DMF	130.50	F006UH1DMM	130.50	F006UH1DMS	130.50	F006UH1DMP	130.50
	24	F006UH1BMF	134.00	F006UH1BMM	134.00	F006UH1BMS	134.00	F006UH1BMP	134.00
	36	F006UH1CMF	140.50	F006UH1CMM	140.50	F006UH1CMS	140.50	F006UH1CMP	140.50
1	12	F010UH1AMF	132.50	F010UH1AMM	132.50	F010UH1AMS	132.50	F010UH1AMP	132.50
	18	F010UH1DMF	137.50	F010UH1DMM	137.50	F010UH1DMS	137.50	F010UH1DMP	137.50
	24	F010UH1BMF	142.00	F010UH1BMM	142.00	F010UH1BMS	142.00	F010UH1BMP	142.00
	36	F010UH1CMF	151.50	F010UH1CMM	151.50	F010UH1CMS	151.50	F010UH1CMP	151.50
1 1/4	12	F012UH1AMF	328.00	F012UH1AMM	328.00	F012UH1AMS	328.00	F012UH1AMP	328.00
	18	F012UH1DMF	336.50	F012UH1DMM	336.50	F012UH1DMS	336.50	F012UH1DMP	336.50
	24	F012UH1BMF	344.50	F012UH1BMM	344.50	F012UH1BMS	344.50	F012UH1BMP	344.50
	36	F012UH1CMF	362.50	F012UH1CMM	362.50	F012UH1CMS	362.50	F012UH1CMP	362.50
1 1/2	12	F014UH1AMF	338.00	F014UH1AMM	338.00	F014UH1AMS	338.00	F014UH1AMP	338.00
	18	F014UH1DMF	348.00	F014UH1DMM	348.00	F014UH1DMS	348.00	F014UH1DMP	348.00
	24	F014UH1BMF	359.00	F014UH1BMM	359.00	F014UH1BMS	359.00	F014UH1BMP	359.00
	36	F014UH1CMF	380.50	F014UH1CMM	380.50	F014UH1CMS	380.50	F014UH1CMP	380.50
2	12	F020UH1AMF	441.50	F020UH1AMM	441.50	F020UH1AMS	441.50	F020UH1AMP	441.50
	18	F020UH1DMF	455.50	F020UH1DMM	455.50	F020UH1DMS	455.50	F020UH1DMP	455.50
	24	F020UH1BMF	471.00	F020UH1BMM	471.00	F020UH1BMS	471.00	F020UH1BMP	471.00
	36	F020UH1CMF	498.00	F020UH1CMM	498.00	F020UH1CMS	498.00	F020UH1CMP	498.00

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

Contact Victaulic for other available configurations.



Hydronic Balancing Products

Series UH1 Flexible Pipe

Refer to publication 106.30

SERIES UH1 FLEXIBLE PIPE

Size	Length	Male Thread/ Female NPT Swivel		Male Thread/ Male NPT Union		Male Thread/ Sweat		Male Thread/ Copper Press	
inches		Part Code	Price Each	Part Code	Price Each	Part Code	Price	Part Code	Price Each
1/2	12	F004UH11MF	\$85.00	F004UH11MM	\$85.00	F004UH11MS	\$85.00	F004UH11MP	\$85.00
	18	F004UH14MF	88.00	F004UH14MM	88.00	F004UH14MS	88.00	F004UH14MP	88.00
	24	F004UH12MF	90.50	F004UH12MM	90.50	F004UH12MS	90.50	F004UH12MP	90.50
	36	F004UH13MF	95.00	F004UH13MM	95.00	F004UH13MS	95.00	F004UH13MP	95.00
3/4	12	F006UH11MF	86.50	F006UH11MM	86.50	F006UH11MS	86.50	F006UH11MP	86.50
	18	F006UH14MF	90.00	F006UH14MM	90.00	F006UH14MS	90.00	F006UH14MP	90.00
	24	F006UH12MF	93.50	F006UH12MM	93.50	F006UH12MS	93.50	F006UH12MP	93.50
	36	F006UH13MF	100.50	F006UH13MM	100.50	F006UH12MS	100.50	F006UH13MP	100.50
1	12	F010UH11MF	90.50	F010UH11MM	90.50	F010UH11MS	90.50	F010UH11MP	90.50
	18	F010UH14MF	95.00	F010UH14MM	95.00	F010UH14MS	95.00	F010UH14MP	95.00
	24	F010UH12MF	99.50	F010UH12MM	99.50	F010UH12MS	99.50	F010UH12MP	99.50
	36	F010UH13MF	109.00	F010UH13MM	109.00	F010UH13MS	109.00	F010UH13MP	109.00
1 1/4	12	F012UH11MF	280.00	F012UH11MM	280.00	F012UH11MS	280.00	F012UH11MP	280.00
	18	F012UH14MF	288.00	F012UH14MM	288.00	F012UH14MS	288.00	F012UH14MP	288.00
	24	F012UH12MF	296.50	F012UH12MM	296.50	F012UH12MS	296.50	F012UH12MP	296.50
	36	F012UH13MF	314.50	F012UH13MM	314.50	F012UH13MS	314.50	F012UH13MP	314.50
1 1/2	12	F014UH11MF	282.50	F014UH11MM	282.50	F014UH11MS	282.50	F014UH11MP	282.50
	18	F014UH14MF	293.00	F014UH14MM	293.00	F014UH14MS	293.00	F014UH14MP	293.00
	24	F014UH12MF	304.00	F014UH12MM	304.00	F014UH12MS	304.00	F014UH12MP	304.00
	36	F014UH13MF	325.50	F014UH13MM	325.50	F014UH13MS	325.50	F014UH13MP	325.50
2	12	F020UH11MF	376.00	F020UH11MM	376.00	F020UH11MS	376.00	F020UH11MP	376.00
	18	F020UH14MF	390.00	F020UH14MM	390.00	F020UH14MS	390.00	F020UH14MP	390.00
	24	F020UH12MF	406.00	F020UH12MM	406.00	F020UH12MS	406.00	F020UH12MP	406.00
	36	F020UH13MF	432.50	F020UH13MM	432.50	F020UH13MS	432.50	F020UH13MP	432.50

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

Contact Victaulic for other available configurations.

TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com