

Price List Addendum

EFFECTIVE May 12, 2025

Fire Protection Valves and Devices

Universal Manifold Check Assembly

SERIES UMC

with Auto Test Switch
Refer to publication 30.72.



SERIES UMC – UNIVERSAL MANIFOLD CHECK ASSEMBLY WITH AUTO TEST SWITCH

| UMC Body Size | | | |
|------------------|---|------------|------------|
| Nominal inches | Description | Part Code | Price Each |
| 1¼ | GxG UMC Right Handed with Control Valve | S012UMCRVA | \$4480.50 |
| | GxG UMC Right Handed with Hose | S012UMCR0A | 4213.50 |
| | GxG UMC Left Handed with Control Valve | S012UMCLVA | 4480.50 |
| | GxG UMC Left Handed with Hose | S012UMCL0A | 4213.50 |
| 1½ | GxG UMC Right Handed with Control Valve | S014UMCRVA | 4590.50 |
| | GxG UMC Right Handed with Hose | S014UMCR0A | 4280.00 |
| | GxG UMC Left Handed with Control Valve | S014UMCLVA | 4590.50 |
| | GxG UMC Left Handed with Hose | S014UMCL0A | 4280.00 |
| 2 | GxG UMC Right Handed with Control Valve | S020UMCRVA | 4373.50 |
| | GxG UMC Right Handed with Hose | S020UMCR0A | 4018.50 |
| | GxG UMC Left Handed with Control Valve | S020UMCLVA | 4373.50 |
| | GxG UMC Left Handed with Hose | S020UMCL0A | 4018.50 |
| 2½ | GxG UMC Right Handed with Control Valve | S024UMCRVA | 4495.00 |
| | GxG UMC Right Handed with Hose | S024UMCR0A | 4144.00 |
| | GxG UMC Left Handed with Control Valve | S024UMCLVA | 4495.00 |
| | GxG UMC Left Handed with Hose | S024UMCL0A | 4144.00 |
| 3 | GxG UMC Right Handed with Control Valve | S030UMCRVA | 4475.00 |
| | GxG UMC Right Handed with Hose | S030UMCR0A | 4150.00 |
| | GxG UMC Left Handed with Control Valve | S030UMCLVA | 4475.00 |
| | GxG UMC Left Handed with Hose | S030UMCL0A | 4150.00 |
| 4 | GxG UMC Right Handed with Control Valve | S040UMCRVA | 5163.00 |
| | GxG UMC Right Handed with Hose | S040UMCR0A | 4853.00 |
| | GxG UMC Left Handed with Control Valve | S040UMCLVA | 5163.00 |
| | GxG UMC Left Handed with Hose | S040UMCL0A | 4853.00 |
| 6 | GxG UMC Right Handed with Control Valve | S060UMCRVA | 5733.00 |
| | GxG UMC Right Handed with Hose | S060UMCR0A | 5245.00 |
| | GxG UMC Left Handed with Control Valve | S060UMCLVA | 5733.00 |
| | GxG UMC Left Handed with Hose | S060UMCL0A | 5245.00 |
| 8 | GxG UMC Right Handed with Control Valve | S080UMCRVA | 7596.00 |
| | GxG UMC Right Handed with Hose | S080UMCR0A | 6518.00 |

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

Universal Manifold Assembly

SERIES UM

with Auto Test Switch

Refer to publication 30.71.



SERIES UM – UNIVERSAL MANIFOLD ASSEMBLY WITH AUTO TEST SWITCH

| UM Body Size | | | |
|-----------------|-------------------------------------|------------|------------|
| Nominal inches | Description | Part Code | Price Each |
| 1¼ | GxG UM with Hose | S0120UM00A | \$3733.00 |
| | GxG UM with Control Valve and Hose | S0120UMV0A | 4191.00 |
| 1½ | GxG UM with Hose | S0140UM00A | 3739.00 |
| | GxG UM with Control Valve and Hose | S0140UMV0A | 4291.00 |
| 2 | GxG UM with Hose | S0200UM00A | 3781.00 |
| | GxG UM with Control Valve and Hose | S0200UMV0A | 4231.00 |
| 2½ | GxG UM with Hose | S0240UM00A | 3918.50 |
| | GxG UM with Control Valve and Hose | S0240UMV0A | 4442.50 |
| 3 | GxG UM with Hose | S0300UM00A | 3983.00 |
| | GxG UM with Control Valve and Hose | S0300UMV0A | 4505.50 |
| 4 | GxG UM with Hose | S0400UM00A | 4300.50 |
| | GxG UM with Control Valve with Hose | S0400UMV0A | 4878.00 |
| 6 | GxG UM with Hose | S0600UM00A | 4405.00 |
| | GxG UM with Control Valve with Hose | S0600UMV0A | 4937.50 |
| 8 | GxG UM with Hose | S0800UM00A | 5106.50 |
| | GxG UM with Control Valve with Hose | S0800UMV0A | 6191.50 |

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

Fire Protection Valves and Devices

UM/UMC REPLACEMENT VSR AUTO TEST FLOW SWITCHES

| Body Size | | | |
|----------------|---|------------|------------|
| Nominal inches | Description | Part Code | Price Each |
| 2 | VSR-AT Switch with Gasket and Adapter for 2" UM and UMC | S020UMCPTA | 2950.00 |
| 2½ | VSR-AT Flow Switch with Gasket and Adapter for 2½" UM and UMC | S024UMCPTA | 2950.00 |
| 3 | VSR-AT Flow Switch with Gasket and Adapter for 3" UM and UMC | S030UMCPTA | 2950.00 |
| 4 | VSR-AT Flow Switch with Gasket and Adapter for 4" UM and UMC | S040UMCKA4 | 2950.00 |
| 6 | VSR-AT Flow Switch with Gasket and Adapter for 6" UM and UMC | S060UMCKA6 | 2950.00 |
| 8 | VSR-AT Flow Switch with Gasket and Adapter for 8" UM and UMC | S080UMCPTA | 2950.00 |

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. Box 31, Easton, PA 18044-0031 • 4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com