

Price List Addendum

EFFECTIVE July 29, 2022

Strainer Inlet Vibration Isolation Pump Drop

SERIES 382

Refer to publication 102.12



SERIES 382 – STRAINER INLET VIBRATION ISOLATION PUMP DROP

Pipe x Connection inches	Vertical Connection Configuration		Horizontal Connection Configuration		Price Each
	Approx. Wgt Each ‡ lb	Part Code †	Approx. Wgt Each ‡ lb	Part Code †	
3 x 2	68.8	KC43382PE0 *	82.3	KC43382PEL *	\$9895.50
	68.3	KC49382PE0 *	85.0	KC49382PEL *	10049.50
	66.4	KC59382PE0 *	75.4	KC59382PEL *	9363.50
4 x 2½	82.6	KD35382PE9	103.2	KD35382PE2	12775.50
	83.8	KD44382PE9	107.4	KD44382PE2	12839.00
	78.7	KD65382PE9	102.1	KD65382PE2	12171.00
5 x 2½	138.7	KE05382PE9	159.8	KE05382PE2	22566.50
	140.4	KE09382PE9	160.6	KE09382PE2	22526.50
	99.4	KE16382PE9	163.6	KE16382PE2	20743.50
	119.0	KM83382PE9	142.2	KM83382PE4	19653.50
6 x 4	166.4	KE79382PE9	185.6	KE79382PE2	19680.00
	167.8	KE90382PE9	193.3	KE90382PE2	20139.00
	156.1	KE98382PE9	193.3	KE98382PE2	20962.50
8 x 5	270.0	KF42382PE9	357.1	KF42382PE2	36171.50
	271.4	KF47382PE9	357.1	KF47382PE2	29612.50
	255.7	KF57382PE9	363.3	KF57382PE2	30519.00
10 x 6	493.8	KF91382PE9	641.5	KF91382PE2	50668.00
	502.4	KF96382PE9	550.7	KF96382PE2	43583.50
	464.5	KG01382PE9	595.2	KG01382PE2	43774.00
12 x 8	630.5	KG35382PE9	816.8	KG35382PE2	68906.00
	625.2	KG39382PE9	827.8	KG39382PE2	68967.50
	580.5	KG45382PE9	765.0	KG45382PE2	60478.50

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

‡ Estimated weight using Sch. 40 black carbon steel pipe

† The 1¼" – 18 UNEF female thermometer connection fits most commercially available thermometers with the well removed.

NOTE: A ¾" female NPT thermometer connection is also available. Contact Victaulic for more information.

* This size has a ¾" FNPT supplied as a connection to accept a customer-supplied thermometer well or other accessory; this part code represents that offering.

NOTE: A Victaulic Style 107V Rigid Coupling is required for the installation of this product (not supplied). Refer to Section 1 – Couplings and Fittings for coupling pricing.

Equipment Modules

Discharge Outlet Vibration Isolation Pump Drop

SERIES 380

Refer to publication 102.10



SERIES 380 – DISCHARGE OUTLET VIBRATION ISOLATION PUMP DROP

Pipe x Connection		Vertical Connection Configuration		Horizontal Connection Configuration		Price Each
inches		Approx. Wgt Each ‡	Part Code †	Approx. Wgt Each ‡	Part Code †	
		lb		lb		
3	x 2	41.8	KC43380PE0 *	49.4	KC43380PEL *	\$6605.50
	2½	41.8	KC49380PE0 *	49.4	KC49380PEL *	6830.50
	3	39.3	KC59380PE0 *	46.3	KC59380PEL *	6388.50
4	x 2	58.0	KD29380PE9	70.2	KD29380PE2	9148.00
	2½	61.2	KD35380PE9	72.2	KD35380PE2	9363.50
	3	62.2	KD44380PE9	73.2	KD44380PE2	9427.00
	4	57.6	KD65380PE9	67.2	KD65380PE2	9082.00
5	x 2½	86.6	KE05380PE9	103.4	KE05380PE2	13982.00
	3	88.3	KE09380PE9	105.1	KE09380PE2	13760.50
	4	89.2	KE16380PE9	106.0	KE16380PE2	14115.50
	5	81.3	KM83380PE9	95.9	KM83380PE2	13460.00
6	x 2	114.2	KE61380PE9	153.3	KE61380PE2	15116.00
	2½	115.5	KE65380PE9	154.6	KE65380PE2	15337.00
	3	116.2	KE71380PE9	155.3	KE71380PE2	15333.50
	4	117.3	KE79380PE9	136.4	KE79380PE2	15713.50
	5	118.4	KE90380PE9	141.4	KE90380PE2	16173.50
	6	105.9	KE98380PE9	130.7	KE98380PE2	14814.00
8	x 4	189.5	KF38380PE9	229.1	KF38380PE2	23068.50
	5	191.1	KF42380PE9	231.5	KF42380PE2	23251.50
	6	192.7	KF47380PE9	222.9	KF47380PE2	23145.00
	8	177.0	KF57380PE9	212.8	KF57380PE2	21694.00
10	x 5	422.1	KF89380PE9	508.0	KF89380PE2	42532.00
	6	410.4	KF91380PE9	496.3	KF91380PE2	39860.00
	8	419.1	KF96380PE9	467.9	KF96380PE2	37771.00
	10	376.9	KG01380PE9	467.0	KG01380PE2	36787.50
12	x 6	534.2	KG32380PE9	636.4	KG32380PE2	47746.00
	8	542.1	KG35380PE9	644.6	KG35380PE2	46862.50
	10	536.7	KG39380PE9	644.3	KG39380PE2	47805.00
	12	489.2	KG45380PE9	595.3	KG45380PE2	42126.50

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

‡ Estimated weight using Sch. 40 black carbon steel pipe

† The 1¼" – 18 UNEF female thermometer connection fits most commercially available thermometers with the well removed.

NOTE: A ¾" female NPT thermometer connection is also available. Contact Victaulic for more information.

* This size has a ¾" FNPT supplied as a connection to accept a customer-supplied thermometer well or other accessory; this part code represents that offering.

NOTE: A Victaulic Style 107V Rigid Coupling is required for the installation of this product (not supplied). Refer to Section 1 – Couplings and Fittings for coupling pricing.

Equipment Modules

Discharge CBV Outlet Vibration Isolation Pump Drop

SERIES 383

Refer to publication 102.13



SERIES 383 – DISCHARGE CBV OUTLET VIBRATION ISOLATION PUMP DROP

Pipe x Connection		Vertical Connection Configuration		Horizontal Connection Configuration		Price Each
inches		Approx. Wgt Each ¥	Part Code †	Approx. Wgt Each ¥	Part Code †	
		lb		lb		
3	x 2	53.3	KC43383PE0 *	60.9	KC43383PEL *	\$7168.50
	2½	55.2	KC49383PE0 *	62.8	KC49383PEL *	7392.50
	3	50.8	KC59383PE0 *	57.8	KC59383PEL *	6972.00
4	x 2	77.2	KD29383PE9	89.4	KD29383PE2	10303.50
	2½	80.4	KD35383PE9	91.4	KD35383PE2	10520.00
	3	81.4	KD44383PE9	92.4	KD44383PE2	10583.00
	4	76.8	KD65383PE9	81.4	KD65383PE2	10239.00
5	x 2½	115.0	KE05383PE9	131.8	KE05383PE2	16142.00
	3	116.7	KE09383PE9	133.5	KE09383PE2	15920.00
	4	117.6	KE16383PE9	134.5	KE16383PE2	16282.00
	5	109.7	KM83383PE9	124.3	KM83383PE2	15620.00
6	x 2½	191.9	KE65383PE9	217.3	KE65383PE2	19445.50
	3	160.4	KE71383PE9	199.5	KE71383PE2	19441.50
	4	161.5	KE79383PE9	180.6	KE79383PE2	19822.50
	5	162.6	KE90383PE9	185.6	KE90383PE2	20282.00
	6	150.1	KE98383PE9	174.9	KE98383PE2	18922.50
8	x 4	291.2	KF38383PE9	330.8	KF38383PE2	33909.00
	5	292.8	KF42383PE9	333.2	KF42383PE2	34091.50
	6	294.4	KF47383PE9	324.6	KF47383PE2	33986.00
	8	278.7	KF57383PE9	314.5	KF57383PE2	32533.00
10	x 6	530.9	KF91383PE9	616.8	KF91383PE2	53935.00
	8	539.6	KF96383PE9	588.4	KF96383PE2	51846.50
	10	497.4	KG01383PE9	587.5	KG01383PE2	50863.50
12	x 8	724.6	KG35383PE9	836.8	KG35383PE2	88215.00
	10	719.2	KG39383PE9	831.4	KG39383PE2	89157.00
	12	671.7	KG45383PE9	777.8	KG45383PE2	83480.00

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

¥ Estimated weight using Sch. 40 black carbon steel pipe

† The 1¼" – 18 UNEF female thermometer connection fits most commercially available thermometers with the well removed.

NOTE: A ¾" female NPT thermometer connection is also available. Contact Victaulic for more information.

* This size has a ¾" FNPT supplied as a connection to accept a customer-supplied thermometer well or other accessory; this part code represents that offering.

NOTE: A Victaulic Style 107V Rigid Coupling is required for the installation of this product (not supplied). Refer to Section 1 – Couplings and Fittings for coupling pricing.

TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. Box 31, Easton, PA 18044-0031 • 4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com