

Price List Addendum

EFFECTIVE October 17, 2022



PL2022-A-GEN-ADD2

Grooved IPS Pipe Couplings

QuickVic™ Rigid Coupling

STYLE 107V

Refer to publication 06.33



STYLE 107V – GRADE “EHP” GASKET

PIPE		Approx. Wgt. Ea.	COUPLING COMPLETE † With Grade “EHP” or “HMT” Gasket		SPARE PARTS			
inches			Price Each		Grade “EHP” or “HMT” Gasket	Plated Bolt & Nut		
Nom. Size	Outside Dia.	lb	Painted	Galv.		No. *	Size inches	Price Each
2	2.375	2.9	\$136.50	171.50	\$107.00 ^{NR}	2	1/2 x 2 3/4	\$43.50
2 1/2	2.875	3.3	154.50	194.50	116.00 ^{NR}	2	1/2 x 2 3/4	43.50
3	3.500	3.7	178.50	226.50	131.00 ^{NR}	2	1/2 x 3	67.50
4	4.500	5.0	247.00	318.50	174.50 ^{NR}	2	1/2 x 3	67.50
5	5.563	7.0	318.50	414.00	261.50	2	5/8 x 4	82.00 ^{NR}
6	6.625	8.1	416.00	541.00	290.50 ^{NR}	2	5/8 x 3 5/8	82.00 ^{NR}
8	8.625	16.1	657.00	853.50	349.50 ^{NR}	2	3/4 x 5	150.00
10	10.750	24.7	1271.00	1694.50	403.50 ^{NR}	2	7/8 x 6 1/2	267.50
12	12.750	29.1	1419.50	1900.50	448.00	2	7/8 x 6 1/2	267.50

† Surcharge for couplings supplied without gasket. Contact Victaulic for pricing.

^{NR} Non-returnable

Orders for the Style 107N QuickVic™ Rigid Coupling may be automatically substituted for the Style 107V QuickVic™ Rigid Coupling at Victaulic's discretion.

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

* Number of bolts equals number of segments supplied.

Grooved IPS Pipe Fittings

QuickVic™ Elbows

Refer to publication 07.14



No. V10



No. V11

ELBOWS – 90° ELBOW OR 45° ELBOW

Nom. Size	Approx. Wgt. Ea. lb	90° Elbow No. V10		Approx. Wgt. Ea. lb	45° Elbow No. V11	
		Price Each			Price Each	
inches	lb	Painted	Galv.	lb	Painted	Galv.
2	1.5	\$45.00	\$61.00	1.2	\$45.00	\$61.00
2 1/2	2.2	52.50	71.00	1.7	52.50	71.00
3	2.9	82.50	111.50	2.3	82.50	111.50
4	4.4	101.00	136.50	3.7	101.00	136.50
5	7.3	130.50	174.50	5.4	130.50	174.50
6	10.8	157.50	213.00	7.4	157.50	213.00
8	25.4	237.50	321.00	18.9	160.00	216.00
10	41.0	256.50	346.50	25.0	166.50	225.00
12	66.3	368.00	497.00	35.9	260.50	352.00



QuickVic™ Couplings and Fittings

QuickVic™ Tee

Refer to publication 07.14



No. V20

STANDARD TEE

Nom. Size	Approx. Wgt. Ea.	Tee No. V20	
		Price Each	
inches	lb	Painted	Galv.
2	2.1	\$70.50	\$95.50
2½	2.2	78.00	105.50
3	4.8	99.00	134.00
4	6.0	169.50	229.00
5	14.4	213.00	286.00
6	20.0	254.00	343.00
8	36.9	287.50	388.50
10	63.6	306.50	414.00
12	90.3	520.50	703.00

TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. Box 31, Easton, PA 18044-0031 • 4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com