

Price List Addendum

EFFECTIVE January 19, 2023



PL2023-A-GEN-ADD5

Grooved IPS Pipe Accessories

Expansion Joint for OGS
Potable Water Piping Systems



STYLE 155P

Refer to publication 09.25

STYLE 155P – EXPANSION JOINT FOR OGS POTABLE WATER PIPING SYSTEMS

Nominal Size	Painted Couplings & Uncoated SS Pipe Sections				Approx. Wgt. Ea.	COUPLING COMPLETE with Grade "P" Gasket and Carbon Steel Bolts & Nuts	COUPLING COMPLETE with Grade "P" Gasket and Stainless Steel Bolts & Nuts
	Movement					Painted Couplings and Uncoated SS Pipe Sections	
	Maximum	Compressed	Neutral	Expanded		Price Each	
	inches				lb	Price Each	
2	0.19	8.00	8.09	8.17	4.0	\$5840.00	+
	0.38	10.25	10.43	10.61	6.3	6567.00	+
	0.57	12.50	12.78	13.05	8.6	6875.50	+
	0.76	14.75	15.12	15.49	10.9	7186.00	+
	0.95	17.00	17.47	17.93	13.2	7494.50	+
	1.14	19.25	19.81	20.37	15.5	10403.00	+
	1.33	21.50	22.16	22.81	17.7	10816.00	+
	1.52	23.75	24.50	25.25	20.0	11231.50	+
	1.71	26.00	26.85	27.69	22.3	11645.50	+
	1.90	28.25	29.19	30.13	24.6	12057.00	+
2½	2.09	30.50	31.54	32.57	26.9	12466.00	+
	2.28	32.75	33.88	35.01	29.2	12881.50	+
	0.19	8.00	8.09	8.17	5.9	7690.50	+
	0.38	10.25	10.43	10.61	8.9	9009.50	+
	0.57	12.50	12.78	13.05	12.0	9472.00	+
	0.76	14.75	15.12	15.49	15.1	9940.00	+
	0.95	17.00	17.47	17.93	18.2	10399.50	+
	1.14	19.25	19.81	20.37	21.3	10862.00	+
	1.33	21.50	22.16	22.81	24.4	11328.00	+
	1.52	23.75	24.50	25.25	27.5	13264.50	+
3	1.71	26.00	26.85	27.69	30.5	13783.50	+
	1.90	28.25	29.19	30.13	33.6	14310.00	+
	2.09	30.50	31.54	32.57	36.7	15155.50	+
	2.28	32.75	33.88	35.01	39.8	15618.00	+
	0.19	8.00	8.09	8.17	7.6	7911.50	+
	0.38	10.25	10.43	10.61	11.5	9374.50	+
	0.57	12.50	12.78	13.05	15.4	9960.00	+
	0.76	14.75	15.12	15.49	19.3	10545.00	+
	0.95	17.00	17.47	17.93	23.2	11964.50	+
	1.14	19.25	19.81	20.37	27.2	12596.50	+
3	1.33	21.50	22.16	22.81	31.1	13224.50	+
	1.52	23.75	24.50	25.25	35.0	13853.00	+
	1.71	26.00	26.85	27.69	38.9	14484.00	+
	1.90	28.25	29.19	30.13	42.8	15114.50	+
	2.09	30.50	31.54	32.57	46.8	15743.00	+
	2.28	32.75	33.88	35.01	50.7	16374.00	+

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

+ Quoted on application. Contact Victaulic for pricing and availability.



Valves & Specialties

Expansion Joint for OGS Potable Water Piping Systems



STYLE 155P

Refer to publication 09.25

STYLE 155P – EXPANSION JOINT FOR OGS POTABLE WATER PIPING SYSTEMS

Nominal Size	Painted Couplings & Uncoated SS Pipe Sections				Approx. Wgt. Ea. lb	COUPLING COMPLETE with Grade "P" Gasket and Carbon Steel Bolts & Nuts	COUPLING COMPLETE with Grade "P" Gasket and Stainless Steel Bolts & Nuts
	Movement					Painted Couplings and Uncoated SS Pipe Sections	
	Maximum inches	Compressed	Neutral	Expanded		Price Each	
4	0.25	11.97	12.1	12.22	3.5	\$10914.50	+
	0.5	14.35	14.6	14.85	7.0	11674.50	+
	0.75	16.73	17.11	17.48	10.5	12432.00	+
	1	19.11	19.61	20.11	14.0	13189.50	+
	1.25	21.49	22.12	22.74	17.5	13950.00	+
	1.5	23.87	24.62	25.37	21.0	14708.50	+
	1.75	26.25	27.13	28	24.5	15464.50	+
	2	28.63	29.63	30.63	28.0	16222.00	+
	2.25	31.01	32.14	33.26	31.5	16982.00	+
	2.5	33.39	34.64	35.89	35.0	17738.00	+
6	0.25	11.97	12.1	12.22	6.7	13568.50	+
	0.5	14.35	14.6	14.85	13.4	15291.50	+
	0.75	16.73	17.11	17.48	20.1	16327.00	+
	1	19.11	19.61	20.11	26.8	17368.00	+
	1.25	21.49	22.12	22.74	33.5	18408.50	+
	1.5	23.87	24.62	25.37	40.2	19448.00	+
	1.75	26.25	27.13	28	46.9	20491.00	+
	2	28.63	29.63	30.63	53.6	21528.00	+
	2.25	31.01	32.14	33.26	60.3	22567.50	+
	2.5	33.39	34.64	35.89	67.0	23609.50	+
8	0.25	12	12.13	12.25	12.5	16484.50	+
	0.5	14.75	15	15.25	25.0	18014.00	+
	0.75	17.5	17.88	18.25	37.5	19547.50	+
	1	20.25	20.75	21.25	50.0	21073.50	+
	1.25	23	23.63	24.25	62.5	22602.00	+
	1.5	25.75	26.5	27.25	75.0	25099.00	+
	1.75	28.5	29.38	30.25	87.5	26688.50	+
	2	31.25	32.25	33.25	100.0	28277.00	+
	2.25	34	35.13	36.25	112.5	29868.00	+
	2.5	36.75	38	39.25	125.0	31461.00	+
	2.75	39.5	40.88	42.25	137.5	33055.00	+
	3	42.25	43.75	45.25	150.0	34638.50	+

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

+ Quoted on application. Contact Victaulic for pricing and availability.

Valves & Specialties

Expansion Joint for OGS Potable Water Piping Systems



STYLE 155P

Refer to publication 09.25

STYLE 155P – EXPANSION JOINT FOR OGS POTABLE WATER PIPING SYSTEMS

Nominal Size	Painted Couplings & Uncoated SS Pipe Sections				Approx. Wgt. Ea.	COUPLING COMPLETE with Grade "P" Gasket and Carbon Steel Bolts & Nuts	COUPLING COMPLETE with Grade "P" Gasket and Stainless Steel Bolts & Nuts
	Movement					Painted Couplings and Uncoated SS Pipe Sections	Price Each
	Maximum	Compressed	Neutral	Expanded			
	inches				lb		
10	0.25	16.00	16.13	16.25	82.3	\$19252.50	+
	0.50	18.75	19.00	19.25	119.9	21749.00	+
	0.75	21.50	21.88	22.25	157.4	24246.00	+
	1.00	24.25	24.75	25.25	195.0	26746.00	+
	1.25	27.00	27.63	28.25	232.6	29243.50	+
	1.50	29.75	30.50	31.25	270.2	31744.50	+
	1.75	32.50	33.38	34.25	307.8	34240.50	+
	2.00	35.25	36.25	37.25	345.3	36739.00	+
	2.25	38.00	39.13	40.25	382.9	40220.50	+
	2.50	40.75	42.00	43.25	420.5	42780.50	+
12	0.25	16.00	16.13	16.25	100.3	19869.00	+
	0.50	18.75	19.00	19.25	145.8	22668.00	+
	0.75	21.50	21.88	22.25	191.4	25465.50	+
	1.00	24.25	24.75	25.25	237.0	28267.00	+
	1.25	27.00	27.63	28.25	282.5	31068.00	+
	1.50	29.75	30.50	31.25	328.1	33865.50	+
	1.75	32.50	33.38	34.25	373.6	36665.50	+
	2.00	35.25	36.25	37.25	419.2	39463.50	+
	2.25	38.00	39.13	40.25	464.8	42264.00	+
	2.50	40.75	42.00	43.25	510.3	45064.00	+
	2.75	43.50	44.88	46.25	555.9	47862.50	+
	3.00	46.25	47.75	49.25	601.4	50662.00	+

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

+ Quoted on application. Contact Victaulic for pricing and availability.

Style 155P Expansion Joint Configurator Painted Couplings and Uncoated Stainless Steel Pipe Sections

C A A N 155P H P Z

Class	Size in/mm	Movement	Length	Style	Finish	Gasket	Bolts and Nuts
C	E - 2/50 F - 2½/65 H - 3/80 J - 4/100 M - 6/150 O - 8/200 P - 10/250 Q - 12/300	A - 0.19 B - 0.25 C - 0.38 D - 0.50 E - 0.57 F - 0.75 G - 0.76 H - 0.95 I - 1.00 J - 1.14 K - 1.25 L - 1.33 M - 1.50 N - 1.52 O - 1.71 P - 1.75 Q - 1.90 R - 2.00 S - 2.09 T - 2.25 U - 2.28 X - 2.50 Y - 2.75 Z - 3.00	C - Compressed N - Neutral E - Expanded	155	H - Painted Blue	P - Fluoroelastomer Blend	Z - Plated X - Stainless Steel

TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. Box 31, Easton, PA 18044-0031 • 4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com