

Price List Addendum

EFFECTIVE November 21, 2022

Series FL-QR/DRY/C
V5634, V8134

DRY TYPE
QUICK RESPONSE
CONCEALED PENDENT
1" NPT (25 MM BSPT) THREAD I
1" IGS GROOVE
1" COVERPLATE ADJUSTMENT

K5.6 (8.1 SI) - V5634
K8.0 (11.5 SI) - V8134
Refer to publication 45.03.



Length Inches	Price Each \$ Plain Brass
Min.* - 8 ⁷ / ₈	\$371.50
9 - 12 ⁷ / ₈	385.00
13 - 16 ⁷ / ₈	415.50
17 - 20 ⁷ / ₈	443.00
21 - 24 ⁷ / ₈	460.00
25 - 26 ⁷ / ₈	467.00
27 - 28 ⁷ / ₈	477.00
29 - 32 ⁷ / ₈	492.50
33 - 35 ⁷ / ₈	506.50
36 - 36 ⁷ / ₈	557.00
37 - 37 ⁷ / ₈	575.00

Length Inches	Price Each \$ Plain Brass
38 - 38 ⁷ / ₈	\$591.00
39 - 39 ⁷ / ₈	607.50
40 - 40 ⁷ / ₈	627.00
41 - 41 ⁷ / ₈	643.50
42 - 42 ⁷ / ₈	662.00
43 - 43 ⁷ / ₈	680.00
44 - 44 ⁷ / ₈	695.50
45 - 45 ⁷ / ₈	713.00
46 - 46 ⁷ / ₈	729.50
47 - 47 ⁷ / ₈	745.50
48	762.00

* Minimum pipe order length is 4" for thread connection and 5¹/₄" for IGS™ groove connection. Any length below the minimum pipe order length is an additional **\$93.00** LIST charge per unit.

§ Price includes coverplate as noted in the order form; for custom finishes contact Victaulic for details.

REPLACEMENT V56, V81 COVER PLATES (IF ADDITIONAL PLATES ARE NEEDED)

Temp. Rating		Victaulic Part Number	Finish	Price
°F	°C			
ORDINARY TEMPERATURE				
135	57	S110NA0020	Chrome	\$9.00
135	57	S110NA0040	White	9.00
135	57	S110NA00W0	Bright White	9.00
135	57	S110NA00B0	Black	20.50
135	57	S110NA00_0	Custom	+
INTERMEDIATE TEMPERATURE				
155	68	S110NC0020	Chrome	9.00
155	68	S110NC0040	White	9.00
155	68	S110NC00W0	Bright White	9.00
155	68	S110NC00B0	Black	20.50
155	68	S110NC00_0	Custom	+

NOTE: Use Dry Sprinkler Order Form to provide correct figure number configuration.

‡ Delivery times and pricing may vary. Customer must provide paint specification.

Recommended Wrenches: V56/V81 Concealed Dry & V11 Concealed ECLH. See Accessories for part number and price.

Dry sprinklers are non-cancellable and non-returnable.

FireLock™ Sprinklers – Dry

Series FL-SR/DRY/C V5689, V8189

DRY TYPE
STANDARD RESPONSE
CONCEALED PENDENT
1" NPT (25 MM BSPT) THREAD I
1" IGS GROOVE
1" COVERPLATE ADJUSTMENT

K5.6 (8.1 SI) - V5689

K8.0 (11.5 SI) - V8189

Refer to publication 45.53.



Length Inches	Price Each \$ Plain Brass
Min.* – 8 ⁷ / ₈	\$345.00
9 – 12 ⁷ / ₈	358.00
13 – 16 ⁷ / ₈	389.50
17 – 20 ⁷ / ₈	413.50
21 – 24 ⁷ / ₈	429.00
25 – 26 ⁷ / ₈	434.00
27 – 28 ⁷ / ₈	450.00
29 – 32 ⁷ / ₈	464.50
33 – 35 ⁷ / ₈	474.00
36 – 36 ⁷ / ₈	518.00
37 – 37 ⁷ / ₈	532.50

Length Inches	Price Each \$ Plain Brass
38 – 38 ⁷ / ₈	\$555.00
39 – 39 ⁷ / ₈	570.00
40 – 40 ⁷ / ₈	588.00
41 – 41 ⁷ / ₈	605.00
42 – 42 ⁷ / ₈	621.50
43 – 43 ⁷ / ₈	638.50
44 – 44 ⁷ / ₈	656.00
45 – 45 ⁷ / ₈	673.00
46 – 46 ⁷ / ₈	689.50
47 – 47 ⁷ / ₈	705.00
48	724.50

§ Price includes chrome or white painted coverplate; for custom finishes contact Victaulic for details.

* Minimum pipe order length is 4" for thread connection and 5¹/₄" for IGS™ groove connection. Any length below the minimum pipe order length is an additional **\$93.00** LIST charge per unit.

§ Price includes coverplate as noted in the order form; for custom finishes contact Victaulic for details.

REPLACEMENT V56, V81 COVER PLATES (IF ADDITIONAL PLATES ARE NEEDED)

Temp. Rating		Victaulic Part Number	Finish	Price
°F	°C			
ORDINARY TEMPERATURE				
135	57	S110NA0020	Chrome	\$9.00
135	57	S110NA0040	White	9.00
135	57	S110NA00W0	Bright White	9.00
135	57	S110NA00B0	Black	20.50
135	57	S110NA00_0	Custom	+
INTERMEDIATE TEMPERATURE				
155	68	S110NC0020	Chrome	9.00
155	68	S110NC0040	White	9.00
155	68	S110NC00W0	Bright White	9.00
155	68	S110NC00B0	Black	20.50
155	68	S110NC00_0	Custom	+

NOTE: Use Dry Sprinkler Order Form to provide correct figure number configuration.

‡ Delivery times and pricing may vary. Customer must provide paint specification.

Recommended Wrenches: V56/V81 RC Dry, V11 C ECLH. See Accessories for part number and price.

Dry sprinklers are non-cancellable and non-returnable.

TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. Box 31, Easton, PA 18044-0031 • 4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com