

# Price List Addendum

EFFECTIVE July 18, 2023



PL2023-GEN-ADD3

## Grooved IPS Valves

### Ball Valve

#### SERIES 727

Refer to publication 08.42



Bare Valve



With Lever Handle

#### SERIES 727 – BARE VALVE WITH CARBON STEEL OR STAINLESS STEEL TRIM

Nominal Size inches	Approx. Wgt. Each lb	Price Each			
		Bare Valve with Carbon Steel Trim	Bare Valve with Carbon Steel Trim and Uni- Directional Ball (Freeze Port)	Bare Valve with Stainless Steel Trim	Bare Valve with Stainless Steel Trim and Uni- Directional Ball (Freeze Port)
<b>Grooved x Grooved</b>					
2	11.0	\$240.00	\$288.00	\$340.00	\$408.00
3	22.0	480.00	576.00	740.00	888.00
4	48.0	640.00	768.00	1100.00	1320.00
6	105.0	2000.00	2400.00	2400.00	2880.00
<b>Grooved x Male Threaded</b>					
2	12.0	\$240.00	\$288.00	\$340.00	\$408.00
3	25.0	480.00	576.00	740.00	888.00
4	50.0	640.00	768.00	1100.00	1320.00

#### SERIES 727 – LEVER HANDLE WITH CARBON STEEL OR STAINLESS STEEL TRIM

Nominal Size inches	Approx. Wgt. Each lb	Price Each			
		Lever Handle with Carbon Steel Trim	Lever Handle with Carbon Steel Trim and Uni-Directional Ball (Freeze Port)	Lever Handle with Stainless Steel Trim	Lever Handle with Stainless Steel Trim and Uni-Directional Ball (Freeze Port)
<b>Grooved x Grooved</b>					
2	13.0	\$300.00	\$348.00	\$400.00	\$468.00
3	24.0	540.00	636.00	800.00	948.00
4	54.0	800.00	928.00	1260.00	1480.00
6	115.0	2160.00	2560.00	2560.00	3040.00
<b>Grooved x Male Threaded</b>					
2	14.0	\$300.00	\$348.00	\$400.00	\$468.00
3	26.0	540.00	636.00	800.00	948.00
4	55.0	800.00	928.00	1260.00	1480.00

V - 040 - 727 P O - S

Type	In./mm	Size Code	Series	End Configuration	Operator/ Ball Option	Trim
V	2/50	020	727	P - Grooved Ends T - Grooved x Male Threaded	0 - Standard Ball w/o handle	C - Electroless nickel plated (ENP) Carbon Steel Trim S - CF8M/316SS Stainless Steel Trim
	3/80	030			1 - Uni-Directional Ball (Freeze Port) w/o handle	
	4/100	040			H - Standard Ball with handle	
	6/150	060			2 - Uni-Directional Ball (Freeze Port) with handle	

When ordered separately, handles and locking device kits are non-cancellable and non-returnable.

### TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. Box 31, Easton, PA 18044-0031 • 4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com

