

# Price List Addendum

EFFECTIVE June 27, 2023



PL2023-SD-ADD1

Series FL-QR/DRY/C  
V5634, V8134

DRY TYPE  
QUICK RESPONSE  
CONCEALED PENDENT  
1" NPT (25 MM BSPT) THREAD |  
1" IGS GROOVE  
1" COVERPLATE ADJUSTMENT

K5.6 (8.1 SI) - V5634  
K8.0 (11.5 SI) - V8134  
Refer to publication 45.03.



Length	Price Each \$
Inches	Plain Brass, Chrome, White, or Black Finishes
Min.* - 8 <sup>7</sup> / <sub>8</sub>	\$401.50
9 - 12 <sup>7</sup> / <sub>8</sub>	416.00
13 - 16 <sup>7</sup> / <sub>8</sub>	449.00
17 - 20 <sup>7</sup> / <sub>8</sub>	478.50
21 - 24 <sup>7</sup> / <sub>8</sub>	497.00
25 - 26 <sup>7</sup> / <sub>8</sub>	504.50
27 - 28 <sup>7</sup> / <sub>8</sub>	515.50
29 - 32 <sup>7</sup> / <sub>8</sub>	532.00
33 - 35 <sup>7</sup> / <sub>8</sub>	547.50
36 - 36 <sup>7</sup> / <sub>8</sub>	602.00
37 - 37 <sup>7</sup> / <sub>8</sub>	621.00

Length	Price Each \$
Inches	Plain Brass, Chrome, White, or Black Finishes
38 - 38 <sup>7</sup> / <sub>8</sub>	\$638.50
39 - 39 <sup>7</sup> / <sub>8</sub>	656.50
40 - 40 <sup>7</sup> / <sub>8</sub>	677.50
41 - 41 <sup>7</sup> / <sub>8</sub>	695.00
42 - 42 <sup>7</sup> / <sub>8</sub>	715.00
43 - 43 <sup>7</sup> / <sub>8</sub>	734.50
44 - 44 <sup>7</sup> / <sub>8</sub>	751.50
45 - 45 <sup>7</sup> / <sub>8</sub>	770.50
46 - 46 <sup>7</sup> / <sub>8</sub>	788.00
47 - 47 <sup>7</sup> / <sub>8</sub>	805.50
48	823.00

§ Price includes chrome or white painted coverplate; for custom finishes contact Victaulic for details.

\* Minimum pipe order length is 4 ¼" for thread connection and 5 ¼" for IGS™ groove connection.

Dry Sprinklers above 48" are not available.

## REPLACEMENT V56, V81 COVER PLATES (IF ADDITIONAL PLATES ARE NEEDED)

Temp. Rating		Victaulic Part Number	Finish	Price
°F	°C			
<b>ORDINARY TEMPERATURE</b>				
135	57	S110NA0020	Chrome	\$10.00
135	57	S110NA0040	White	10.00
135	57	S110NA00W0	Bright White	10.00
135	57	S110NA00B0	Black	22.50
135	57	S110NA00_0	Custom	+
<b>INTERMEDIATE TEMPERATURE</b>				
155	68	S110NC0020	Chrome	10.00
155	68	S110NC0040	White	10.00
155	68	S110NC00W0	Bright White	10.00
155	68	S110NC00B0	Black	22.50
155	68	S110NC00_0	Custom	+

**NOTE: Use Dry Sprinkler Order Form to provide correct figure number configuration.**

‡ Delivery times and pricing may vary. Customer must provide paint specification.

**Recommended Wrenches:** V56/V81 Concealed Dry & V11 Concealed ECLH. See Accessories for part number and price.

**Dry sprinklers are non-cancellable and non-returnable.**



# FireLock™ Sprinklers – Dry

## Series FL-SR/DRY/C V5689, V8189

DRY TYPE  
STANDARD RESPONSE  
CONCEALED PENDENT  
1" NPT (25 MM BSPT) THREAD I  
1" IGS GROOVE  
1" COVERPLATE ADJUSTMENT

K5.6 (8.1 SI) - V5689  
K8.0 (11.5 SI) - V8189

Refer to publication 45.53.



Length	Price Each §
Inches	Plain Brass, Chrome, White, or Black Finishes
Min.* – 8 <sup>7</sup> / <sub>8</sub>	\$373.00
9 – 12 <sup>7</sup> / <sub>8</sub>	387.00
13 – 16 <sup>7</sup> / <sub>8</sub>	421.00
17 – 20 <sup>7</sup> / <sub>8</sub>	447.00
21 – 24 <sup>7</sup> / <sub>8</sub>	463.50
25 – 26 <sup>7</sup> / <sub>8</sub>	469.00
27 – 28 <sup>7</sup> / <sub>8</sub>	486.00
29 – 32 <sup>7</sup> / <sub>8</sub>	502.00
33 – 35 <sup>7</sup> / <sub>8</sub>	512.00
36 – 36 <sup>7</sup> / <sub>8</sub>	559.50
37 – 37 <sup>7</sup> / <sub>8</sub>	575.50

Length	Price Each §
Inches	Plain Brass, Chrome, White, or Black Finishes
38 – 38 <sup>7</sup> / <sub>8</sub>	\$599.50
39 – 39 <sup>7</sup> / <sub>8</sub>	616.00
40 – 40 <sup>7</sup> / <sub>8</sub>	635.50
41 – 41 <sup>7</sup> / <sub>8</sub>	653.50
42 – 42 <sup>7</sup> / <sub>8</sub>	671.50
43 – 43 <sup>7</sup> / <sub>8</sub>	690.00
44 – 44 <sup>7</sup> / <sub>8</sub>	708.50
45 – 45 <sup>7</sup> / <sub>8</sub>	727.00
46 – 46 <sup>7</sup> / <sub>8</sub>	745.00
47 – 47 <sup>7</sup> / <sub>8</sub>	761.50
48	782.50

§ Price includes chrome or white painted coverplate; for custom finishes contact Victaulic for details.

\* Minimum pipe order length is 4 1/4" for thread connection and 5 1/4" for IGS™ groove connection.

Dry Sprinklers above 48" are not available.

### REPLACEMENT V56, V81 COVER PLATES (IF ADDITIONAL PLATES ARE NEEDED)

Temp. Rating		Victaulic Part Number	Finish	Price
°F	°C			
<b>ORDINARY TEMPERATURE</b>				
135	57	S110NA0020	Chrome	\$10.00
135	57	S110NA0040	White	10.00
135	57	S110NA00W0	Bright White	10.00
135	57	S110NA00B0	Black	22.50
135	57	S110NA00_0	Custom	+
<b>INTERMEDIATE TEMPERATURE</b>				
155	68	S110NC0020	Chrome	10.00
155	68	S110NC0040	White	10.00
155	68	S110NC00W0	Bright White	10.00
155	68	S110NC00B0	Black	22.50
155	68	S110NC00_0	Custom	+

**NOTE: Use Dry Sprinkler Order Form to provide correct figure number configuration.**

‡ Delivery times and pricing may vary. Customer must provide paint specification.

**Recommended Wrenches:** V56/V81 RC Dry, V11 C ECLH. See Accessories for part number and price.

Dry sprinklers are non-cancellable and non-returnable.

### TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. Box 31, Easton, PA 18044-0031 • 4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com