

# Price List Addendum

EFFECTIVE May 28, 2024

## AWWA Fittings

### Mechanical-T Spigot

#### STYLE 926

For use with AWWA C151 Size Pipe

Refer to publication 11.07



Nominal Size inches	Approx. Wgt. Ea.	COMPLETE MECHANICAL-T Spigot		SPARE PARTS	
		Price Each		O-Ring Grade "T"	U-Bolts/Nuts
		Unlined	Rubber Lined †	Price Each	Price per Set •
10 x 4	30.0	\$1226.50	+	\$107.50 <sup>NR</sup>	\$124.50
12 x 4	33.0	1402.00	+	107.50 <sup>NR</sup>	124.50
14 x 4	35.0	1577.50	+	107.50 <sup>NR</sup>	124.50
16 x 4	36.0	1927.00	+	107.50 <sup>NR</sup>	124.50
	6	2102.00	+	142.50 <sup>NR</sup>	124.50
18 x 4	37.0	2188.50	+	107.50 <sup>NR</sup>	124.50
	6	2408.00	+	142.50 <sup>NR</sup>	124.50
20 x 4	39.0	2539.50	+	107.50 <sup>NR</sup>	124.50
	6	2802.50	+	142.50 <sup>NR</sup>	124.50
24 x 4	41.0	3064.00	+	107.50 <sup>NR</sup>	124.50
	6	3458.00	+	142.50 <sup>NR</sup>	124.50
30 x 4	46.0	3808.00	+	107.50 <sup>NR</sup>	124.50
	6	4857.00	+	142.50 <sup>NR</sup>	124.50
	8	8434.50	+	149.50 <sup>NR</sup>	124.50
36 x 6	58.0	5601.00	+	142.50 <sup>NR</sup>	124.50
	8	8647.50	+	149.50 <sup>NR</sup>	124.50

\* Replacement hardware kit consists of one 6, 8, or 10" U-bolt, two washers and two hex nuts.

† Standard rubber lining – ¼" thick, 40 durometer natural rubber lining. Other materials or thicknesses quoted upon request.

**NOTE: Items listed in shaded areas are non-cancellable and non-returnable.**

<sup>NR</sup> Non-returnable

#### TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. Box 31, Easton, PA 18044-0031 • 4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com