

Tool Accessories

PS3400



Adjustable Pipe Stands are portable and self-standing units. Rotating design allows pipe to be spun around for grooving of both pipe ends without removing pipe from the stand. They are designed for direct use with roll grooving tools: RG3212 and RG3400.

Capacities: 1 – 12"/DN25 – DN300 IPS pipe †

Load Rating: 750 lbs

Vertical Stroke: 9.9"/251 mm

Min. Pipe Height from Floor: 17.83"/453mm on 12"/DN300 pipe and 21.3"/541mm on 1"/DN25 pipe

Max. Pipe Height from Floor: 27.72"/704mm on 12"/DN300 pipe and 31.2"/792mm on 1"/DN25 pipe

Tool Model	Part Number	Tool Weight/ Shipping Weight lb	Tool List Price
PS3400	NMSC000120	40/45	\$1000.00

† Indicates pipe size capacity. For wall thickness capacity and general tool ratings see separate Tool Rating Data in publication 24.01.

TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. Box 31, Easton, PA 18044-0031 • 4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com