

# Price List Addendum

EFFECTIVE May 28, 2024



PL2024-GEN-ADD1

## Couplings for HDPE Pipe

(See Hole Cut Section for Style 920/920N Mechanical-T Outlets.)

### Mechanical-T Spigot

#### STYLE 926

For use with IPS Steel and HDPE Pipe

Refer to publication 11.07



Nominal Size inches	Approx. Wgt. Ea.	COMPLETE MECHANICAL-T Spigot		SPARE PARTS	
		Price Each		O-Ring Grade "T"	U-Bolts/Nuts
		Unlined	Rubber Lined †	Price Each	Price per Set *
Host Pipe x Outlet	lb				
10 x 4	31.0	\$1183.00	+	\$107.50 <sup>NR</sup>	124.50
12 x 4	33.0	1350.00	+	107.50 <sup>NR</sup>	124.50
14 x 4	33.0	1515.50	+	107.50 <sup>NR</sup>	124.50
16 x 4	35.0	1700.00	+	107.50 <sup>NR</sup>	124.50
16 x 6	43.0	1840.50	+	142.50 <sup>NR</sup>	124.50
18 x 4	36.0	2015.00	+	107.50 <sup>NR</sup>	124.50
18 x 6	45.0	2188.50	+	142.50 <sup>NR</sup>	124.50
20 x 4	38.0	2364.00	+	107.50 <sup>NR</sup>	124.50
20 x 6	46.0	2609.50	+	142.50 <sup>NR</sup>	124.50
22 x 4	39.0	2627.00	+	107.50 <sup>NR</sup>	124.50
22 x 6	47.0	2802.50	+	142.50 <sup>NR</sup>	124.50
24 x 4	40.0	2802.50	+	107.50 <sup>NR</sup>	124.50
24 x 6	48.0	3107.50	+	142.50 <sup>NR</sup>	124.50
26 x 4	41.0	3064.00	+	107.50 <sup>NR</sup>	124.50
26 x 6	50.0	3458.00	+	142.50 <sup>NR</sup>	124.50
28 x 4	43.0	3414.50	+	107.50 <sup>NR</sup>	124.50
28 x 6	51.0	4114.00	+	142.50 <sup>NR</sup>	124.50
28 x 8	52.0	8305.50	+	149.50 <sup>NR</sup>	124.50
30 x 4	44.0	3589.00	+	107.50 <sup>NR</sup>	124.50
30 x 6	53.0	4376.50	+	142.50 <sup>NR</sup>	124.50
30 x 8	52.0	8356.00	+	149.50 <sup>NR</sup>	124.50
32 x 4	46.0	3808.00	+	107.50 <sup>NR</sup>	124.50
32 x 6	54.0	4857.00	+	142.50 <sup>NR</sup>	124.50
32 x 8	52.0	8434.50	+	149.50 <sup>NR</sup>	124.50
36 x 6	56.0	5426.50	+	142.50 <sup>NR</sup>	124.50
36 x 8	50.0	8494.00	+	149.50 <sup>NR</sup>	124.50
42 x 6	60.0	+	+	+	+
48 x 6	64.0	+	+	+	+

**NOTE: Items listed in shaded areas are non-cancellable and non-returnable.**

\* Replacement hardware kit consists of one 6, 8, or 10" U-bolt, two washers and two hex nuts.

† Standard rubber lining – 1/4" thick, 40 durometer natural rubber lining. Other materials or thicknesses quoted upon request.

<sup>NR</sup> Non-returnable

+ Quoted on application. Contact Victaulic for pricing and availability.

### Style 926 Spigot Hole Saw for HDPE Pipe



Nominal Size inches	Cutter Diameter inches	Part Number	Purchase List Price Each
4	4.500	R040926HHS	\$807.50
6	6.625	R060926HHS	1203.50
8	8.250	R080926HHS	1453.00

**NOTE: Items listed in shaded areas are non-cancellable and non-returnable.**

#### TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. Box 31, Easton, PA 18044-0031 • 4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com

