

# Price List Addendum

EFFECTIVE July 1, 2024



PL2024-GEN-ADD4

## QuickVic™ Rigid Coupling

### STYLE 107V

Refer to publication 06.33



#### STYLE 107V – GRADE “EHP” GASKET

PIPE		Approx. Wgt. Ea.	COUPLING COMPLETE † With Grade “EHP” or “HMT” Gasket and Plated Bolts and Nuts		COUPLING COMPLETE † With Grade “EHP” or “HMT” Gasket and Stainless Steel Bolts and Nuts		COUPLING COMPLETE † With Grade “EHP” or “HMT” Gasket and Galvanized Bolts and Nuts		COUPLING COMPLETE † With Grade “EHP” or “HMT” Gasket and TDZ Bolts and Nuts	
inches			Price Each		Price Each		Price Each		Price Each	
Nom. Size	Outside Dia.		Painted	Galv.	Painted	Galv.	Painted	Galv.	Painted	Galv.
2	2.375	2.9	\$156.50	\$197.00	\$465.00	\$550.00	\$295.00	\$335.00	\$285.00	+
2½	2.875	3.3	177.50	223.50	505.00	590.00	345.00	390.00	315.00	+
3	3.500	3.7	205.00	260.00	565.00	655.00	440.00	505.00	355.00	+
4	4.500	5.0	283.50	365.00	670.00	785.00	535.00	615.00	455.00	+
5	5.563	7.0	365.00	474.50	1055.00	1190.00	635.00	745.00	+	+
6	6.625	8.1	476.50	620.00	1175.00	1340.00	765.00	905.00	665.00	+
8	8.625	16.1	753.00	977.50	1470.00	1735.00	1070.00	1305.00	965.00	+
10	10.750	24.7	1455.50	1940.50	2176.50	2760.00	1790.00	2280.00	1675.00	+
12	12.750	29.1	1626.00	2176.50	2385.00	3075.00	1975.00	2535.00	1865.00	+

† Surcharge for couplings supplied without gasket. Contact Victaulic for pricing.

Orders for the Style 107N QuickVic™ Rigid Coupling may be automatically substituted for the Style 107V QuickVic™ Rigid Coupling at Victaulic's discretion.

**NOTE: Items listed in shaded areas are non-cancellable and non-returnable.**

+ Quoted on application. Contact Victaulic for pricing and availability.

## QuickVic™ Flexible Coupling for Steel

### STYLE 177N

Refer to publication 06.24



#### STYLE 177N – GRADE “EHP”, “T” OR “O” GASKET

PIPE			Approx. Wgt. Ea.	COUPLING COMPLETE † With Grade “EHP” or “T” Gasket with Plated Bolts and Nuts		COUPLING COMPLETE † With Grade “EHP” or “T” Gasket with Stainless Steel Bolts and Nuts		COUPLING COMPLETE † With Grade “EHP” or “T” Gasket with Galvanized Bolts and Nuts		COUPLING COMPLETE † With Grade “EHP” or “T” Gasket with TDZ Bolts and Nuts	
inches				Price Each		Price Each		Price Each		Price Each	
Nom. Size	Outside Dia.	Style		Painted	Galv.	Painted	Galv.	Painted	Galv.	Painted	Galv.
2	2.375	177	3.3	\$157.00	\$205.50	\$480.00	\$565.00	\$305.00	\$345.00	\$290.00	+
2½	2.875		3.8	182.50	252.50	530.00	605.00	355.00	420.00	325.00	+
3	3.500		4.3	200.00	276.50	570.00	675.00	460.00	525.00	355.00	+
4	4.500		7.4	289.00	404.50	685.00	790.00	555.00	655.00	465.00	+
5	5.563		10.0	460.00	657.50	1090.00	1215.00	730.00	945.00	+	+
6	6.625		12.8	511.50	731.00	1195.00	1445.00	795.00	1020.00	705.00	+
8	8.625		20.7	878.00	1302.00	1585.00	2055.00	1195.00	1630.00	1090.00	+
10	10.750	077	23.5	1346.50	1926.50	2175.00	2755.00	1690.00	2270.00	+	+
12	12.750		28.2	1529.50	2186.50	2410.00	3075.00	1880.00	2545.00	+	+

**NOTE: Items listed in shaded areas are non-cancellable and non-returnable.**

† Surcharge for couplings supplied without gasket. Contact Victaulic for pricing.

+ Quoted on application. Contact Victaulic for pricing and availability.

### TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. Box 31, Easton, PA 18044-0031 • 4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com

