

Price List Addendum

EFFECTIVE October 17, 2024

Balancing Control Valves

TA Series 7MP
 Sizes 2½ – 3” – Ductile Iron
 High Pressure

PRESSURE INDEPENDENT BALANCING AND MODULATING CONTROL VALVE

Refer to publication 08.55



TA SERIES 7MP – DUCTILE IRON

Actuator Code Option	Description	Nominal Size inches			
		2½ HF		3 HF	
		Victaulic Part Code	List Price	Victaulic Part Code	List Price
70	SL750/24 Std, 3-pt-24 VAC/VDC	V0247MPH70	\$6409.50	V0307MPH70	\$8521.00
8A	SL750/24 Adv, 3-pt-24 VAC/VDC-w/o opt board	V0247MPH8A	6749.00	V0307MPH8A	8860.50
8B	SL750/24 Adv, 3-pt-24 VAC/VDC-KNX-TP	V0247MPH8B	7007.00	V0307MPH8B	9118.50
8C	SL750/24 Adv, 3-pt-24 VAC/VDC-Modbus RS485	V0247MPH8C	7064.00	V0307MPH8C	9175.50
8D	SL750/24 Adv, 3-pt-24 VAC/VDC-BACnet RS-485	V0247MPH8D	7048.50	V0307MPH8D	9160.00
8E	SL750/24 Adv, 3-pt-24 VAC/VDC-Modbus/TCP	V0247MPH8E	6961.00	V0307MPH8E	9072.50
8F	SL750/24 Adv, 3-pt-24 VAC/VDC-KNX-IP	V0247MPH8F	6961.00	V0307MPH8F	9072.50
8G	SL750/24 Adv, 3-pt-24 VAC/VDC-BACnet/IP	V0247MPH8G	6961.00	V0307MPH8G	9072.50
8I	SL750/24 Adv, 3-pt-24 VAC/VDC-KNX-TP+Rly	V0247MPH8I	7082.50	V0307MPH8I	9194.00
8J	SL750/24 Adv, 3-pt-24 VAC/VDC-Modbus RS485+Rly	V0247MPH8J	7125.00	V0307MPH8J	9236.50
8K	SL750/24 Adv, 3-pt-24 VAC/VDC-BACnet RS-485+Rly	V0247MPH8K	7125.00	V0307MPH8K	9236.50
8L	SL750/24 Adv, 3-pt-24 VAC/VDC-Modbus/TCP+Rly	V0247MPH8L	7038.50	V0307MPH8L	9150.00
8M	SL750/24 Adv, 3-pt-24 VAC/VDC-KNX-IP+Rly	V0247MPH8M	7038.50	V0307MPH8M	9150.00
8N	SL750/24 Adv, 3-pt-24 VAC/VDC-BACnet/IP+Rly	V0247MPH8N	7038.50	V0307MPH8N	9150.00
G0	SL750/HV Std, 3-pt-115/230 VAC	V0247MPHG0	6832.00	V0307MPHG0	8943.50
HA	SL750/HV Adv, 3-pt-115/230 VAC-w/o opt board	V0247MPHHA	7172.00	V0307MPHHA	9283.50
HB	SL750/HV Adv, 3-pt-115/230 VAC-KNX-TP	V0247MPHHB	7428.50	V0307MPHHB	9540.00
HC	SL750/HV Adv, 3-pt-115/230 VAC-Modbus RS485	V0247MPHHC	7485.00	V0307MPHHC	9596.50
HD	SL750/HV Adv, 3-pt-115/230 VAC-BACnet RS-485	V0247MPHHD	7472.00	V0307MPHHD	9583.50
HE	SL750/HV Adv, 3-pt-115/230 VAC-Modbus/TCP	V0247MPHHE	7384.50	V0307MPHHE	9496.00
HF	SL750/HV Adv, 3-pt-115/230 VAC-KNX-IP	V0247MPHHF	7384.50	V0307MPHHF	9496.00
HG	SL750/HV Adv, 3-pt-115/230 VAC-BACnet/IP	V0247MPHHG	7384.50	V0307MPHHG	9496.00
HI	SL750/HV Adv, 3-pt-115/230 VAC-KNX-TP+Rly	V0247MPHHI	7507.00	V0307MPHHI	9618.50
HJ	SL750/HV Adv, 3-pt-115/230 VAC-Modbus RS485+Rly	V0247MPHHJ	7548.00	V0307MPHHJ	9659.50
HK	SL750/HV Adv, 3-pt-115/230 VAC-BACnet RS-485+Rly	V0247MPHHK	7548.00	V0307MPHHK	9659.50
HL	SL750/HV Adv, 3-pt-115/230 VAC-Modbus/TCP+Rly	V0247MPHHL	7459.00	V0307MPHHL	9570.50
HM	SL750/HV Adv, 3-pt-115/230 VAC-KNX-IP+Rly	V0247MPHHM	7459.00	V0307MPHHM	9570.50
HN	SL750/HV Adv, 3-pt-115/230 VAC-BACnet/IP+Rly	V0247MPHHN	7459.00	V0307MPHHN	9570.50
7F	SL750/24 Fail-Safe, 0(2)-10VDC, 0(4)-20 mA, 3-point, on-off	V0247MPH7F	8114.50	V0307MPH7F	10226.00
7R	SL750 /HV Fail-Safe w/Relay, 0(2)-10VDC, 0(4)-20 mA, 3-point, on-off	V0247MPH7R	8677.00	V0307MPH7R	10788.50

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. Box 31, Easton, PA 18044-0031 • 4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com