

Price List Addendum

EFFECTIVE July 2, 2024



PL2024-SD-ADD1

Series FL-SC/VS2
V3202

**QUICK RESPONSE
K5.6 (8.0 SI)**

**Recessed Pendent
1" NPT (25 mm BSPT) Thread
1" IGST™ Groove**

Refer to publication 10.93.



Pendent
V3202 with
Style 108
Coupling



Pendent
V3202



Length inches	Temp. Rating		Victaulic Part Number	Price Each	Sold in Box Quantities of
	°F	°C			
IGST™ Groove with Style 108 Coupling					
CHROME PLATED					
56	155	68	A32LBCQ5F3	\$225.00	10
	200	93	A32LBFQ5F3	225.00	10
68	155	68	A32LBCQ6F3	235.00	10
	200	93	A32LBFQ6F3	235.00	10
WHITE FINISH					
56	155	68	A32LBCQ5F2	\$225.00	10
	200	93	A32LBFQ5F2	225.00	10
68	155	68	A32LBCQ6F2	235.00	10
	200	93	A32LBFQ6F2	235.00	10
Threaded Connection					
CHROME PLATED					
56	155	68	A323BCQ5F1	\$217.50	10
	200	93	A323BFQ5F1	217.50	10
68	155	68	A323BCQ6F1	227.00	10
	200	93	A323BFQ6F1	227.00	10
WHITE FINISH					
56	155	68	A323BCQ5F0	\$217.50	10
	200	93	A323BFQ5F0	217.50	10
68	155	68	A323BCQ6F0	227.00	10
	200	93	A323BFQ6F0	227.00	10

V3202 REPLACEMENT SPRINKLER HEADS – QUICK RESPONSE – PENDENT

Temp. Rating		Victaulic Part Number	Price Each	Sold in Box Quantities of
°F	°C			
CHROME PLATED				
155	68	K322BCQ42F	\$96.50	6
200	93	K322BFQ42F	96.50	6
WHITE FINISH				
155	68	K322BCQ44F	\$96.50	6
200	93	K322BFQ44F	96.50	6

V32 OPEN END WRENCH

Description	Victaulic Part Number	Price Each
V32 Open End Wrench	ST32000003	\$32.50 ^{NR}

^{NR} Non-returnable

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.



FireLock™ Sprinklers – Standard Coverage

Series FL-SC/VS2
V3201

STANDARD RESPONSE
K5.6 (8.0 SI)

Recessed Pendant
1" NPT (25mm BSPT) Thread
1" IGS™ Groove

Refer to publication 10.93.



Pendant
V3201 with
Style 108
Coupling



Pendant
V3201



Length inches	Temp. Rating		Victaulic Part Number	Price Each	Sold in Box Quantities of
	°F	°C			
IGS™ Groove with Style 108 Coupling					
CHROME PLATED					
56	155	68	A32LBCS5F3	\$223.50	10
	200	93	A32LBF55F3	223.50	10
68	155	68	A32LBCS6F3	229.00	10
	200	93	A32LBF56F3	229.00	10
WHITE FINISH					
56	155	68	A32LBCS5F2	\$223.50	10
	200	93	A32LBF55F2	223.50	10
68	155	68	A32LBCS6F2	229.00	10
	200	93	A32LBF56F2	229.00	10
Threaded Connection					
CHROME PLATED					
56	155	68	A323BCS5F1	\$216.00	10
	200	93	A323BFS5F1	216.00	10
68	155	68	A323BCS6F1	225.50	10
	200	93	A323BFS6F1	225.50	10
WHITE FINISH					
56	155	68	A323BCS5F0	\$216.00	10
	200	93	A323BFS5F0	216.00	10
68	155	68	A323BCS6F0	225.50	10
	200	93	A323BFS6F0	225.50	10

V3201 REPLACEMENT SPRINKLER HEADS – STANDARD RESPONSE – PENDENT

Temp. Rating		Victaulic Part Number	Price Each	Sold in Box Quantities of
°F	°C			
CHROME PLATED				
155	68	K322BCS42F	\$94.50	6
200	93	K322BFS42F	94.50	6
WHITE FINISH				
155	68	K322BCS44F	\$94.50	6
200	93	K322BFS44F	94.50	6

V32 OPEN END WRENCH

Description	Victaulic Part Number	Price Each
V32 Open End Wrench	ST32000003	\$32.50 ^{NR}

^{NR} Non-returnable

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

FireLock™ Sprinklers – Standard Coverage

Series FL-SC/VS2 V3204

**QUICK RESPONSE
K5.6 (8.0 SI)**

**Concealed Pendent
1" NPT (25 mm BSPT) Thread
1" IGS™ Groove**

Refer to publication 10.93.



Pendent
V3204 with
Style 108
Coupling



Pendent
V3204



Series FL-SC/VS2 V3204 is FM Approved as a Standard Response sprinkler

Length inches	Temp. Rating		Victaulic Part Number	Price Each	Sold in Box Quantities of
	°F	°C			
IGS™ Groove with Style 108 Coupling					
PLAIN BRASS					
56	155	68	A32LPCQ5F1	\$220.00	10
	200	93	A32LPFQ5F1	220.00	10
68	155	68	A32LPCQ6F1	231.00	10
	200	93	A32LPFQ6F1	231.00	10
Threaded Connection					
PLAIN BRASS					
56	155	68	A323PCQ5F0	\$213.00	10
	200	93	A323PFQ5F0	213.00	10
68	155	68	A323PCQ6F0	223.00	10
	200	93	A323PFQ6F0	223.00	10

V3204 REPLACEMENT SPRINKLER HEADS – QUICK RESPONSE – CONCEALED PENDENT

Temp. Rating		Victaulic Part Number	Price Each	Sold in Box Quantities of
°F	°C			
Brass				
155	68	K322PCQ41F	\$95.00	6
200	93	K322PFQ41F	95.00	6

SERIES VS2 COVER PLATES

Finish	135° F/57° C		165°F/74°C	
	Part Code	Price	Part Code	Price
Bright Brass	S3506A0030	\$40.00 ^{NR}	S3506D0030	\$40.00 ^{NR}
Brushed Brass	S3506A00D0	40.00 ^{NR}	S3506D00D0	40.00 ^{NR}
Chrome	S3506A0020	40.00 ^{NR}	S3506D0020	40.00 ^{NR}
Brushed Chrome	S3506A00C0	40.00 ^{NR}	S3506D00C0	40.00 ^{NR}
White	S3506A0040	40.00 ^{NR}	S3506D0040	40.00 ^{NR}
Bright White	S3506A00W0	40.00 ^{NR}	S3506D00W0	40.00 ^{NR}
Cream	S3506A00G0	40.00 ^{NR}	S3506D00G0	40.00 ^{NR}
Black	S3506A00B0	40.00 ^{NR}	S3506D00B0	40.00 ^{NR}
Custom	S3506A00_0	+	S3506D00_0	+

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

For custom finishes, contact Victaulic for details.

+ Quoted on application. Contact Victaulic for pricing and availability.

^{NR} **Non-returnable**

V32 OPEN END WRENCH

Description	Victaulic Part Number	Price Each
V32 Open End Wrench	ST32000003	\$32.50 ^{NR}

^{NR} **Non-returnable**

FireLock™ Sprinklers – Standard Coverage

Series FL-SC/VS2 V3203

**STANDARD RESPONSE
K5.6 (8.0 SI)**

**Concealed Pendent
1" NPT (25 mm BSPT) Thread
1" IGS™ Groove**

Refer to publication 10.93.



Pendent
V3203 with
Style 108
Coupling



Pendent
V3203



Length inches	Temp. Rating		Victaulic Part Number	Price Each	Sold in Box Quantities of
	°F	°C			
IGS™ Groove with Style 108 Coupling					
PLAIN BRASS					
56	155	68	A32LPCS501	\$218.50	10
	200	93	A32LPFS501	218.50	10
68	155	68	A32LPCS601	228.00	10
	200	93	A32LPFS601	228.00	10
Threaded Connection					
PLAIN BRASS					
56	155	68	A323PCS500	\$211.00	10
	200	93	A323PFS500	211.00	10
68	155	68	A323PCS600	220.50	10
	200	93	A323PFS600	220.50	10

V3203 REPLACEMENT SPRINKLER HEADS – STANDARD RESPONSE – CONCEALED PENDENT

Temp. Rating		Victaulic Part Number	Price Each	Sold in Box Quantities of
°F	°C			
Brass				
155	68	K322PCS41U	\$92.50	6
200	93	K322PFS41U	92.50	6

SERIES VS2 COVER PLATES

Finish	135° F/57° C		165°F/74°C	
	Part Code	Price	Part Code	Price
Bright Brass	S3506A0030	\$40.00 ^{NR}	S3506D0030	\$40.00 ^{NR}
Brushed Brass	S3506A00D0	40.00 ^{NR}	S3506D00D0	40.00 ^{NR}
Chrome	S3506A0020	40.00 ^{NR}	S3506D0020	40.00 ^{NR}
Brushed Chrome	S3506A00C0	40.00 ^{NR}	S3506D00C0	40.00 ^{NR}
White	S3506A0040	40.00 ^{NR}	S3506D0040	40.00 ^{NR}
Bright White	S3506A00W0	40.00 ^{NR}	S3506D00W0	40.00 ^{NR}
Cream	S3506A00G0	40.00 ^{NR}	S3506D00G0	40.00 ^{NR}
Black	S3506A00B0	40.00 ^{NR}	S3506D00B0	40.00 ^{NR}
Custom	S3506A00_0	+	S3506D00_0	+

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

For custom finishes, contact Victaulic for details.

+ Quoted on application. Contact Victaulic for pricing and availability.

^{NR} **Non-returnable**

V32 OPEN END WRENCH

Description	Victaulic Part Number	Price Each
V32 Open End Wrench	ST32000003	\$32.50 ^{NR}

^{NR} **Non-returnable**

TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. Box 31, Easton, PA 18044-0031 • 4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com