

Price List Addendum

EFFECTIVE July 25, 2025

PGS-300 Grooved End Fittings

PGS-300 Expansion Joint for
Potable Water Applications



STYLE 355P

Refer to publication 33.05

STYLE 355P – PGS-300 EXPANSION JOINT FOR POTABLE WATER APPLICATIONS

Nominal Size	Rated Movement				Approx. Wgt. Ea.	COUPLING COMPLETE with Grade "P" Gasket and Carbon Steel Bolts & Nuts	COUPLING COMPLETE with Grade "P" Gasket and Coated* Carbon Steel Bolts & Nuts	COUPLING COMPLETE with Grade "P" Gasket and Stainless Steel Bolts & Nuts
		Length						
		Compressed	Neutral	Expanded				
inches						Price Each		
lb						Painted		
2	0.35	9.17 ± 0.07	9.41 ± 0.08	9.69 ± 0.06	3.5	\$3401.00	+	+
	0.75	12.34 ± 0.12	12.83 ± 0.14	13.37 ± 0.11	6.6	3570.00	+	+
	1.15	15.51 ± 0.17	16.24 ± 0.21	17.06 ± 0.15	9.6	3739.00	+	+
	1.55	18.68 ± 0.22	19.66 ± 0.27	20.75 ± 0.19	12.7	3907.00	+	+
	1.95	21.86 ± 0.28	23.07 ± 0.33	24.44 ± 0.24	15.7	4074.50	+	+
	2.35	25.03 ± 0.33	26.48 ± 0.39	28.12 ± 0.28	18.8	4242.00	+	+
	2.75	28.20 ± 0.38	29.90 ± 0.45	31.81 ± 0.32	21.8	4411.00	+	+
	3.15	31.37 ± 0.43	33.31 ± 0.52	35.50 ± 0.36	24.9	4578.50	+	+
	3.55	34.54 ± 0.48	36.73 ± 0.58	39.18 ± 0.41	28.0	4749.00	+	+
	3.95	37.71 ± 0.53	40.14 ± 0.64	42.87 ± 0.45	31.0	4915.00	+	+
	4.35	40.88 ± 0.58	43.55 ± 0.70	46.56 ± 0.49	34.1	5083.50	+	+
2½	0.35	9.17 ± 0.07	9.38 ± 0.08	9.62 ± 0.06	4.2	3486.00	+	+
	0.75	12.34 ± 0.12	12.76 ± 0.14	13.23 ± 0.11	7.6	3674.50	+	+
	1.15	15.51 ± 0.17	16.14 ± 0.21	16.85 ± 0.15	11.0	3863.50	+	+
	1.55	18.68 ± 0.22	19.52 ± 0.27	20.47 ± 0.19	14.4	4053.00	+	+
	1.95	21.86 ± 0.28	22.90 ± 0.33	24.09 ± 0.24	17.8	4240.50	+	+
	2.35	25.03 ± 0.33	26.27 ± 0.39	27.70 ± 0.28	21.2	4429.50	+	+
	2.75	28.20 ± 0.38	29.65 ± 0.45	31.32 ± 0.32	24.7	4618.00	+	+
	3.15	31.37 ± 0.43	33.03 ± 0.52	34.94 ± 0.36	28.1	4808.00	+	+
	3.55	34.54 ± 0.48	36.41 ± 0.58	38.55 ± 0.41	31.5	4995.50	+	+
	3.95	37.71 ± 0.53	39.79 ± 0.64	42.17 ± 0.45	34.9	5187.00	+	+
	4.35	40.88 ± 0.58	43.17 ± 0.70	45.79 ± 0.49	38.3	5373.50	+	+
3	0.35	9.17 ± 0.07	9.41 ± 0.08	9.69 ± 0.06	5.3	3583.50	+	+
	0.75	12.34 ± 0.12	12.83 ± 0.14	13.37 ± 0.11	9.7	3822.50	+	+
	1.15	15.51 ± 0.17	16.24 ± 0.21	17.06 ± 0.15	14.1	4062.00	+	+
	1.55	18.68 ± 0.22	19.66 ± 0.27	20.75 ± 0.19	18.4	4300.00	+	+
	1.95	21.86 ± 0.28	23.07 ± 0.33	24.44 ± 0.24	22.8	4538.50	+	+
	2.35	25.03 ± 0.33	26.48 ± 0.39	28.12 ± 0.28	27.1	4778.50	+	+
	2.75	28.20 ± 0.38	29.90 ± 0.45	31.81 ± 0.32	31.5	5016.50	+	+
	3.15	31.37 ± 0.43	33.31 ± 0.52	35.50 ± 0.36	35.8	5254.50	+	+
	3.55	34.54 ± 0.48	36.73 ± 0.58	39.18 ± 0.41	40.2	5494.00	+	+
	3.95	37.71 ± 0.53	40.14 ± 0.64	42.87 ± 0.45	44.6	5732.50	+	+
	4.35	40.88 ± 0.58	43.55 ± 0.70	46.56 ± 0.49	48.9	5970.50	+	+
3	4.75	44.05 ± 0.63	46.97 ± 0.76	50.24 ± 0.54	53.3	6206.00	+	+

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

+ Quoted on application. Contact Victaulic for pricing and availability.

* Fluoropolymer top coat. See publication 33.05 for more information.

PGS-300 Expansion Joint for Potable Water Applications

STYLE 355P

Refer to publication 33.05



STYLE 355P – PGS-300 EXPANSION JOINT FOR POTABLE WATER APPLICATIONS

Nominal Size	Rated Movement				Approx. Wgt. Ea.	COUPLING COMPLETE with Grade “P” Gasket and Carbon Steel Bolts & Nuts	COUPLING COMPLETE with Grade “P” Gasket and Coated* Carbon Steel Bolts & Nuts	COUPLING COMPLETE with Grade “P” Gasket and Stainless Steel Bolts & Nuts
		Length						
		Compressed	Neutral	Expanded				
inches					lb	Price Each		
						Painted		
4	0.35	11.22 ± 0.07	11.46 ± 0.08	11.74 ± 0.06	8.3	\$4046.00	+	+
	0.75	14.44 ± 0.12	14.92 ± 0.14	15.47 ± 0.11	14.6	4326.50	+	+
	1.15	17.66 ± 0.17	18.39 ± 0.21	19.21 ± 0.15	20.9	4607.50	+	+
	1.55	20.88 ± 0.22	21.85 ± 0.27	22.94 ± 0.19	27.2	4888.50	+	+
	1.95	24.10 ± 0.28	25.31 ± 0.33	26.68 ± 0.24	33.5	5171.50	+	+
	2.35	27.31 ± 0.33	28.77 ± 0.39	30.41 ± 0.28	39.9	5452.00	+	+
	2.75	30.53 ± 0.38	32.23 ± 0.45	34.15 ± 0.32	46.2	5732.50	+	+
	3.15	33.75 ± 0.43	35.70 ± 0.52	37.88 ± 0.36	52.5	6014.00	+	+
	3.55	36.97 ± 0.48	39.16 ± 0.58	41.62 ± 0.41	58.8	6295.00	+	+
	3.95	40.19 ± 0.53	42.62 ± 0.64	45.35 ± 0.45	65.2	6574.50	+	+
	4.35	43.41 ± 0.58	46.08 ± 0.70	49.09 ± 0.49	71.5	6855.00	+	+
4.75	46.63 ± 0.63	49.54 ± 0.76	52.82 ± 0.54	77.8	7137.50	+	+	
6	0.35	13.22 ± 0.08	13.47 ± 0.08	13.74 ± 0.06	14.2	5531.50	+	+
	0.75	16.45 ± 0.13	16.93 ± 0.14	17.47 ± 0.11	23.8	5937.00	+	+
	1.15	19.67 ± 0.19	20.40 ± 0.21	21.21 ± 0.15	33.4	6339.00	+	+
	1.55	22.89 ± 0.24	23.86 ± 0.27	24.94 ± 0.19	43.0	6743.00	+	+
	1.95	26.12 ± 0.30	27.33 ± 0.33	28.68 ± 0.24	52.6	7147.50	+	+
	2.35	29.34 ± 0.35	30.80 ± 0.39	32.41 ± 0.28	62.2	7551.00	+	+
	2.75	32.56 ± 0.41	34.26 ± 0.45	36.15 ± 0.32	71.8	7956.00	+	+
	3.15	35.78 ± 0.46	37.73 ± 0.52	39.88 ± 0.36	81.4	8359.00	+	+
	3.55	39.01 ± 0.52	41.19 ± 0.58	43.62 ± 0.41	91.0	8762.50	+	+
	3.95	42.23 ± 0.57	44.66 ± 0.64	47.35 ± 0.45	100.6	9165.50	+	+
	4.35	45.45 ± 0.62	48.13 ± 0.70	51.09 ± 0.49	110.2	9465.50	+	+
4.75	48.68 ± 0.68	51.59 ± 0.76	54.82 ± 0.54	119.8	9972.00	+	+	
8	0.35	13.23 ± 0.08	13.47 ± 0.08	13.74 ± 0.06	26.4	6720.50	+	+
	0.75	16.46 ± 0.13	16.95 ± 0.14	17.49 ± 0.11	45.9	7344.50	+	+
	1.15	19.69 ± 0.19	20.42 ± 0.21	21.23 ± 0.15	65.4	7970.00	+	+
	1.55	22.92 ± 0.24	23.90 ± 0.27	24.97 ± 0.19	84.9	8591.50	+	+
	1.95	26.16 ± 0.30	27.37 ± 0.33	28.72 ± 0.24	104.4	9214.50	+	+
	2.35	29.39 ± 0.35	30.84 ± 0.39	32.46 ± 0.28	123.9	9837.00	+	+
	2.75	32.62 ± 0.41	34.32 ± 0.45	36.20 ± 0.32	143.4	10460.00	+	+
	3.15	35.85 ± 0.46	37.79 ± 0.52	39.94 ± 0.36	162.8	11085.50	+	+
	3.55	39.08 ± 0.52	41.27 ± 0.58	43.69 ± 0.41	182.3	11708.50	+	+
	3.95	42.31 ± 0.57	44.74 ± 0.64	47.43 ± 0.45	201.8	12332.00	+	+
	4.35	45.54 ± 0.62	48.21 ± 0.70	51.17 ± 0.49	221.3	12956.50	+	+
4.75	48.77 ± 0.68	51.69 ± 0.76	54.92 ± 0.54	240.8	13577.50	+	+	

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

+ Quoted on application. Contact Victaulic for pricing and availability.

* Fluoropolymer top coat. See publication 33.05 for more information.

PGS-300 Expansion Joint for Potable Water Applications

STYLE 355P

Refer to publication 33.05



STYLE 355 – PGS-300 EXPANSION JOINT FOR POTABLE WATER APPLICATIONS

Nominal Size	Rated Movement				Approx. Wgt. Ea.	COUPLING COMPLETE with Grade "P" Gasket and Carbon Steel Bolts & Nuts	COUPLING COMPLETE with Grade "P" Gasket and Coated* Carbon Steel Bolts & Nuts	COUPLING COMPLETE with Grade "P" Gasket and Stainless Steel Bolts & Nuts
		Length						
		Compressed	Neutral	Expanded				
inches					lb	Painted		
10	0.35	13.23 ± 0.08	13.47 ± 0.08	13.74 ± 0.06	36.0	\$7849.50	+	+
	0.75	16.46 ± 0.13	16.95 ± 0.14	17.49 ± 0.11	61.7	8867.00	+	+
	1.15	19.69 ± 0.19	20.42 ± 0.21	21.23 ± 0.15	87.3	9884.00	+	+
	1.55	22.92 ± 0.24	23.90 ± 0.27	24.97 ± 0.19	113.0	10903.00	+	+
	1.95	26.16 ± 0.30	27.37 ± 0.33	28.72 ± 0.24	138.7	11922.00	+	+
	2.35	29.39 ± 0.35	30.84 ± 0.39	32.46 ± 0.28	164.3	12940.50	+	+
	2.75	32.62 ± 0.41	34.32 ± 0.45	36.20 ± 0.32	190.0	13813.50	+	+
	3.15	35.85 ± 0.46	37.79 ± 0.52	39.94 ± 0.36	215.7	14975.50	+	+
	3.55	39.08 ± 0.52	41.27 ± 0.58	43.69 ± 0.41	241.3	15995.00	+	+
	3.95	42.31 ± 0.57	44.74 ± 0.64	47.43 ± 0.45	267.0	17014.00	+	+
	4.35	45.54 ± 0.62	48.21 ± 0.70	51.17 ± 0.49	292.7	18032.00	+	+
4.75	48.77 ± 0.68	51.69 ± 0.76	54.92 ± 0.54	318.4	19049.50	+	+	
12	0.35	13.23 ± 0.08	13.47 ± 0.08	13.74 ± 0.06	43.5	8526.50	+	+
	0.75	16.46 ± 0.13	16.95 ± 0.14	17.49 ± 0.11	72.7	9727.00	+	+
	1.15	19.69 ± 0.19	20.42 ± 0.21	21.23 ± 0.15	102.0	10928.50	+	+
	1.55	22.92 ± 0.24	23.90 ± 0.27	24.97 ± 0.19	131.2	12130.00	+	+
	1.95	26.16 ± 0.30	27.37 ± 0.33	28.72 ± 0.24	160.5	13330.50	+	+
	2.35	29.39 ± 0.35	30.84 ± 0.39	32.46 ± 0.28	189.7	14532.50	+	+
	2.75	32.62 ± 0.41	34.32 ± 0.45	36.20 ± 0.32	218.9	15733.50	+	+
	3.15	35.85 ± 0.46	37.79 ± 0.52	39.94 ± 0.36	248.2	16933.50	+	+
	3.55	39.08 ± 0.52	41.27 ± 0.58	43.69 ± 0.41	277.4	18136.00	+	+
	3.95	42.31 ± 0.57	44.74 ± 0.64	47.43 ± 0.45	306.7	19337.00	+	+
	4.35	45.54 ± 0.62	48.21 ± 0.70	51.17 ± 0.49	335.9	20538.00	+	+
	4.75	48.77 ± 0.68	51.69 ± 0.76	54.92 ± 0.54	365.2	21703.50	+	+

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

+ Quoted on application. Contact Victaulic for pricing and availability.

* Fluoropolymer top coat. See publication 33.05 for more information.

Products for CPVC/PVC Pipe

C

E

A

N

355

H

P

Z

Class	Size In./DN	Movement	Length	Style	Finish	Gasket	Bolts and Nuts
C	E - 2/50 F - 2 1/2 H - 3/80 J - 4/100 M - 6/150 O - 8/200 P - 10/250 Q - 12/300	A - 0.35 B - 0.75 C - 1.15 D - 1.55 E - 1.95 F - 2.35 G - 2.75 H - 3.15 I - 3.55 J - 3.95 K - 4.35 L - 4.75	C - Compressed N - Neutral E - Expanded	355P	H - Blue Enamel	P - Fluoroelastomer Blend	Z - Plated X - Stainless Steel B - Fluoropolymer Coated

TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. Box 31, Easton, PA 18044-0031 • 4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com

