

Price List Addendum

EFFECTIVE September 16, 2025

Fire Protection Valves and Devices

Universal Manifold Check Assembly

SERIES UMC

with Auto Test Switch
Refer to publication 30.72.



SERIES UMC – UNIVERSAL MANIFOLD CHECK ASSEMBLY WITH AUTO TEST SWITCH

UMC Body Size			
Nominal inches	Description	Part Code	Price Each
1¼	GxG UMC Right Handed with Control Valve	S012UMCRVA	\$4772.00
	GxG UMC Right Handed with Hose	S012UMCR0A	4487.50
	GxG UMC Left Handed with Control Valve	S012UMCLVA	4772.00
	GxG UMC Left Handed with Hose	S012UMCL0A	4487.50
1½	GxG UMC Right Handed with Control Valve	S014UMCRVA	4889.00
	GxG UMC Right Handed with Hose	S014UMCR0A	4558.50
	GxG UMC Left Handed with Control Valve	S014UMCLVA	4889.00
	GxG UMC Left Handed with Hose	S014UMCL0A	4558.50
2	GxG UMC Right Handed with Control Valve	S020UMCRVA	4658.00
	GxG UMC Right Handed with Hose	S020UMCR0A	4280.00
	GxG UMC Left Handed with Control Valve	S020UMCLVA	4658.00
	GxG UMC Left Handed with Hose	S020UMCL0A	4280.00
2½	GxG UMC Right Handed with Control Valve	S024UMCRVA	4787.50
	GxG UMC Right Handed with Hose	S024UMCR0A	4413.50
	GxG UMC Left Handed with Control Valve	S024UMCLVA	4787.50
	GxG UMC Left Handed with Hose	S024UMCL0A	4413.50
3	GxG UMC Right Handed with Control Valve	S030UMCRVA	4766.00
	GxG UMC Right Handed with Hose	S030UMCR0A	4420.00
	GxG UMC Left Handed with Control Valve	S030UMCLVA	4766.00
	GxG UMC Left Handed with Hose	S030UMCL0A	4420.00
4	GxG UMC Right Handed with Control Valve	S040UMCRVA	5499.00
	GxG UMC Right Handed with Hose	S040UMCR0A	5168.50
	GxG UMC Left Handed with Control Valve	S040UMCLVA	5499.00
	GxG UMC Left Handed with Hose	S040UMCL0A	5168.50
6	GxG UMC Right Handed with Control Valve	S060UMCRVA	6106.00
	GxG UMC Right Handed with Hose	S060UMCR0A	5586.00
	GxG UMC Left Handed with Control Valve	S060UMCLVA	6106.00
	GxG UMC Left Handed with Hose	S060UMCL0A	5586.00
8	GxG UMC Right Handed with Control Valve	S080UMCRVA	8090.00
	GxG UMC Right Handed with Hose	S080UMCR0A	6942.00

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

Universal Manifold Assembly

SERIES UM

with Auto Test Switch

Refer to publication 30.71.



SERIES UM – UNIVERSAL MANIFOLD ASSEMBLY WITH AUTO TEST SWITCH

UM Body Size			
Nominal inches	Description	Part Code	Price Each
1¼	GxG UM with Hose	S0120UM00A	\$3976.00
	GxG UM with Control Valve and Hose	S0120UMV0A	4463.50
1½	GxG UM with Hose	S0140UM00A	3982.50
	GxG UM with Control Valve and Hose	S0140UMV0A	4570.00
2	GxG UM with Hose	S0200UM00A	4027.00
	GxG UM with Control Valve and Hose	S0200UMV0A	4506.50
2½	GxG UM with Hose	S0240UM00A	4173.50
	GxG UM with Control Valve and Hose	S0240UMV0A	4731.50
3	GxG UM with Hose	S0300UM00A	4242.00
	GxG UM with Control Valve and Hose	S0300UMV0A	4798.50
4	GxG UM with Hose	S0400UM00A	4580.50
	GxG UM with Control Valve with Hose	S0400UMV0A	5195.50
6	GxG UM with Hose	S0600UM00A	4691.50
	GxG UM with Control Valve with Hose	S0600UMV0A	5258.50
8	GxG UM with Hose	S0800UM00A	5438.50
	GxG UM with Control Valve with Hose	S0800UMV0A	6594.00

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

Fire Protection Valves and Devices

UM/UMC REPLACEMENT VSR AUTO TEST FLOW SWITCHES

Body Size			
Nominal inches	Description	Part Code	Price Each
1¼ – 2	VSR-AT Switch with Gasket and Adapter for 1¼ – 2" UM and UMC	S020UMCPTA	\$3142.00
2½	VSR-AT Flow Switch with Gasket and Adapter for 2½" UM and UMC	S024UMCPTA	3142.00
3	VSR-AT Flow Switch with Gasket and Adapter for 3" UM and UMC	S030UMCPTA	3142.00
4	VSR-AT Flow Switch with Gasket and Adapter for 4" UM and UMC	S040UMCKA4	3142.00
6	VSR-AT Flow Switch with Gasket and Adapter for 6" UM and UMC	S060UMCKA6	3142.00
8	VSR-AT Flow Switch with Gasket and Adapter for 8" UM and UMC	S080UMCPTA	3142.00

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. Box 31, Easton, PA 18044-0031 • 4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com