

Price List Addendum

EFFECTIVE March 1, 2025

Cut Grooving Tools

Notice: When ordering a cut grooving tool, please specify standard steel or ductile iron (rigid or flexible).

CG336 Portable Cut Grooving Tool



The CG336 is the industry's first field tool to cut and groove AWWA ductile iron pipe from 3 – 36".

Capacities: 3 – 36" AWWA ductile iron pipe.

NOTE: Specifically designed for field closure pieces.

Tool Model	Part Number	Tool Weight/ Shipping Weight lb	Rental Per Month	List Price
CG336 Base Kit	R052336KIT	-/292	\$4977.50	\$75842.50
CG336 Pipe Size Kit 3 – 12"	R062336KIT	305/470	1988.00	30580.50
CG336 Pipe Size Kit 14 – 18"	R072336KIT	334/461	1784.50	27451.50
CG336 Pipe Size Kit 20 – 24"	R082336KIT	425/702	2239.00	34116.50
CG336 Pipe Size Kit 30 – 36"	R092336KIT	507/787	3754.50	57208.00
CG336 Complete Kit	R000336KIT	-/2712	14742.50	168898.50

For tool rating capacity please reference publication 24.25.

CG336 ACCESSORIES

Tool Accessories	Part Number	Weight lb	Rental Per Month	List Price
Optional Platform	R195336ASY	169	\$442.50	\$2664.00

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

CG336 PARTS

Tool Components	Sold Only in Box Quantities of	Pipe Size Tool Bit Marking inches	Part Number	Purchase Price Each
Tool Bits	10	3 – 6	RK00T30POP	\$290.00
		8 – 12	RK00T30P1P	303.50
		14 – 24	RK00T30P2P	373.00
		30 – 36	RK00T30P3P	392.00
Tool Holder	1	3 – 6	R015T30MCP	1394.50
		8 – 12	R017T30MCP	1394.50
		14 – 24	R021T30MCP	1394.50
		30 – 36	R023T30MCP	1394.50
Cutoff Blade	1	-	R046336MCH	303.50

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. Box 31, Easton, PA 18044-0031 • 4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com