

# Price List Addendum

EFFECTIVE March 1, 2025



PL2025-GEN-ADD1

## Roll Grooving Tools – Field Portable

### RG2300



The RG2300 is a combo roll grooving tool that can be used manually in-air or mounted to a power drive for increased productivity. This tool provides 1 to 12 inches of grooving capacity in a compact, lightweight package well suited for field use. The available tool configurations are listed below.

Tool Model, Roll Package and Grooving Capability	Part Number	Shipping Weight lb	Tool List Price
RG2300 Roll Grooving Tool and Fire Protection Roll Package (See table below for package contents)	R0102300ZR	56.0	\$3000.00
RG2300 Roll Grooving Tool and Carbon Steel/Stainless Steel OGS Roll Package (See table below for package contents)	R010230AZR	53.1	3000.00
RG2300 Roll Grooving Tool and Light Wall Stainless Steel Roll Package (See table below for package contents)	R010230XZR	49.0	3000.00
RG2300 Roll Grooving Tool and Copper Roll Package (See table below for package contents)	R010230RZR	48.5	3000.00

**For tool rating capacity please reference publication 24.24.**

All tools come with a RIDGID 300 Power Drive Adapter

**RG2300 GROOVING ROLL PACKAGES \***

Roll Package and Grooving Capability	Part Number	Pipe Size Range inches   DN	Purchase List Price Each Set
Fire Protection Roll Package: – Carbon Steel (Sch. 5 – 40) : 1" IGS™ – Carbon Steel (Sch. 5 – 40) / Stainless Steel (Sch. 40S) : 1¼ – 4" – Carbon Steel (Sch. 5 – 40) : 5 – 6" – Carbon Steel (Sch. 5 – 20) : 8" – Carbon Steel (Sch. 5 – 10) : 10 – 12"	R901230001	1 – 12/DN25 – DN300	\$1600.00
Carbon Steel/Stainless Steel OGS Roll Package: – Carbon Steel (Sch. 5 – 40) / Stainless Steel (Sch. 40S) : 1 – 4" – Carbon Steel (Sch. 5 – 40) : 5 – 6" – Carbon Steel (Sch. 5 – 20) : 8" – Carbon Steel (Sch. 5 – 10) : 10 – 12"	R901230012	1 – 12/DN25 – DN300	1333.50
Lt. Wall Stainless Steel RX Roll Package: – Lt. Wall Stainless Steel RX (Sch. 5S – 10S) : 2 – 12"	RX02230012	2 – 12/DN50 – DN300	1333.50
Copper Roll Package: – Copper (Types K, L, M, DWV) : 2 – 8"	RR02230P08	2 – 8/DN50 – DN200	1333.50
PVC and Aluminum RP Roll Package: – PVC (Sch. 40) : 2", 8" – PVC (Sch. 40 – 80) : 2½ – 6" – Aluminum (Sch. 5 – 40) : 2 – 8"	RP02230P08	2 – 8/DN50 – DN200	1333.50

**NOTE:** Roll sets for the RG2300 are not compatible with other roll grooving tools.

\* Refer to How to Order at the end of this section.

Please reference publication 24.24 for pipe wall thickness and tool capacity ratings.

**NOTE: Items listed in shaded areas are non-cancellable and non-returnable.**



## Pipe Preparation Tools

### RG2300 GROOVING ROLLS\*

Grooving Capability	Part Number	Pipe Size Range inches   DN	Purchase List Price Each Set
Carbon Steel (Sch. 10 – 40) : 1" IGS™	RI01230201	1/DN25	\$440.50
Carbon Steel (Sch. 5 – 40) / Stainless Steel (Sch. 40S) : 1 – 4"	R901230201	1 – 1½/DN25 – DN40	451.00
Carbon Steel (Sch. 5 – 40) : 5 – 6"	R90A230201	1¼ – 1½/DN32 – DN40	451.00
Carbon Steel (Sch. 5 – 20) : 8"	R902230206	2 – 6/DN50 – DN150	515.50
Carbon Steel (Sch. 5 – 10) : 10 – 12"	R908230212	8 – 12/DN200 – DN300	519.00
Lt. Wall Stainless Steel RX (Sch. 5S – 10S)	RX02230006	2 – 6/DN50 – DN150	757.00
	RX08230012	8 – 12/DN200 – DN300	757.00
Copper (Types K, L, M, DWV)	RR02230006	2 – 6/DN50 – DN150	757.00
	RR08230008	8/DN200	757.00
PVC (Sch. 40) : 2", 8" PVC (Sch. 40 – 80) : 2½ – 6" Aluminum (Sch. 5 – 40) : 2 – 6" Aluminum (Sch. 5 – 20) : 8"	RP02230006	2 – 6/DN50 – DN150	757.00
	RP08230008	8/DN200	757.00

For tool rating capacity please reference publication 24.24.

**NOTE: Items listed in shaded areas are non-cancellable and non-returnable.**

### RG2300 ADAPTERS

Description	Part Number	List Price
RG2300 Power Drive Adapter for REMS	R001230PDA	\$74.50
RG2300 Power Drive Adapter and Shaft for RIDGID 300 Compact	R002230PDA	332.00

**NOTE: Items listed in shaded areas are non-cancellable and non-returnable.**

### TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. Box 31, Easton, PA 18044-0031 • 4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com