

Price List Addendum

EFFECTIVE March 19, 2025

Tool Accessories

VAPS112



Adjustable Pipe Stands are portable and self-standing units. Turnstile design allows pipe to be spun around for grooving of both pipe ends without dismounting pipe from stand. Unique trough design allows for rotational and forward/traverse movement. They are designed for direct use with roll grooving tools: VE272SFS, VE268, VE270FSD.

Capacities: $\frac{3}{4}$ – 12"/20 – 300 mm IPS pipe †

Load Rating: 1075 lbs

Vertical Stroke: 10 $\frac{3}{4}$ "/273.1 mm

Min. Pipe Height from Floor: 23 $\frac{1}{4}$ "/590.6 mm on $\frac{3}{4}$ "/19.1 mm pipe

Handle Effort Required to Raise 1075 lbs Load: 50 lbs Max.

Tool Model	Part Number	Tool Weight/ Shipping Weight lb	Rental Per Month	Tool List Price
VAPS 112	R000112PS0	190/220	\$1595.50	\$12529.50

† Indicates pipe size capacity. For wall thickness capacity and general tool ratings see separate Tool Rating Data in publication 24.01.

TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. Box 31, Easton, PA 18044-0031 • 4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com