

# Price List Addendum

EFFECTIVE May 12, 2025

## Fire Protection Valves and Devices

### Universal Manifold Check Assembly

#### SERIES UMC

with Auto Test Switch  
Refer to publication 30.72.



#### SERIES UMC – UNIVERSAL MANIFOLD CHECK ASSEMBLY WITH AUTO TEST SWITCH

UMC Body Size			
Nominal inches	Description	Part Code	Price Each
1¼	GxG UMC Right Handed with Control Valve	S012UMCRVA	\$4480.50
	GxG UMC Right Handed with Hose	S012UMCR0A	4213.50
	GxG UMC Left Handed with Control Valve	S012UMCLVA	4480.50
	GxG UMC Left Handed with Hose	S012UMCL0A	4213.50
1½	GxG UMC Right Handed with Control Valve	S014UMCRVA	4590.50
	GxG UMC Right Handed with Hose	S014UMCR0A	4280.00
	GxG UMC Left Handed with Control Valve	S014UMCLVA	4590.50
	GxG UMC Left Handed with Hose	S014UMCL0A	4280.00
2	GxG UMC Right Handed with Control Valve	S020UMCRVA	4373.50
	GxG UMC Right Handed with Hose	S020UMCR0A	4018.50
	GxG UMC Left Handed with Control Valve	S020UMCLVA	4373.50
	GxG UMC Left Handed with Hose	S020UMCL0A	4018.50
2½	GxG UMC Right Handed with Control Valve	S024UMCRVA	4495.00
	GxG UMC Right Handed with Hose	S024UMCR0A	4144.00
	GxG UMC Left Handed with Control Valve	S024UMCLVA	4495.00
	GxG UMC Left Handed with Hose	S024UMCL0A	4144.00
3	GxG UMC Right Handed with Control Valve	S030UMCRVA	4475.00
	GxG UMC Right Handed with Hose	S030UMCR0A	4150.00
	GxG UMC Left Handed with Control Valve	S030UMCLVA	4475.00
	GxG UMC Left Handed with Hose	S030UMCL0A	4150.00
4	GxG UMC Right Handed with Control Valve	S040UMCRVA	5163.00
	GxG UMC Right Handed with Hose	S040UMCR0A	4853.00
	GxG UMC Left Handed with Control Valve	S040UMCLVA	5163.00
	GxG UMC Left Handed with Hose	S040UMCL0A	4853.00
6	GxG UMC Right Handed with Control Valve	S060UMCRVA	5733.00
	GxG UMC Right Handed with Hose	S060UMCR0A	5245.00
	GxG UMC Left Handed with Control Valve	S060UMCLVA	5733.00
	GxG UMC Left Handed with Hose	S060UMCL0A	5245.00
8	GxG UMC Right Handed with Control Valve	S080UMCRVA	7596.00
	GxG UMC Right Handed with Hose	S080UMCR0A	6518.00

**NOTE:** Items listed in shaded areas are non-cancellable and non-returnable.

Universal Manifold Assembly

SERIES UM

with Auto Test Switch

Refer to publication 30.71.



SERIES UM – UNIVERSAL MANIFOLD ASSEMBLY WITH AUTO TEST SWITCH

UM Body Size			
Nominal inches	Description	Part Code	Price Each
1¼	GxG UM with Hose	S0120UM00A	\$3733.00
	GxG UM with Control Valve and Hose	S0120UMV0A	4191.00
1½	GxG UM with Hose	S0140UM00A	3739.00
	GxG UM with Control Valve and Hose	S0140UMV0A	4291.00
2	GxG UM with Hose	S0200UM00A	3781.00
	GxG UM with Control Valve and Hose	S0200UMV0A	4231.00
2½	GxG UM with Hose	S0240UM00A	3918.50
	GxG UM with Control Valve and Hose	S0240UMV0A	4442.50
3	GxG UM with Hose	S0300UM00A	3983.00
	GxG UM with Control Valve and Hose	S0300UMV0A	4505.50
4	GxG UM with Hose	S0400UM00A	4300.50
	GxG UM with Control Valve with Hose	S0400UMV0A	4878.00
6	GxG UM with Hose	S0600UM00A	4405.00
	GxG UM with Control Valve with Hose	S0600UMV0A	4937.50
8	GxG UM with Hose	S0800UM00A	5106.50
	GxG UM with Control Valve with Hose	S0800UMV0A	6191.50

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

## Fire Protection Valves and Devices

### UM/UMC REPLACEMENT VSR AUTO TEST FLOW SWITCHES

Body Size			
Nominal inches	Description	Part Code	Price Each
2	VSR-AT Switch with Gasket and Adapter for 2" UM and UMC	S020UMCPTA	2950.00
2½	VSR-AT Flow Switch with Gasket and Adapter for 2½" UM and UMC	S024UMCPTA	2950.00
3	VSR-AT Flow Switch with Gasket and Adapter for 3" UM and UMC	S030UMCPTA	2950.00
4	VSR-AT Flow Switch with Gasket and Adapter for 4" UM and UMC	S040UMCKA4	2950.00
6	VSR-AT Flow Switch with Gasket and Adapter for 6" UM and UMC	S060UMCKA6	2950.00
8	VSR-AT Flow Switch with Gasket and Adapter for 8" UM and UMC	S080UMCPTA	2950.00

**NOTE:** Items listed in shaded areas are non-cancellable and non-returnable.

### TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. Box 31, Easton, PA 18044-0031 • 4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • [pickvic@victaulic.com](mailto:pickvic@victaulic.com)