

Price List Addendum

EFFECTIVE March 9, 2026

Standard AWWA Couplings

Vic-Flange Adapter

STYLE 341

Refer to publication 23.04.



STYLE 341 – GRADE “S” OR “M” GASKET

PIPE Inches		Approx. Wgt. Each lb	Vic-Flange Adapter Complete with Grade “S” or “M” Gasket †
Nominal Size	Outside Diameter		Price Each Tnemec 37H-77
STYLE 341 - Hinged			
3	3.96	5.4	\$721.00
4	4.80	8.2	802.50
6	6.90	12.0	1051.50
8	9.05	17.4	1326.50
10	11.10	24.6	1939.00
12	13.20	34.4	2517.50
STYLE 341 - Four Piece			
14	15.30	61.0	\$5108.50
16	17.40	80.0	5907.00
18	19.50	98.8	7248.00
20	21.60	113.9	8717.50
24	25.80	134.9	11156.50
30	32.00	225.0	11252.50
36	38.30	320.0	12154.00

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

Vic-Flange adapters sizes 4 – 12” are UL Listed/FM Approved for underground fire protection water supply systems.

† Surcharge for couplings supplied without gasket. Contact Victaulic for pricing.

Flange Parts

FOR STYLE 341 VIC-FLANGE ADAPTERS

FOR STYLE 341 VIC-FLANGE ADAPTERS

PIPE Inches	Flange Washers	“S” or “M” Gasket
Nominal Size	Price Each	Price Each
STYLE 341 - Hinged		
3	\$313.00 ^{NR}	\$176.50
4	363.50 ^{NR}	176.50 ^{NR}
6	499.00 ^{NR}	195.00 ^{NR}
8	627.00 ^{NR}	223.00 ^{NR}
10	866.00 ^{NR}	254.50 ^{NR}
12	1262.50 ^{NR}	301.00 ^{NR}
STYLE 341 - Four Piece		
14	\$1375.00 ^{NR}	\$337.50 ^{NR}
16	2438.00 ^{NR}	364.00 ^{NR}
18	2601.00 ^{NR}	512.50
20	+	551.50 ^{NR}
24	+	610.50 ^{NR}
30	+	2416.50
36	+	2934.50

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

+ Quoted on application. Contact Victaulic for pricing and availability.

^{NR} Non-returnable

TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com