

Price List Addendum

EFFECTIVE April 20, 2026



PL2026-GEN-ADD12

Stainless Steel and Duplex Couplings

AGS Stainless Steel Flexible Coupling

STYLE W77S

Refer to publication 20.31



STYLE W77S – GRADE “E” OR “T” GASKET

PIPE inches		Approx. Wgt. Each	Price Each	STAINLESS STEEL BOLT & NUT	
Nominal Size	Outside Diameter	lb	COUPLING COMPLETE † With Grade “E” or “T” Gasket	No.	Size § inches
14	14.000	65.0	\$8521.50	2	1 ¹ / ₈ x 5 ¹ / ₂
16	16.000	80.0	12851.50	2	1 ¹ / ₈ x 5 ¹ / ₂
18	18.000	93.0	12974.50	2	1 ¹ / ₈ x 5 ¹ / ₂
20	20.000	114.0	14921.00	2	1 ¹ / ₈ x 5 ¹ / ₂
24	24.000	181.2	16712.00	2	1 ¹ / ₈ x 5 ¹ / ₂

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

† Surcharge for couplings supplied without gasket. Contact Victaulic for pricing.

§ Metric thread size bolts available. Contact Victaulic.

TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com

