

Price List Addendum

EFFECTIVE June 22, 2026

Stainless Steel Valves for Grooved IPS SS Pipe

Vic-300 MasterSeal™
Stainless Steel Butterfly Valve

SERIES 461

Refer to publication 1740



	2" (020)	2½" (024)	3" (030)	4" (040)	5" (050)	6" (060)	8" (080)	10" (100)	12" (120)
BARE VALVE									
EPDM (E) or Nitrile (T) Seat V - XXX - 461 - X - E - 0	\$1731.00	\$2255.50	\$2382.00	\$2954.00	\$5605.00	\$5963.50	\$7938.50	\$16074.00	\$18160.50
Fluoroelastomer (CHP) Seat V - XXX - 461 - X - O - 0	2077.50	2793.00	2858.00	3545.50	6727.50	7156.50	9526.50	19287.50	21792.00
PRICE OF VALVE COMPLETE WITH OPERATOR									
10-POSITION OPERATOR – ZINC PLATED									
EPDM (E) or Nitrile (T) Seat 10-Position Handle with Memory Stop V - XXX - 461 - X - E - 2	\$2288.00	\$2819.00	\$2942.00	\$3512.00	\$6206.00	\$6603.00	\$8584.50	-	-
Fluoroelastomer (CHP) Seat 10-Position Handle with Memory Stop V - XXX - 461 - X - O - 2	2745.50	3381.00	3529.50	4214.00	7447.50	7924.50	10301.50	-	-
EPDM (E) or Nitrile (T) Seat 10-Position – Tamper Proof	2634.50	3164.00	3284.50	3859.50	6530.00	6948.00	8926.00	-	-
10-POSITION OPERATOR - STAINLESS STEEL									
EPDM (E) or Nitrile (T) Seat 10-Position Handle with Memory Stop	\$2746.00	\$3381.00	\$3529.50	\$4211.50	7447.00	\$7922.50	\$10301.50	-	-
Fluoroelastomer (CHP) Seat 10-Position Handle with Memory Stop	+	+	+	+	+	+	+	+	+
GEAR OPERATOR - ALUMINUM									
EPDM (E) or Nitrile (T) Seat Gear Operator V - XXX - 461 - X - E - 3	\$4179.00	\$4705.50	\$4825.50	\$5401.00	\$7905.50	\$8410.00	\$10394.00	\$19131.50	\$21645.50
EPDM (E) or Nitrile (T) Seat Gear Operator with Memory Stop	4681.50	5209.50	5329.50	5903.00	8498.50	9041.50	11018.00	20280.50	23482.50
Fluoroelastomer (CHP) Seat Gear Operator V - XXX - 461 - X - O - 3	5013.50	5645.50	5790.50	6480.50	9485.00	10090.50	12471.50	22957.00	25973.50
EPDM (E) or Nitrile (T) Seat Gear Operator with Chain Wheel V - XXX - 461 - X - E - 6	6035.00	6562.00	6684.00	7257.50	9648.00	10264.00	12245.00	22539.50	25466.50
EPDM (E) or Nitrile (T) Seat Gear Operator with Memory Stop and Chain Wheel	6534.50	7063.50	7186.00	7754.50	10235.00	10890.00	12873.50	23700.50	26780.50
Gear Operator with AWWA 2" Square Operator Nut	+	+	+	+	+	+	+	+	+

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

+ Quoted on application. Contact Victaulic for pricing and availability.

Products for IPS Stainless Steel Pipe

V - 030 461 X E - O

Type	Actual OD in/mm	Size Code	Series	Disc/Stem	Seat	Operator
V	2.375/60.3	020	461	X - 316SS/17-4PH	E - EPDM	0 - Bare
	2.875/73.0	024	E461	(461 only)	T - Nitrile	2 - 10-Position Handle with Memory Stop
	3.000/76.1	761		E - 316SS/17-4PH	O - Fluoroelastomer	3 - Gear Operator
	3.500/88.9	030		(E461 only)		4 - Lever Lock with Tamper-Resistant Device (8"/200 mm)
	4.500/114.3	040				5 - Gear Operator with Memory Stop
	5.500/139.7	139				6 - Gear Operator with Chain Wheel
	5.563/141.3	050				7 - Gear Operator with Memory Stop and Chain Wheel
	6.500/165.1	165				8 - Gear Operator with AWWA 2" Square Oper. Nut
	6.625/168.3	060				S - Bare Valve with ISO 5211 Diagonal Square Head Drive
	8.500/216.3	216				X - Stainless Steel 10-Position Handle with Memory Stop
	8.625/219.1	080				
	10.500/267.4	267				
	10.750/273.0	100				
	12.500/318.5	318				
12.750/323.9	120					

TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. Box 31, Easton, PA 18044-0031 • 4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com

