

Price List Addendum

EFFECTIVE July 13, 2026



PL2026-GEN-ADD17

Ductile Iron Couplings for Stainless Steel Applications

Rigid Coupling for
Technology Cooling
Systems

STYLE 07-TCS

Refer to publication 06.34



STYLE 07-TCS – GRADE “E” FLUSH-SEAL™ GASKET

PIPE		Approx. Wgt. Ea.	COUPLING COMPLETE † with Flush-Seal Grade “E” Gasket	SPARE PARTS	
inches			Price Each	Stainless Steel Bolt & Nut	
Nom. Size	Outside Dia.		lb	Painted	No. *
1	1.315	1.6	\$262.50	2	$\frac{3}{8}$ x 2
1¼	1.660	1.6	267.50	2	$\frac{3}{8}$ x 2
1½	1.900	1.6	282.50	2	$\frac{3}{8}$ x 2
2	2.375	2.3	336.50	2	$\frac{1}{2}$ x 2½
2½	2.875	2.6	401.50	2	$\frac{1}{2}$ x 2¾
3	3.500	3.0	423.00	2	$\frac{1}{2}$ x 2½
4	4.500	5.3	590.00	2	$\frac{1}{2}$ x 2¾
6	6.625	8.3	1091.50	2	$\frac{5}{8}$ x 3¼
8	8.625	15.1	1442.50	2	$\frac{3}{4}$ x 4¼
10	10.750	23.5	2882.50	2	$\frac{7}{8}$ x 6½
12	12.750	28.2	3275.00	2	$\frac{7}{8}$ x 6½

* Number of bolts equals number of segments supplied.

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

† Surcharge for couplings supplied without gasket. Contact Victaulic for pricing.

§ Metric thread size bolts available. Contact Victaulic.

NOTE: See Spare Parts Section for spare part prices.



Products for Grooved Stainless Steel Pipe

Series BH1 Braided Flexible Hose

Refer to publication 11.10



BH1 FLEXIBLE HOSE

Size (Diameter)	Length inches	OGS x OGS		OGS x NPT		OGS x BSPT		OGS x BSPP		BSPP x BSPP	
		Part Code	Price Each	Part Code	Price Each	Part Code	Price Each	Part Code	Price Each	Part Code	Price Each
¾	12	AA70BH1OGO	+	-	-	-	-	-	-	-	-
	18	AA71BH1OGO	+	-	-	-	-	-	-	-	-
	24	AA72BH1OGO	+	-	-	-	-	-	-	-	-
	36	AA74BH1OGO	+	-	-	-	-	-	-	-	-
	48	ADC5BH1OGO	+	-	-	-	-	-	-	-	-
	72	ADC6BH1OGO	+	-	-	-	-	-	-	-	-
1	18	AA96BH1OGO	+	-	-	-	-	-	-	AA96BH1BMB	+
	24	AA97BH1OGO	+	-	-	-	-	-	-	AA97BH1BMB	+
	36	AA99BH1OGO	+	-	-	-	-	-	-	AA99BH1BMB	+
	48	ALC1BH1OGO	+	-	-	-	-	-	-	ALC1BH1BMB	+
	72	ADC7BH1OGO	+	-	-	-	-	-	-	ADC7BH1BMB	+
1¼	18	AB20BH1OGO	+	AB20BH1OGN	+	AB20BH1OGB	+	AB20BH1OMB	+	AB20BH1BMB	+
	24	AB21BH1OGO	+	AB21BH1OGN	+	AB21BH1OGB	+	AB21BH1OMB	+	AB21BH1BMB	+
	36	AB23BH1OGO	+	AB23BH1OGN	+	AB23BH1OGB	+	AB23BH1OMB	+	AB23BH1BMB	+
	48	ADC8BH1OGO	+	ADC8BH1OGN	+	ADC8BH1OGB	+	ADC8BH1OMB	+	ADC8BH1BMB	+
	72	ADC9BH1OGO	+	ADC9BH1OGN	+	ADC9BH1OGB	+	ADC9BH1OMB	+	ADC9BH1BMB	+
1½	18	AB49BH1OGO	+	AB49BH1OGN	+	AB49BH1OGB	+	AB49BH1OMB	+	AB49BH1BMB	+
	24	AB50BH1OGO	+	AB50BH1OGN	+	AB50BH1OGB	+	AB50BH1OMB	+	AB50BH1BMB	+
	36	AB52BH1OGO	+	AB52BH1OGN	+	AB52BH1OGB	+	AB52BH1OMB	+	AB52BH1BMB	+
	48	ADD0BH1OGO	+	ADD0BH1OGN	+	ADD0BH1OGB	+	ADD0BH1OMB	+	ADD0BH1BMB	+
	72	ADD1BH1OGO	+	ADD1BH1OGN	+	ADD1BH1OGB	+	ADD1BH1OMB	+	ADD1BH1BMB	+
2	24	AB90BH1OGO	+	AB90BH1OGN	+	AB90BH1OGB	+	AB90BH1OMB	+	AB90BH1BMB	+
	36	AB92BH1OGO	+	AB92BH1OGN	+	AB92BH1OGB	+	AB92BH1OMB	+	AB92BH1BMB	+
	48	AB58BH1OGO	+	AB58BH1OGN	+	AB58BH1OGB	+	AB58BH1OMB	+	AB58BH1BMB	+
	72	ABT1BH1OGO	+	ABT1BH1OGN	+	ABT1BH1OGB	+	ABT1BH1OMB	+	ABT1BH1BMB	+
2½	24	AC32BH1OGO	+	-	-	-	-	-	-	-	-
	36	AC34BH1OGO	+	-	-	-	-	-	-	-	-
	48	ADD2BH1OGO	+	-	-	-	-	-	-	-	-
3	36	AC83BH1OGO	+	-	-	-	-	-	-	-	-
	48	ADD3BH1OGO	+	-	-	-	-	-	-	-	-
4	36	AD94BH1OGO	+	-	-	-	-	-	-	-	-
	48	AP04BH1OGO	+	-	-	-	-	-	-	-	-
6	39	ADD4BH1OGO	+	-	-	-	-	-	-	-	-
	51	ADD5BH1OGO	+	-	-	-	-	-	-	-	-
	53	ADD6BH1OGO	+	-	-	-	-	-	-	-	-

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

+ Quoted on application. Contact Victaulic for pricing and availability.

TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. Box 31, Easton, PA 18044-0031 • 4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com