

Price List Addendum

EFFECTIVE August 12, 2026



PL2026-GEN-ADD19

Stainless Steel Valves for Grooved IPS SS Pipe

Vic-300 MasterSeal™

Stainless Steel Butterfly Valve
for High Pressure Applications



SERIES 462

Refer to publication 17.42

	2" (020)	2½" (024)	3" (030)	4" (040)	5" (050)	6" (060)	8" (080)	10" (100)	12" (120)
BARE VALVE									
EPDM (E) or Nitrile (T) Seat V - XXX - 462 - X - E - 0	\$2077.00	\$2706.50	\$2858.50	\$3545.00	\$6726.00	\$7156.00	\$9526.00	\$19289.00	\$21792.50
Fluoroelastomer (CHP) Seat V - XXX - 462 - X - O - 0	2493.00	3351.50	3429.50	4254.50	8073.00	8588.00	11432.00	23145.00	26150.50
PRICE OF VALVE COMPLETE WITH OPERATOR									
10-POSITION OPERATOR – ZINC PLATED									
EPDM (E) or Nitrile (T) Seat 10-Position Handle with Memory Stop V - XXX - 462 - X - E - 2	\$2745.50	\$3383.00	\$3530.50	\$4214.50	\$7447.00	\$7923.50	\$10301.50	–	–
Fluoroelastomer (CHP) Seat 10-Position Handle with Memory Stop V - XXX - 462 - X - O - 2	3294.50	4057.00	4235.50	5057.00	8937.00	9509.50	12362.00	–	–
EPDM (E) or Nitrile (T) Seat 10-Position – Tamper Proof V - XXX - 462 - X - E - 4	+	+	+	+	+	+	+	–	–
10-POSITION OPERATOR - STAINLESS STEEL									
EPDM (E) or Nitrile (T) Seat 10-Position Handle with Memory Stop V - XXX - 462 - X - E - X	+	+	+	+	+	+	+	–	–
Fluoroelastomer (CHP) Seat 10-Position Handle with Memory Stop V - XXX - 462 - X - O - X	+	+	+	+	+	+	+	+	+
EPDM (E) or Nitrile (T) Seat 10-Position Handle with Memory Stop and Tamper Proof V - XXX - 462 - X - E - Y	+	+	+	+	+	+	+	+	+
Fluoroelastomer (CHP) Seat 10-Position Handle with Memory Stop and Tamper Proof V - XXX - 462 - X - O - Y	+	+	+	+	+	+	+	+	+
GEAR OPERATOR - ALUMINUM									
EPDM (E) or Nitrile (T) Seat Gear Operator V - XXX - 462 - X - E - 3	\$5015.00	\$5646.50	\$5790.50	\$6481.00	\$9486.50	\$10092.00	\$12473.00	\$22958.00	\$25974.50
EPDM (E) or Nitrile (T) Seat Gear Operator with Memory Stop V - XXX - 462 - X - E - 5	+	+	+	+	+	+	+	+	+
Fluoroelastomer (CHP) Seat Gear Operator V - XXX - 462 - X - O - 3	6016.00	6774.50	6948.50	7776.50	11382.00	12108.50	14966.00	27548.50	31168.00
EPDM (E) or Nitrile (T) Seat Gear Operator with Chain Wheel V - XXX - 462 - X - E - 6	+	+	+	+	+	+	+	+	+
EPDM (E) or Nitrile (T) Seat Gear Operator with Memory Stop and Chain Wheel V - XXX - 462 - X - E - 7	+	+	+	+	+	+	+	+	+
Gear Operator with AWWA 2" Square Operator Nut V - XXX - 462 - X - E - 8	+	+	+	+	+	+	+	+	+

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

+ Quoted on application. Contact Victaulic for pricing and availability.



Products for IPS Stainless Steel Pipe

V 040 462 X E O						
Type	Actual OD in/mm	Size Code	Series	Disc/Stem	Seat	Operator
V	2.375/60.3 2.875/73.0 3.000/76.1 3.500/88.9 4.500/114.3 5.500/139.7 5.563/141.3 6.500/165.1 6.625/168.3 8.625/219.1 10.750/273.0 12.750/323.9	020 024 030 040 139 050 165 060 080 100 120	462	X - 316SS/17-4PH	E - EPDM T - Nitrile O - Fluoroelastomer	0 - Bare Valve with Flat-Head Drive (2 - 12"/DN50 - DN300) 2 - Carbon Steel 10-Postion/Lever Lock Handle with Memory Stop (2 - 8"/DN50 - DN200) 3 - Gear Operator with Handwheel (2 - 12"/DN50 - DN300) 4 - Carbon Steel 10-Postion/Lever Lock Handle with Memory Stop and Tamper-Resistant Hardware (2 - 8"/DN50 - DN200) 5 - Gear Operator with Handwheel and Memory Stop (2 - 12"/DN50 - DN300) 6 - Gear Operator with Handwheel and Chainwheel Kit (2 - 12"/DN50 - DN300) 7 - Gear Operator with Handwheel, Memory Stop, and Chainwheel Kit (2 - 12"/DN50 - DN300) 8 - Gear Operator with AWWA 2" Square Operation Nut (2 - 12"/DN50 - DN300) S - Bare Valve with ISO 5211 Diagonal Square-Head Drive (2 - 12"/DN50 - DN300) X - Stainless Steel 10-Postion/Lever Lock Handle with Memory Stop (2 - 8"/DN50 - DN200) Y - Stainless Steel 10-Postion/Lever Lock Handle with Memory Stop and Tamper-Resistant Hardware (2 - 8"/DN50 - DN200)

TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. Box 31, Easton, PA 18044-0031 • 4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com