

Price List Addendum

EFFECTIVE March 31, 2026



PL2026-GEN-ADD8

Stainless Steel and Duplex Couplings

NOTE: For 1/2 – 2” stainless steel pipe refer to Section 9 Vic-Press™ System for Schedule 10S Stainless Steel Pipe

Stainless Steel Mechanical-T Branch Outlet

STYLE 422

Refer to publication 17.02



Grooved Branch



Threaded Branch



STYLE 422 BRANCH OUTLET

Size	Complete <i>Mechanical-T</i>						Spare Parts			
	Inches	Grooved Branch			Threaded Branch			Bolts & Nuts Size	Standard Grade "E" Gaskets	
		Approx. Wgt. Ea.	Stainless Steel Upper, Galvanized Lower Outlet Housing	Stainless Steel Upper Housing, Stainless Steel Lower Housing	Approx. Wgt. Ea.	Stainless Steel Upper Housing, Galvanized Lower Housing	Stainless Steel Upper Housing, Stainless Steel Lower Housing			
	Run x Brch.	Lbs	Price Each		Lbs	Price Each	Inches	Price Each		
2	x 3/4	-	-	-	3.0	\$381.50	\$616.50	1/2 x 2 3/4	+	
	x 1	-	-	-	3.0	381.50	616.50	1/2 x 2 3/4	\$47.00	
	x 2 1/2	x 3/4	-	-	-	3.2	435.50	676.00	1/2 x 2 3/4	+
		x 1	-	-	-	2.9	435.50	676.00	1/2 x 2 3/4	+
2 1/2	x 1 1/4	-	-	-	4.0	435.50	665.50	1/2 x 3 1/4	55.00	
	x 1 1/2	-	-	-	4.0	435.50	665.50	1/2 x 3 1/4	55.00	
	x 3	x 3/4	-	-	-	3.4	489.50	676.00	1/2 x 2 3/4	+
		x 1	-	-	-	3.4	489.50	676.00	1/2 x 2 3/4	47.00
3	x 1 1/2	-	-	-	5.0	544.00	869.50	1/2 x 2 3/4	55.00	
	x 2	4.6	\$580.00	+	5.3	544.00	1117.50	1/2 x 3 1/4	55.00	
	x 4	x 3/4	-	-	-	5.1	600.00	1089.50	1/2 x 3 1/4	+
		x 1	-	-	-	5.0	600.00	1089.50	1/2 x 3 1/4	47.00
4	x 1 1/2	-	-	-	5.6	665.50	1152.50	1/2 x 3 1/4	55.00	
	x 2	4.6	708.50	+	6.0	665.50	1262.00	1/2 x 3 1/4	55.00	
	x 3	6.4	704.50	+	6.4	-	-	1/2 x 3 1/4	65.50	
	6	x 3/4	-	-	-	9.1	816.50	2021.50	5/8 x 5	+
x 1		-	-	-	9.0	816.50	2021.50	5/8 x 5	47.00	
x 1 1/2		-	-	-	8.3	906.50	2082.50	5/8 x 5	55.00	
x 2		5.6	965.50	+	8.9	906.50	2082.50	5/8 x 5	55.00	
x 3		8.4	927.50	+	8.4	-	-	5/8 x 5	65.50	
8	x 4	10.1	965.50	+	10.1	-	-	5/8 x 5	85.50	
	x 8	x 3/4	-	-	-	13.4	1344.50	2155.50	3/4 x 4 1/4	+
		x 1	-	-	-	13.3	1344.50	2155.50	3/4 x 4 1/4	47.00
	x 1 1/2	-	-	-	12.6	1344.50	2155.50	3/4 x 4 1/4	55.00	
	x 2	11.6	1433.00	+	11.8	1344.50	2155.50	3/4 x 4 1/4	62.00	
x 3	11.6	1419.50	+	11.6	-	-	3/4 x 4 1/4	65.50		
10	x 4	12.5	1377.50	+	12.5	-	-	3/4 x 4 1/4	85.50	
	x 10	x 3/4	-	-	-	17.0	+	2629.50	3/4 x 4 1/4	+
		x 1	-	-	-	16.8	+	2629.50	3/4 x 4 1/4	+
	x 1 1/2	-	-	-	16.2	+	2629.50	3/4 x 4 1/4	55.00	
x 2	-	-	-	15.4	+	2629.50	3/4 x 4 1/4	+		

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.

+ Quoted on application. Contact Victaulic for pricing and availability.

TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com

