Victaulic[®] Lubricant SDS

(Safety Data Sheet)

1.0 IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING		
1.1. Product Identifier		
Trade name	: VictaulicLubricant	
1.2. Relevant identified uses of the substance of	or mixture and uses advised against	
1.2.1. Relevant identified uses		
Industrial/Professional use spec.	: Industrial. For professional use only.	
Use of the substance/mixture	: A Pipe Joint Lubricant. For professional use only.	
1.2.2. Uses advised against		
No additional information available		
1.3. Details of the supplier of the safety data s	heet	
Supplier	Manufacturer	
Victaulic Europe BVBA	JTM Products, Inc.	
Prijkelstraat 36	31025 Carter Street	
B-9810 Nazareth, Belgium	Solon, OH 44139	
Telephone Number: +0032 9381 1500 Email:	Telephone Number: 001-1-440-287-2302	
viceuro@victaulic.com		
web: www.victaulic.com		
1.4. Emergency telephone number		
For Chemical Emergency: spill, leak, fire,	Europe/International: 00-1-703-741-5970 (collect calls accepted)	
exposure, or accident CHEMTREC [®] 24-hour service:	US/Canada: 1-800-424-9300	
2.0 HAZARDS IDENTIFICATION		

2.1. Classification of the Substance or Mixture

2.1.1. Classification according to Regulation (EC) No. 1272/2008 [CLP]

This mixture is classified as H319, a Category 2 eye irritant

2.1.2. Adverse physicochemical, human health and environmental effects

No additional information available

ALWAYS REFER TO ANY NOTIFICATIONS AT THE END OF THIS DOCUMENT REGARDING PRODUCT INSTALLATION, MAINTENANCE OR SUPPORT.				
System No.	Location	Spec Section	Paragraph	
Submitted By	Date	Approved	Date	

1

victaulic.com

05.02-EU 7503 Rev G Updated 08/2020

© 2020 Victaulic Company. All rights reserved.



2.0 HAZARDS IDENTIFICATION (Continued)

2.1.4. Additional information

For a full text of H-statements: see Section 16

2.2. Label Elements

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictogram:



Signal Word: Warning

Hazard Statement:

H319: Causes serious eye irritation

Precautionary Statements:

P264 Wash your hands thoroughly after handling

P280 Wear eye protection.

P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P337+P313 If eye irritation persists: Get medical advice/attention.

2.3. Other Hazards

Not applicable

3.0 COMPOSITION/INFORMATION ON INGREDIENTS

- 3.1. Substances
- Not applicable

3.2. Mixture

Name	Product Identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
Fatty acids, tall-oil, potassium salts	(CAS No) 61790-44-1 (EC No) 262-993-9	77.3	H319
1,2-Propylene glycol	(CAS No) 57-55-6 (EC No) 200-338-0	14.6	Not classified
Mica substance with national workplace exposure limit(s) (AT, BE, BG, CZ, ES, GB, IE, IT, PT, SK)	(CAS No) 12001-26-2	8	Not classified

Full text of H-phrases: see section 16

05.02-EU 7503 Rev G Updated 08/2020

© 2020 Victaulic Company. All rights reserved.

victaulic.com

ictaulic



4.0 DESCRIPTION OF FIRST AID MEASURES

4.1. Description of first aid measures	
General	: Never give anything by mouth to an unconscious person. If you feel unwell, seek medical advice (show the label where possible).
After inhalation	: Not expected to present a significant inhalation hazard.
After skin contact	: Remove contaminated clothing. Gently wash with plenty of soap and water. Wash contaminated clothing before reuse.
After eye contact	 Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
After ingestion	: Rinse mouth. Do NOT induce vomiting.
4.2. Most important symptoms and effect	s, both acute and delayed
General	: Not expected to present a significant health hazard under normal conditions of use.
After inhalation	: Not expected to present a significant inhalation hazard.
After skin contact	: May cause irritation due to prolonged/repeated periods of use.
After eye contact	: May cause eye irritation.
After ingestion	:: May cause gastrointestinal irritation.
4.3 Indication of any immediate medical at	tention and special treatment needed

If you feel unwell, get medical advice and attention.

FIREFIGHTING MEASURES 5.0 5.1. Extinguishing media Suitable extinguishing media : Use extinguishing media appropriate for surrounding fire. : Do not use a heavy water stream. Use of heavy stream of water Unsuitable extinguishing media may spread fire. 5.2. Special hazards arising from the substance or mixture Fire hazard : Not considered flammable but may burn at high temperatures. Explosion hazard : Product is not explosive. Reactivity : Hazardous reactions will not occur. 5.3. Advice for firefighters Precautionary measures fire : Exercise caution when fighting any chemical fire. **Firefighting instructions** : Use water spray or fog for cooling exposed containers. Protection during firefighting : Do not enter fire area without proper protective equipment, including respiratory protection.

05.02-EU 7503 Rev G Updated 08/2020

© 2020 Victaulic Company. All rights reserved.

victaulic.com

erveu.



6.0 ACCIDENTAL RELEASE MEASURES			
6.1. Personal precautions, protective equipr	nent and emergency procedures		
Seneral measures : Avoid all contact with eyes, skin, or clothing.			
6.1.1. For non-emergency personnel			
Protective equipment	: Use appropriate personal protection equipment (PPE).		
Emergency procedures	: Evacuate unnecessary personnel.		
6.1.2. For emergency responders			
Protective equipment	: Equip cleanup crew with proper protection.		
Emergency procedures	: Ventilatearea.		
6.2. Environmental precautions			
Prevent entry to sewers and public waters.			
6.3. Methods and material for containment a	nd cleaning up		
For containment	: Absorb and/or contain spill with inert material, then place in suitable container.		
Methods for cleaning up	: Clear up spills immediately and dispose of waste safely.		
6.4. Reference to other sections			
See Section 8.			
7.0 HANDLING AND STORAGE			
71. Precautions for safe handling			
Precautions for safe handling	: Avoid all contact with eyes, skin, or clothing.		
Hygiene measures	: Handle in accordance with good industrial hygiene and safety procedures. Wash hands and other exposed areas with mild soap and water before eating, drinking, or smoking and agair when leaving work.		
72. Conditions for safe storage, including ar	y incompatibilities		
Technical measures	: Comply with applicable regulations.		
Storage conditions	: Store in a dry, cool and well-ventilated place.		
Incompatible products	: Strong acids. Strong bases. Strong oxidizers.		
73. Specific end use(s)			

A Pipe Joint Lubricant. For professional use only.

05.02-EU 7503 Rev G Updated 08/2020

© 2020 Victaulic Company. All rights reserved.

victaulic.com

victaulic



8.0 EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1. Control parameters

Fatty acids, tall-oil, potassiu	m salts (CAS 61790-44-1)	
	Limit value - Eight hours	Limit value - Short term
	None established	None established
Mica (CAS 12001-26-2)		
	Limit value - Eight hours	Limit value - Short term
Austria	10 mg/m ³ (inhalable aerosol)	
Belgium	3 mg/m ³	
Denmark	0.3 fibers per cm ³	0.3 fibers per cm ³
Ireland	10 mg/m ³ (inhalable fraction) 0.8 mg/m ³ (respirable fraction)	
Latvia	4 mg/m ³ (and phlogopite muscovite)	
Switzerland	3 mg/m ³ (respirable aerosol)	
United Kingdom	10 mg/m ³ (inhalable aerosol) 0.8 mg/m ³ (respirable aerosol)	
1,2-Propylene glycol (CAS 57	7-55-6)	
	Limit value - Eight hours	Limit value - Short term
Ireland	470 mg/m ³ (total vapor & particulate) 10 mg/m ³ (particulate)	
Latvia	7 mg/m ³ (particulate)	
Norway	79 mg/m³	
United Kingdom	474 mg/m ³ (total vapor & particulate) 10 mg/m ³ (particulate)	

Source: GESTIS International Limit Values: http://limitvalue.ifa.dguv.de/

8.2. Exposure controls

Appropriate engineering controls	: Not expected to exceed permissible exposure level under intended use. Emergency eye wash fountains and safety showers should be available in the immediate vicinity. Ensure all national/ local regulations are observed.
Personal protective equipment	: Safetyglasses.
Materials for protective clothing	: No special clothing required.
Hand protection	: No special clothing required.
Eye protection	: Wear safety glasses.
Skin and body protection	: No special clothing required.
Respiratory protection	: Under normal use it is not expected that exposure limits will be exceeded.
Other information	: When using, do not eat, drink or smoke.
05.02-EU 7503 Rev G Updated 08/2020	© 2020 Victaulic Company. All rights reserved.

victaulic.com



9.0 PHYSICAL AND CHEMICAL PROPERTIES

9.1. Information on basic physical and chemical properties

Physical state	: Liquid			
Appearance	: Amber viscous paste			
Odor	: Mild			
Odor threshold	: No dataavailable			
рН	: 11			
Relative evaporation rate (butyl acetate=1)	: No dataavailable			
Melting point	: <0°C(32°F)			
Freezing point	: No dataavailable			
Boiling point	: >104°C(220°F)			
Flash Point	: >104°C(220°F)			
Auto-ignition temperature	: No dataavailable			
Decomposition Temperature	: No dataavailable			
Flammability (solid, gas)	: No dataavailable			
Vapor pressure	: No dataavailable			
Relative vapor density at 20°C	: No dataavailable			
Relative density	: 1.08 (water = 1)			
Density	: 1.07 kg/L(9.01 lbs/gal) at room temperature			
Solubility	: Soluble in water			
Log Pow	: No dataavailable			
Log Kow	: No dataavailable			
Viscosity, kinematic	: No dataavailable			
Viscosity, dynamic	: No dataavailable			
Explosive properties	: No dataavailable			
9.1. Information on basic physical and chemical properties Oxidizing				
properties	: No data available			
Explosive limits	: Notapplicable			
9.2. Other information	9.2. Other information			

: 146g/L

VOC content

10.0 STABILITY AND REACTIVITY

10.1. Reactivity

Hazardous reactions will not occur.

10.2. Chemical stability

Stable at standard temperature and pressure.

10.3. Possibility of hazardous reactions

Hazardous reactions will not occur.

10.4. Conditions to avoid

Direct sunlight. Extremely high or low temperatures.

10.5. Incompatible materials

Strong acids. Strong bases. Strong oxidizers.

10.6. Hazardous decomposition products

Carbon oxides (CO, CO₂). Silicon oxides.

05.02-EU 7503 Rev G Updated 08/2020 © 2020 Victaulic Company. All rights reserved.

victaulic.com



11.0 TOXICOLOGICAL INFORMATION

11.1. Information on toxicological effects

Acute toxicity

: No data is available on the mixture. Acute toxicity data via the oral route is available for 1,2-propylene glycol. Not acutely toxic.

1,2-Propylene glycol (57-55-6)		
LD50 oral rat	22000 mg/kg	
LD50 dermal rabbit	>2000 mg/kg	
Skin corrosion/irritation	: Not classified (pH: 11).	
Serious eye damage/irritation	: The mixture is classified as eye irritant substance H319 according to Regulation (EC) 1272/2008.	
Respiratory or skin sensitisation	: Not classified	
Germ cell mutagenicity	: Not classified	
Carcinogenicity	: Not classified	
Reproductive toxicity	: Not classified	
Specific target organ toxicity (single	e exposure) : Not classified	
Specific target organ toxicity (repea	ted exposure) : Not classified	
Aspiration hazard	: Notclassified	
Potential Adverse human health effec symptoms	ts and : Not expected to present a significant hazard under normal conditions of use.	

12.0 ECOLOGICAL INFORMATION

12.1. Toxicity

No data are available on the mixture. Aquatic toxicity data are available for 1,2-propylene glycol. The substance is not classified for aquatic toxicity.

1,2-Propylene glycol (57-55-6)		
LC50 fishes 1	51600 mg/l (Exposure time: 96 h - Species: Oncorhynchus mykiss [static])	
EC50 Daphnia 1	10000 mg/l (Exposure time: 96 h - Species: Daphnia magna)	
EC50 Aquatic algae	19000 mg/l (Exposure time: 96 h - Species: Pseudokirchneriella subcapitata)	
LC50 fish 2	41000 (41000 - 47000) mg/l (Exposure time: 96 h - Species: Oncorhynchus mykiss [static])	
EC50 Daphnia 2	1000 mg/l (Exposure time: 48 h - Species: Daphnia magna [Static])	
12.2. Persistence and degra	adability	
Victaulic Lubricant		

Persistence and degradability	Not established.

12.3. Bioaccumulative potential

No data is available on this mixture. A BCF value has been estimated by calculation based on the phys-chem properties of the substance 1,2-propylene glycol.

Victaulic Lubricant	
Bioaccumulative potential	Not established.
1,2-Propylene glycol (CAS 57-55-6)	
BCF calculated value	<1

05.02-EU 7503 Rev G Updated 08/2020

 $\ensuremath{\mathbb{C}}$ 2020 Victaulic Company. All rights reserved.

victaulic.com



ECOLOGICAL INFORMATION (Continued) 12.0

12.4. Mobility in soil

No additional information available

12.5. Results of PBT and vPvB assessment

No additional information available

12.6. Other adverse effects

Other information

: Avoid release to the environment.

DISPOSAL CONSIDERATIONS 13.0

13.1. Waste treatment methods

Waste disposal recommendations

: Dispose of waste material in accordance with all local, regional, national, and international regulations.

TRANSPORT INFORMATION 14.0

In accordance with ADR / RID / ADNR / IMDG / ICAO / IATA

14.1. UN number

No dangerous good in sense of transport regulations.

14.2. UN proper shipping name

Not applicable

14.3. Transport hazard class(es)

Not applicable

14.4. Packing group

Not applicable.

14.5. Environmental hazards

Other information

: No supplementary information available.

14.6. Special precautions for user

14.6.1 Overland transport

No additional information available

14.6.2 Transport by sea

No additional information available

14.6.3. Air transport

No additional information available

14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Not applicable.

05.02-EU 7503 Rev G Updated 08/2020

© 2020 Victaulic Company. All rights reserved.

victaulic.com

ictaulic



15.0 REGULATORY INFORMATION

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

No REACH Annex XVII restrictions Contains

no REACH candidate substance

VOC content

: 146g/L

15.1.2. National regulations

No additional information available

15.2. Chemical safety assessment

No chemical safety assessment has been carried out

16.0 OTHER INFORMATION

16.1. Indication of changes

updated 11/2017

16.2. Abbreviations and acronyms

	•
ADNR	: European Agreement Concerning the International Carriage of Dangerous Goods by Inland Waterways
ADR	: European Agreement Concerning the International Carriage of Dangerous Goods by Road
AGS	: Ausschuss für Gefahrstoffe
CLP	: Classification, Labelling and Packaging regulation
DFG	: Deutsche Forschungsgemeinschaft
DPD	: Dangerous Preparation Directive
EC50	: effective concentration which causes 50% of the maximum response
IATA	: International Air Transport Association
ICAO	: International Civil Aviation Organization
IMDG	: International Maritime Dangerous Goods Code
LC50	: lethal concentration which causes death of 50% of a group of test animals PBT
	: persistent, bioaccumulative, toxic
PPM	: parts per million
RID	: European Agreement Concerning the International Carriage of Dangerous Goods by Rail

05.02-EU 7503 Rev G Updated 08/2020

 $\ensuremath{\mathbb{C}}$ 2020 Victaulic Company. All rights reserved.

victaulic.com

ictaulic

16.0 **OTHER INFORMATION (Continued)**

16.2. Abbreviations and acronyms

vPvB : very persistent, very bioaccumulative

VOC : volatile organic compound

16.3. Data Sources

REGULATION (EC) No 1272/2008 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006.

GESTIS International Limit Values: http://limitvalue.ifa.dguv.de/

Classification and procedure used to derive the classification for the mixture according to Regulation (EC) No 1272/2008 :

Classification according to Regulation (EC) 1272/2008	Classification procedure
Eye irrit. 2, H319	Calculation method (Fatty acids, vegetable-oil, potassium salts)

16.4. Relevant H-statements (number and full text)

H319: Causes serious eye irritation

16.5. Training advice

Always refer to the installation instructions, supplied with the product, and Victaulic publication 05.02-EU (Victaulic Lubricant Safety Data Sheet) for complete lubrication information and requirements. These documents can be downloaded at victaulic com

SDS EU (REACH ANNEX II)

Disclaimer: This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.

User Responsibility for Product Selection and Suitability	
Each user bears final responsibility for making a determination as to the suitability of	
Victaulic products for a particular end-use application, in accordance with industry sta	ndards
and project specifications, as well as Victaulic performance, maintenance, safety, and	
warning instructions. Nothing in this or any other document, nor any verbal	
recommendation, advice, or opinion from any Victaulic employee, shall be deemed to	alter,
vary, supersede, or waive any provision of Victaulic Company's standard conditions of	sale,
installation guide, or this disclaimer.	

tellectual Property Rights No statement contained herein concerning a possible or suggested use of any material, product, service, or design is intended, or should be constructed, to grant any license under any patent or other intellectual property right of Victaulic or any of its subsidiaries or affiliates covering such use or design, or as a recommendation of any of its substanties of such material, product, service, or design in the infringement of any patent or other intellectual property right. The terms "Patented" or "Patent Pending" refer to design or utility patents or patent applications for articles and/or methods of use in the United States and/or other countries.

Note

This product shall be manufactured by Victaulic or to Victaulic specifications. All products to be installed in accordance with current Victualic installation/assembly instructions. Victualic reserves the right to change product specifications, designs and standard equipn without notice and without incurring obligations.

Reference should always be made to the Victaulic installation handbook or installation instructions of the product you are installing. Handbooks are included with each shipment of Victaulic products, providing complete installation and assembly data, and are available in PDF format on our website at www.victaulic.com.

Installation

Warranty Refer to the Warranty section of the current Price List or contact Victaulic for details.

Trademarks Victaulic and all other Victaulic marks are the trademarks or registered trade Company, and/or its affiliated entities, in the U.S. and/or other countries. arks of Victaulio

05.02-EU 7503 Rev G Updated 08/2020

© 2020 Victaulic Company. All rights reserved.

