Victaulic[®] EndSeal[™] Coupling Style HP-70ES





PRODUCT DESCRIPTION

Available Sizes

• 2 - 12"/DN50 - DN300

Pipe Material

Carbon steel

Maximum Working Pressure

Accommodates pressures ranging from full vacuum (29.9 in Hg/760 mm Hg) up to 2500psi/17235 kPa

Operating Temperature

• Dependent on gasket selection from section 3.0.

Function

• Provides a rigid pipe joint designed to restrict axial or angular movement

Pipe Preparation

• Cut or roll grooved in accordance with <u>publication 25.02</u>: Victaulic EndSeal™ Groove Specifications.

2.0 CERTIFICATION/LISTINGS





• See <u>publication 10.01</u> for Fire Protection Certifications/Listings Reference Guide

ALWAYS REFER TO ANY NOTIFICATIONS AT THE END OF THIS DOCUMENT REGARDING PRODUCT INSTALLATION, MAINTENANCE OR SUPPORT.



3.0 SPECIFICATIONS - MATERIAL

Housing: Ductile iron conforming to ASTM A536, Grade 65-45-12.

Housing Coating: (specify choice)

Standard: Black enamel.

Optional: Hot dipped galvanized conforming to ASTM A153.

Optional: Contact Victaulic with your requirements for other coatings.

Gasket: (specify choice1)

Victaulic Grade "HMT" High Modulus Nitrile (EndSeal™)

High Modulus Nitrile (Orange and silver stripe color code). May be specified for oil related services, including air with oil vapor, this gasket may be specified for temperatures rated up to +180°F/+82°C. For water related services, this gasket may be specified for temperatures rated up to +150°F/+66°C. For oil free, dry air services, this gasket may be specified for temperatures rated up to +140°F/+60°C. **NOT COMPATIBLE FOR USE WITH HOT WATER SERVICES OR STEAM SERVICES.**

Victaulic Grade "T-607" Nitrile (EndSeal™)

Nitrile (Grey gasket color code). May be specified for oil related services, including air with oil vapor, this gasket may be specified for temperatures rated up to $+180^{\circ}F/+82^{\circ}C$. For water related services, this gasket may be specified for temperatures rated up to $+150^{\circ}F/+66^{\circ}C$. For oil free, dry air services, this gasket may be specified for temperatures rated up to $+140^{\circ}F/+60^{\circ}C$. **NOT COMPATIBLE FOR USE WITH HOT WATER SERVICES OR STEAM SERVICES.**

Others

For alternate gasket selection, reference <u>publication 05.01</u>: Victaulic Seal Selection Guide – Elastometric Seal Construction.

Services listed are General Service Guidelines only. It should be noted that there are services for which these gaskets are not compatible. Reference should always be made to the latest <u>Victaulic Seal Selection Guide</u> for specific gasket service guidelines and for a listing of services which are not compatible.

NOTE

• EndSeal™ Grade "T-607" Nitrile gaskets with HP-70ES couplings may be specified in systems requiring compliance with API607 fire testing and in foam systems requiring compliance with NFPA 11.


Bolts/Nuts:

Standard: Standard: Carbon steel oval neck track bolts meeting the mechanical property requirements of ASTM A449 (imperial) and ISO 898-1 (metric) Class 9.8 (M10-M16) and Class 8.8 (M20 and greater). Carbon steel hex nuts meeting the mechanical property requirements of ASTM A563 Grade B (imperial - heavy hex nuts) and ASTM A563M Class 9 (metric - hex nuts). Track bolts and hex nuts are zinc electroplated per ASTM B633 FE/ZN5, finish Type III (imperial) or Type II (metric).



4.0 DIMENSIONS

Style HP-70 ES





Size					Dimensions			Weight
Nominal	Actual Outside Diameter	Maximum Allowable Pipe End Sep. ²	No. Bolts Required ³	Imperial Bolt/ Nut Size ⁴	X	Y	Z	Approximate (Each)
inches	inches	inches			inches	inches	inches	lb
DN	mm	mm	Qty.	inches	mm	mm	mm	kg
2 DN50	2.375 60.3	0.19 4.8	2	5/8 X 2 3/4	3.50 89	6.50 165	1.88 48	3.3 1.5
		0.19			4.00	7.13	1.88	4.0
21/2	2.875 73.0	4.8	2	5/8 x 3 1/2	4.00 102	181	48	1.8
3	3.500	0.19		F/ 54/	4.75	7.75	1.88	4.6
DN80	88.9	4.8	2	% x 3 ½	121	197	48	2.1
	4.250	0.19	2	3/4 x 4 1/4	5.75	9.63	2.25	7.7
	108.0	4.8	Z	74 X 4 74	146	244	57	3.5
4	4.500	0.19	2	³ / ₄ x 4 ¹ / ₄	6.00	9.63	2.13	7.7
DN100	114.3	4.8		74 X 4 74	152	244	54	3.5
5	5.563	0.27	2	7/8 x 5 1/2	7.50	11.38	2.38	14.8
	141.3	6.9		78 X J 72	191	289	60	6.7
	6.250	0.27	2	% x 5 ½	8.25	12.63	2.50	15.8
	159.0	6.9		78 X J 72	210	321	64	7.2
6	6.625	0.27	2	% x 5 ½	8.50	12.63	2.50	15.8
DN150	168.3	6.9		78 X J 72	216	321	64	7.2
8	8.625	0.27	2	1 x 5 ½	11.00	15.00	2.75	26.6
DN200	219.1	6.9	۷	1 / 3 / 2	279	381	70	12.1
10	10.750	0.28	2	1 x 6 ½	13.38	17.25	3.00	33.7
DN250	273.0	7.1		1 A U 72	340	438	76	15.3
12	12.750	0.28	2	1 x 6 ½	15.50	19.00	3.00	41.5
DN300	323.9	7.1		1 X 0 /2	394	483	76	18.8

² The Maximum Allowable Pipe End Separation dimension is for system layout purposes only. Style HP-70ES EndSeal couplings are considered rigid connections and will not accommodate expansion/contraction or angular movement of the piping system. Contact Victaulic for torsional resistance information.

NOTES

- Pipe shall be grooved to Victaulic® EndSeal™ Pipe Groove Specifications found in Victaulic <u>publication 25.02</u>.
- Victaulic® Original Groove System (OGS) ductile iron fittings may be used with HP-70ES couplings up to the maximum working pressure of the fittings (1000psi 2 6"/DN50 DN150, 800psi 8 12"/DN200 DN300)
- Victaulic EndSeal Extra Strong fittings may be used with HP-70ES couplings up to the maximum working pressure of HP-70ES couplings.
- HP-70ES couplings cannot be used with Victaulic Series 700 Butterfly Valves.



³ Number of bolts required equals number of housing segments.

⁴ Metric thread size bolts are available (color coded gold) for all coupling sizes upon request. Contact Victaulic for details.

5.0 PERFORMANCE

Siz	ze	Performance			
Nominal	Actual Outside Diameter	Maximum Working Pressure ⁵	Maximum End Load⁵		
inches	inches	psi	Lbs.		
DN	mm	kPa	N		
2	2.375	2500	11075		
DN50	60.3	17237	49264		
2½	2.875	2500	16230		
	73.0	17237	72195		
3	3.500	2500	24053		
DN80	88.9	17237	106993		
DNOU	4.250	2500	35465		
	108.0	17237	157756		
4	4.500	2500	39761		
DN100	114.3	17237	176866		
5	5.563	2000	48611		
	141.3	13790	216233		
	6.250	2000	61359		
	159.0	13790	272938		
6	6.625	2000	68943		
DN150	168.3	13790	306674		
8	8.625	1500	87640		
DN200	219.1	10342	389842		
10	10.750	1250	113453		
DN250	273.0	8618	504664		
12	12.750	1250	159596		
DN300	323.9	8618	709918		

⁵ Working Pressure and End Load are total, from all internal and external loads, based on standard weight (ANSI) steel pipe, "ES" cut or roll grooved in accordance with Victaulic specifications. Contact Victaulic for performance on other pipe.

NOTE

• WARNING: FOR ONE TIME FIELD TEST ONLY, the Maximum Joint Working Pressure may be increased to 11/4 times the figures shown.

6.0 NOTIFICATIONS













• Style HP-70ES Couplings shall be used ONLY with pipe that is prepared to Victaulic EndSeal™ "ES" specifications. DO NOT attempt to install Style HP-70ES Couplings on pipe that is prepared to any other groove specification.

WARNING

- Style HP-70ES Couplings SHALL NOT be used for installation of Victaulic Series 700 Butterfly Valves.
- Heavy-wall fittings shall be used for applications with operating pressures over 1000 psi/69 Bar (for 2 6-inch/DN50 DN150 coupling sizes) and 800 psi/55 Bar (for 8 12-inch/DN200 DN300 coupling sizes).

Failure to follow these instructions could cause joint failure, resulting in death or serious personal injury and property damage.

NOTICE

4

 Victaulic does not recommend the use of any furnace butt-welded pipe with sizes NPS 2"/DN50 and smaller Victaulic gasketed joint products. This includes, but is not limited to, ASTM A53 Type F pipe.



victaulic.com

7.0 REFERENCE MATERIALS

05.01: Victaulic Seal Selection Guide

07.03 Extra Strong EndSeal Fittings

10.01: Victaulic Products for Fire Protection Piping Systems - Regulatory Approval Reference Guide

25.02: EndSeal™ Groove Specifications

26.01 Victaulic Design Data

29.01: Victaulic Terms and Conditions of Sale

I-100: Victaulic Field Installation Handbook

I-ENDCAP: Victaulic End Cap Installation Safety Instructions

I-IMPACT: Victaulic Impact Tool Usage Guidelines

User Responsibility for Product Selection and Suitability

Each user bears final responsibility for making a determination as to the suitability of Victaulic products for a particular end-use application, in accordance with industry standards and project specifications, as well as Victaulic performance, maintenance, safety, and warning instructions. Nothing in this or any other document, nor any verbal recommendation, advice, or opinion from any Victaulic employee, shall be deemed to alter, vary, supersede, or waive any provision of Victaulic Company's standard conditions of sale, installation guide, or this disclaimer.

Intellectual Property Rights

No statement contained herein concerning a possible or suggested use of any material, product, service, or design is intended, or should be constructed, to grant any license under any patent or other intellectual property right of Victaulic or any of its subsidiaries or affiliates covering such use or design, or as a recommendation for the use of such material, product, service, or design in the infringement of any patent or other intellectual property right. The terms "Patented" or "Patent Pending" refer to design or utility patents or patent applications for articles and/or methods of use in the United States and/or other countries. countries.

Note

This product shall be manufactured by Victaulic or to Victaulic specifications. All products to be installed in accordance with current Victaulic installation/assembly instructions Victaulic reserves the right to change product specifications, designs and standard equipment without notice and without incurring obligations.

Reference should always be made to the Victaulic installation handbook or installation instructions of the product you are installing. Handbooks are included with each shipment of Victaulic products, providing complete installation and assembly data, and are available in PDF format on our website at www.victaulic.com.

Warranty
Refer to the Warranty section of the current Price List or contact Victaulic for details.

Trademarks

Victaulic and all other Victaulic marks are the trademarks or registered trademarks of Victaulic Company, and/or its affiliated entities, in the U.S. and/or other countries.

06.13 1943 Rev H Updated 08/2021 © 2021 Victaulic Company. All rights reserved.

