


# Victaulic® FireLock™ IGS™ Installation-Ready™ Style V9 Sprinkler Coupling



Patented



## 1.0 PRODUCT DESCRIPTION

### Available Sizes

- Branch Line Connection: 1"/DN25
- Sprinkler Connections: 1"/DN25, ¾"/DN20, ½"/DN15


### Maximum Working Pressure

- Up to 250 psi/1725 kPa.

### Function

- Intended only for joining Victaulic IGS™ grooved sprinklers to IGS™ grooved sprinkler outlets. See the IGS roll groove specification, [publication 25.14](#) and the FireLock™ IGS™ System, [publication 10.54](#) for more information.
- Provides a rigid pipe to sprinkler connection.

## 2.0 CERTIFICATION/LISTINGS



## 3.0 SPECIFICATIONS – MATERIAL

### Housing:

Bronze according to the chemical requirements of UNS C87800 modified, or Dezincification Resistant (DZR) Brass

### Gasket<sup>1</sup>:

#### Victaulic Grade “E” EPDM (Type A)

Applicable for wet and dry (oil-free air) sprinkler services only. Listed/Approved for continuous use in wet and dry systems. Listed/Approved for dry systems at -40°F/-40°C and above. NOT COMPATIBLE FOR USE WITH HOT WATER SERVICES OR STEAM SERVICES.

<sup>1</sup> It should be noted that there are services for which these gaskets are not compatible. Reference should always be made to the latest [Victaulic Gasket Selection Guide](#) for specific gasket service guidelines and for a listing of services which are not compatible.


### Bolts/Nuts:

Standard: Button head cap screws per ASTM F835, zinc plated. Nylon insert locknut, Grade 5, zinc plated.

ALWAYS REFER TO ANY NOTIFICATIONS AT THE END OF THIS DOCUMENT REGARDING PRODUCT INSTALLATION, MAINTENANCE OR SUPPORT.

## 4.0 DIMENSIONS

### Style V9 Sprinkler Coupling



Style V9 Pre-Assembled  
(Push On Condition)

Style V9 Joint Assembled

Size		Pipe End Separation Allowable <sup>2</sup>	Bolt/Nut		Dimensions								Weight	
Nominal inches mm	Actual Outside Diameter inches mm		Qty.	Size inches mm	Preassembled				Assembled Joint				Approx. (Each) lb kg	
					YL inches mm	YB inches mm	X inches mm	Z inches mm	YL inches mm	YB inches mm	X inches mm	Z inches mm		
1 DN25 x DN15	1/2 DN15	1.315 33.7 x 0.840 21.3	.13 3.3	1	5/16 x 1 1/8	1.36 34.6	1.66 42.1	2.18 55.3	1.17 29.7	1.37 34.7	1.73 44.0	1.97 50.0	1.17 29.7	.36 .16
	3/4 DN20	1.050 26.9	.13 3.3	1	5/16 x 1 1/8	1.36 34.6	1.66 42.1	2.18 55.3	1.17 29.7	1.37 34.7	1.73 44.0	1.97 50.0	1.17 29.7	.36 .16
	1 DN25	1.315 33.7	.13 3.3	1	5/16 x 1 1/8	1.36 34.6	1.66 42.1	2.18 55.3	1.17 29.7	1.37 34.7	1.73 44.0	1.97 50.0	1.17 29.7	.36 .16

<sup>2</sup> The allowable pipe separation dimension shown is for system layout purposes only. FireLock™ sprinkler couplings are considered rigid connections and will not accommodate expansion or contraction of the piping system.

## 5.0 PERFORMANCE







### Listings/Approval

The information provided below is based on the latest listing and approval data at the time of publication. Listings/Approvals are subject to change and/or additions by the approvals agencies. Contact Victaulic for performance on other pipe and the latest listings and approvals.

Size	UL	FM
<b>Nominal</b>		
inches	psi	psi
mm	kPa	kPa
1 DN25 x DN15	250	175
	1725	1205
	175	175
3/4 DN20	1205	1205
1 DN25	175	175
	1205	1205

## 6.0 NOTIFICATIONS

**⚠ WARNING**

- Read and understand all instructions before attempting to install, remove, adjust, or maintain any Victaulic piping products.**
- Depressurize and drain the piping system before attempting to install, remove, adjust, or maintain any Victaulic piping products.**
- Wear safety glasses, hardhat, and foot protection.**

**Failure to follow these instructions could result in death or serious personal injury and property damage.**

## 7.0 REFERENCE MATERIALS

- [05.01: Seal Selection Guide](#)
- [10.54 Firelock™ Innovative Groove System](#)
- [25.14: Victaulic FireLock™ IGS™ Groove Specifications](#)
- [41.01 Victaulic® FireLock™ Series FL-QR](#)
- [41.02 Victaulic® FireLock™ Series FL-QR/SW](#)
- [41.51 Victaulic® FireLock™ Series FL-SR](#)
- [41.52 Victaulic® FireLock™ Series FL-SR/SW](#)
- [44.01 Victaulic® FireLock™ Series FL-QR/ST](#)
- [44.11 Victaulic® FireLock™ Series FL-QR/ST/ESFR](#)
- [44.12 Victaulic® FireLock™ Series FL-QR/ST/ESFR](#)
- [44.13 Victaulic® FireLock™ Series FL-QR/ST/ESFR](#)
- [44.21 Victaulic® FireLock™ Series FL-QR/ST/INT](#)
- [44.51 Victaulic® FireLock™ Series FL-SR/ST](#)
- [44.61 Victaulic® FireLock™ Series FL-SR/ST/CMSA](#)
- [44.71 Victaulic® FireLock™ Series FL-SR/ST/INT](#)
- [45.01 Victaulic® FireLock™ Model FL-QR/DRY](#)
- [45.02 Victaulic® FireLock™ Model FL-QR/DRY/SW](#)
- [45.03 Victaulic® FireLock™ Model FL-QR/DRY/C](#)
- [45.04 Victaulic® FireLock™ Series FL-QR/DRY/ST](#)
- [45.05 Victaulic® FireLock™ Series FL-QR/DRY/VSW](#)
- [45.51 Victaulic® FireLock™ Model FL-SR/DRY](#)
- [45.52 Victaulic® FireLock™ Model FL-SR/DRY/SW](#)
- [45.53 Victaulic® FireLock™ Model FL-SR/DRY/C](#)
- [45.54 Victaulic® FireLock™ Series FL-SR/DRY/ST](#)
- [45.55 Victaulic® FireLock™ Series FL-SR/DRY/VSW](#)
- [I-V9: Installation Instructions FireLock™ IGS Installation-Ready Style V9 Rigid Coupling](#)
- [I-40: FireLock™ Automatic Sprinklers Installation Manual](#)

### User Responsibility for Product Selection and Suitability

Each user bears final responsibility for making a determination as to the suitability of Victaulic products for a particular end-use application, in accordance with industry standards and project specifications, and the applicable building codes and related regulations as well as Victaulic performance, maintenance, safety, and warning instructions. Nothing in this or any other document, nor any verbal recommendation, advice, or opinion from any Victaulic employee, shall be deemed to alter, vary, supersede, or waive any provision of Victaulic Company's standard conditions of sale, installation guide, or this disclaimer.

### Intellectual Property Rights

No statement contained herein concerning a possible or suggested use of any material, product, service, or design is intended, or should be construed, to grant any license under any patent or other intellectual property right of Victaulic or any of its subsidiaries or affiliates covering such use or design, or as a recommendation for the use of such material, product, service, or design in the infringement of any patent or other intellectual property right. The terms "Patented" or "Patent Pending" refer to design or utility patents or patent applications for articles and/or methods of use in the United States and/or other countries.

### Note

This product shall be manufactured by Victaulic or to Victaulic specifications. All products to be installed in accordance with current Victaulic installation/assembly instructions. Victaulic reserves the right to change product specifications, designs and standard equipment without notice and without incurring obligations.

### Installation

Reference should always be made to the Victaulic installation handbook or installation instructions of the product you are installing. Handbooks are included with each shipment of Victaulic products, providing complete installation and assembly data, and are available in PDF format on our website at [www.victaulic.com](http://www.victaulic.com).

### Warranty

Refer to the Warranty section of the current Price List or contact Victaulic for details.

### Trademarks

*Victaulic* and all other Victaulic marks are the trademarks or registered trademarks of Victaulic Company, and/or its affiliated entities, in the U.S. and/or other countries.