
Hole Cut Piping System



1.0 PRODUCT DESCRIPTION

The bolted mechanical branch connection concept was developed by Victaulic to provide a fast, easy mid-pipe outlet without welding. A hole is first cut or drilled in the pipe to receive the outlet. Positioning in the hole is enhanced with either a locating collar (Styles 920, 920N and 929) or a toe and heel (Styles 923 and 924) and provides a smooth outlet area for maximum flow characteristics.

The gasket is molded to conform to the pipe O.D. and is of pressure-responsive design. Gasket seal is further enhanced by pressure or vacuum in the line.

Styles 920, 920N and 929 are ideal for a variety of branch connections. Styles 923 and 924 provide a weldless connection for a variety of gauges, drains and thermometers.

Victaulic hole cut products must be installed on the true centerline of the pipe. Vic Hole Cutting Tools are recommended for preparing pipe to receive all Victaulic hole cut products.



Styles 920 and 920N



Style 920 Cross



Style 920 Threaded Outlet

ALWAYS REFER TO ANY NOTIFICATIONS AT THE END OF THIS DOCUMENT REGARDING PRODUCT INSTALLATION, MAINTENANCE OR SUPPORT.

System No.	Location	
Submitted By	Date	

Spec Section	Paragraph	
Approved	Date	







PRODUCT DESCRIPTION (Continued) 1.0



Provides a bolted branch connection



Locating collar assures permanent connection



Fast, easy preparation




Combines for crosstype connection

Vic-Let[™] Style 923 and Vic-O-Well[™] Style 924



Weldless connection for guages, drains, thermometers



Toe and heel engage inside of pipe



Easy one nut assembly



No welding – no special assembly tools

2.0 **CERTIFICATION/LISTINGS**







• Refer to submittal 10.01: Victaulic Fire Protection Approval Reference Guide for more details.

3.0 PERFORMANCE

Flow Data


Flow test data has shown that the total head loss between point (1) and (2) for the Style 920, 920N and 929 Mechanical-T® fittings can best be expressed in terms of the pressure difference across the inlet and branch. The pressure difference can be obtained from the relationship below.

C_v and K_v Values

Values for flow of water at +60°F/+16°C are shown in the table below.

Formulas for C_V/K_V Values:

$$\begin{array}{ll} \Delta P = \frac{Q^2}{C_v^2} & \textbf{Where:} \\ Q = \text{Flow (GPM)} \\ \Delta P = \text{Pressure Drop (psi)} \\ Q = C_v \times \sqrt{\Delta P} & C_v = \text{Flow Coefficient} \end{array}$$



Exaggerated for clarity

$\Delta P = Q^2$	Where:
K, 2	$Q = Flow (m^3/hr)$
v	$\Delta P = Pressure Drop (Bar)$
$Q = K_v \times \sqrt{\Delta P}$	K, = Flow Coefficient

Outlet Size		Equivalent Length of Outlet Size Schedule 40 Carbon Steel Pipe (per UL 213, Sec. 16) (C = 120) ¹ ft		Cv/Kv Values	
Nominal Size	Actual Outside Diameter	Grooved	Threaded	Grooved	Threaded
inches DN	inches mm				
½ DN15	0.840 21.3	-	2	-	11.0 9.4
³ / ₄ DN20	1.050 26.9	-	4	-	16.0 13.7
1 DN25	1.315 33.7	-	8	-	21.0 18.0
1¼ DN32	1.660 42.4	5½	6	50.0 42.9	48.0 41.1
1½ DN40	1.900 48.3	11	11	53.6 45.4	53.0 45.4
2 DN50	2.375 60.3	9	101/2	112.0 96.0	104.0 89.1
2½	2.875 73.0	20	121/2	119.0 102.0	150.0 128.5
DN65	3.000 76.1	16 ²	-	161.0 138.1	-
3 DN80	6.500 88.9	14	151/2	249.0 213.4	237.0 203.1
4 DN100	4.500 114.3	20	22	421.0 360.8	401.0 343.6

¹ Hazen-Williams coefficient of friction is 120.



 $^{^{2}\,\,}$ Pipe with a wall thickness of 0.165 in/4.2 mm.

User Responsibility for Product Selection and Suitability

Each user bears final responsibility for making a determination as to the suitability of Victaulic products for a particular end-use application, in accordance with industry standards and project specifications, and the applicable building codes and related regulations as well as Victaulic performance, maintenance, safety, and warning instructions. Nothing in this or any other document, nor any verbal recommendation, advice, or opinion from any Victaulic employee, shall be deemed to alter, vary, supersede, or waive any provision of Victaulic Company's standard conditions of sale, installation guide, or this disclaimer.

Intellectual Property Rights

No statement contained herein concerning a possible or suggested use of any material, product, service, or design is intended, or should be constructed, to grant any license under any patent or other intellectual property right of Victaulic or any of its subsidiaries or affiliates covering such use or design, or as a recommendation for the use of such material, product, service, or design in the infringement of any patent or other intellectual property right. The terms "Patented" or "Patent Pending" refer to design or utility patents or patent applications for articles and/or methods of use in the United States and/or other countries.

Note

This product shall be manufactured by Victaulic or to Victaulic specifications. All products to be installed in accordance with current Victaulic installation/assembly instructions. Victaulic reserves the right to change product specifications, designs and standard equipment without notice and without incurring obligations.

Installation

Reference should always be made to the Victaulic installation handbook or installation instructions of the product you are installing. Handbooks are included with each shipment of Victaulic products, providing complete installation and assembly data, and are available in PDF format on our website at www.victaulic.com.

Warranty

Refer to the Warranty section of the current Price List or contact Victaulic for details.

Trademarks

Victaulic and all other Victaulic marks are the trademarks or registered trademarks of Victaulic Company, and/or its affiliated entities, in the U.S. and/or other countries.

11.01 1670 Rev E Updated 06/2016 © 2016 Victaulic Company. All rights reserved.

