

Victaulic Strapless Outlet

Style 923




11.05



NPT & BSPT Models



BSPP Model



Patented Design

1.0 PRODUCT DESCRIPTION

Available Sizes

- 4 – 8”/DN100 – DN200
- 10”/DN250 and larger

Maximum Working Pressure

- 4 – 8”/DN100 – DN200: 300 psi/2068 kPa for Schedule 40 steel pipe
- 10”/DN250 and larger: 300 psi/2068 kPa for Schedules 10 and 40 steel pipe
- 4 – 12”/DN100 – DN300: UL/ULC Listed for fire protection services at 175 psi/1207 kPa

Function

- Provides fast, easy pipe outlet without the need for a strap or lower housing to wrap around the pipe
- Main body casting has an internal lug which inserts into a hole cut in the pipe and grips against the pipe's inside wall
- Tightened nut on the main body forces the gasket and containing collar against the pipe's outside surface, creating a rigid joint

2.0 CERTIFICATION/LISTINGS



EN 10311
CPR (EU)
No. 305/2011



BS EN 10311
CPR (UK)
2019 No. 465

ALWAYS REFER TO ANY NOTIFICATIONS AT THE END OF THIS DOCUMENT REGARDING PRODUCT INSTALLATION, MAINTENANCE OR SUPPORT.



3.0 SPECIFICATIONS – MATERIAL

Housing: Ductile iron conforming to ASTM A536, Grade 65-45-12, painted black. Ductile iron conforming to ASTM A395, Grade 65-45-15, is available upon special request.

Collar: Hot rolled, pickled and oiled steel, conforming to ASTM A569, zinc electroplated to ASTM B633.

Bushing: Brass per UNS C37700.

Seat/Liner: (specify choice¹)

Grade “E” EPDM

EPDM (Green stripe color code). Temperature range –30°F to +230°F/–34°C to +110°C. May be specified for hot water service within the specified temperature range plus a variety of dilute acids, oil-free air and many chemical services.


Grade “T” Nitrile

Nitrile (Orange stripe color code). Temperature range –20°F to +180°F/–29°C to +82°C. May be specified for petroleum products, hydrocarbons, air with oil vapors, vegetable and mineral oils within the specified temperature range; not compatible for hot dry air over +140°F/+60°C and water over +150°F/+66°C. NOT COMPATIBLE FOR USE WITH HOT WATER SERVICES OR STEAM SERVICES.

¹ Services listed are General Service Guidelines only. It should be noted that there are services for which these gaskets are not compatible. Reference should always be made to the latest [Victaulic Gasket Selection Guide](#) for specific gasket service guidelines and for a listing of services which are not compatible.

4.0 DIMENSIONS

Style 923 Strapless Outlet



	Size				Dimensions							Weight	
	Nominal	Actual Outside Diameter			Hole Dimensions		Style 923 Dimensions						
		Run x Branch inches DN	Run x Branch inches mm			Hole Saw Size inches mm	Max. Permissible Diameter inches mm	T ³ inches mm	X inches mm	X ₁ inches mm	X ₂ inches mm		Y ⁴ inches mm
NPT & BSPT Models	4 – 8 DN100 – DN200 ^x	½ DN15	4.500 – 8.625 114.3 – 219.1 ^x	0.840 21.3	1.50 38	1.56 40	2.47 63	3.00 76	–	–	3.09 78	1.9 0.9	
		¾ DN20		1.050 26.9	1.50 38	1.56 40	2.44 62	3.00 76	–	–	3.09 78	1.6 0.7	
		10 and larger DN250 and larger ^x		½ DN15	10.750 and larger 273.0 mm and larger ^x	0.840 21.3	1.50 38	1.56 40	2.47 63	3.00 76	–	–	3.00 76
	¾ DN20	1.050 26.9	1.50 38	1.56 40		2.44 62	3.00 76	–	–	3.00 76	1.6 0.7		
	BSPP Model	4 – 8 ² DN100 – DN200 ^x	½ DN15	4.500 – 8.625 114.3 – 219.1 ^x		0.840 21.3	1.50 38	1.56 40	2.47 63	–	4.50 114	3.00 76	3.09 78
			¾ DN20		1.050 26.9	1.50 38	1.56 40	2.44 62	–	4.50 114	3.00 76	3.09 78	1.8 0.8
10 and larger ² DN250 and larger ^x			½ DN15		10.750 and larger 273.0 mm and larger ^x	0.840 21.3	1.50 38	1.56 40	2.47 63	–	4.50 114	3.00 76	3.00 76
	¾ DN20	1.050 26.9	1.50 38	1.56 40		2.44 62	–	4.50 114	3.00 76	3.00 76	1.8 0.8		

² BSPP outlet, with BSPT male x BSPP female threaded bushing

³ Inside wall of run to end of probe

⁴ Width of collar is as supplied, width assembled changes due to collar deformation at assembly.

5.0 PERFORMANCE

Style 923 Strapless Outlet

Size		Actual Outside Diameter		Maximum Working Pressure ⁵⁻⁷
Nominal Run x Branch inches DN		Run x Branch inches mm		
4 – 8 DN100 – DN200	x ½ DN15	4.500 – 8.625 114.3 – 219.1	x 0.840 21.3	300 2068
	x ¾ DN20		1.050 26.9	300 2068
	10 and larger DN250 and larger	x ½ DN15	10.750 and larger 273.0 mm and larger	x 0.840 21.3
	x ¾ DN20	1.050 26.9		300 2068

⁵ On 4 – 8”/DN100 - DN200 Schedule 40 pipe and 10”/DN250 and larger Schedules 10 – 40 pipe.

⁶ Pressure rating is for Style 923 outlet only. Pipe used must also be rated at this pressure or higher.







⁷ BSPP model requires the use of a face seal per ISO 228-1.

NOTES

- Flow area equivalent to ¾”/20 mm pipe. Accepts 7/16”/11 mm diameter pipe.
- Style 923 provides flow characteristics in accordance with UL-213.

6.0 NOTIFICATIONS

⚠ WARNING

- Read and understand all instructions before attempting to install, remove, adjust, or maintain any Victaulic piping products.
- Depressurize and drain the piping system before attempting to install, remove, adjust, or maintain any Victaulic piping products.
- Wear safety glasses, hardhat, and foot protection.

Failure to follow these instructions could result in death or serious personal injury and property damage.

DUE TO DEFORMATION OF THE COLLAR, THE VICTAULIC STYLE 923 STRAPLESS OUTLET SHOULD NOT BE RE-USED AFTER INITIAL INSTALLATION.

7.0 REFERENCE MATERIALS

[I-100: Victaulic Field Installation Handbook](#)

User Responsibility for Product Selection and Suitability

Each user bears final responsibility for making a determination as to the suitability of Victaulic products for a particular end-use application, in accordance with industry standards and project specifications, and the applicable building codes and related regulations as well as Victaulic performance, maintenance, safety, and warning instructions. Nothing in this or any other document, nor any verbal recommendation, advice, or opinion from any Victaulic employee, shall be deemed to alter, vary, supersede, or waive any provision of Victaulic Company’s standard conditions of sale, installation guide, or this disclaimer.

Intellectual Property Rights

No statement contained herein concerning a possible or suggested use of any material, product, service, or design is intended, or should be construed, to grant any license under any patent or other intellectual property right of Victaulic or any of its subsidiaries or affiliates covering such use or design, or as a recommendation for the use of such material, product, service, or design in the infringement of any patent or other intellectual property right. The terms “Patented” or “Patent Pending” refer to design or utility patents or patent applications for articles and/or methods of use in the United States and/or other countries.

Note

This product shall be manufactured by Victaulic or to Victaulic specifications. All products to be installed in accordance with current Victaulic installation/assembly instructions. Victaulic reserves the right to change product specifications, designs and standard equipment without notice and without incurring obligations.

Installation

Reference should always be made to the Victaulic installation handbook or installation instructions of the product you are installing. Handbooks are included with each shipment of Victaulic products, providing complete installation and assembly data, and are available in PDF format on our website at www.victaulic.com.

Warranty

Refer to the Warranty section of the current Price List or contact Victaulic for details.

Trademarks

Victaulic and all other Victaulic marks are the trademarks or registered trademarks of Victaulic Company, and/or its affiliated entities, in the U.S. and/or other countries.