

Victaulic Potable Water Entry Gate Valves

Series 771P, 772P



17.47



Series 771P



Series 772P

1.0 PRODUCT DESCRIPTION

Available sizes

- 2" – 12"/DN50 – DN300

Maximum Working Pressure

- cULus Listed, FM Approved up to 300 psi/2068 kPa/20 bar.

Maximum Working Temperature

- 140 °F/60 °C

Function

- OS&Y: Provides positive shutoff and a quick visual indicator of open or closed position.
- NRS: Provides remote shutoff service, for applications behind a wall or buried.

2.0 CERTIFICATION/LISTINGS



UL Classified in accordance with ANSI/NSF 61 and ANSI/NSF 372.

ALWAYS REFER TO ANY NOTIFICATIONS AT THE END OF THIS DOCUMENT REGARDING PRODUCT INSTALLATION, MAINTENANCE OR SUPPORT.



3.0 SPECIFICATIONS – MATERIAL

Series 771P OS&Y Gate Valve

Body: Ductile iron conforming to ASTM A536 grade 65-45-12

Body/Bonnet coating: Fusion bonded epoxy, RAL 3000 color – Red

Wedge: Ductile iron conforming to ASTM A536 grade 65-45-12, EPDM encapsulated

Stem: 304 Stainless steel

Gasket: EPDM

Bonnet: Ductile iron conforming to ASTM A536 grade 65-45-12

Gland: Ductile iron conforming to ASTM A536 grade 65-45-12

Stem Nut: Bronze conforming to C95200

O-Ring: Nitrile

Bolt: 304 Stainless steel

Packing: Graphite

Washer: 304 Stainless steel

Nut: 316 Stainless steel

Stem Washer: Brass

Handwheel: Ductile iron conforming to ASTM A536 grade 65-45-12

Handwheel Nut: Ductile iron conforming to ASTM A536 grade 65-45-12

Pin: 304 Stainless steel

Wedge nut: 304 Stainless steel

Plug: Brass

Series 772P NRS Gate Valve

Body: Ductile iron conforming to ASTM A536 grade 65-45-12

Body/Bonnet coating: Fusion bonded epoxy, RAL 3000 color – Red

Wedge: Ductile iron conforming to ASTM A536 grade 65-45-12, EPDM encapsulated

Wedge Nut: Bronze conforming to C95200

Stem: 304 Stainless steel

Gasket: EPDM

Bonnet: Ductile iron conforming to ASTM A536 grade 65-45-12

Thrust Collar: Bronze conforming to C95200

O-ring: Nitrile

Gland: Ductile iron conforming to ASTM A536 grade 65-45-12

Bolt: 304 Stainless steel

Dustproof Ring: Nitrile

Indicator Post Flange: Ductile iron conforming to ASTM A536 grade 65-45-12

Washer: 304 Stainless steel


Operating Nut: Ductile iron conforming to ASTM A536 grade 65-45-12

NOTE


- Series 772P Gate valves can be utilized with the Series 773 wall-post indicator and Series 774 upright indicator.

4.0 DIMENSIONS

Series 771P OS&Y and Series 772P NRS Grooved x Grooved



Series 771P OS&Y





Series 772P NRS

Size		Dimensions				Weight
Nominal inches DN	Actual Outside Diameter inches mm	E to E inches mm	ØA inches mm	H inches mm	H Closed inches mm	Approx. (Each) lb kg
2 DN50	2.375 60.3	7.00 178	7.30 185	15.40 391	13.2 335.3	26.5 12.0
2½	2.875 73.0	7.50 191	7.30 185	17.10 434	14.4 365.8	29.3 13.3
3 DN80	3.500 88.9	8.00 203	10.00 254	19.90 505	16.5 419.1	38.6 17.5
4 DN100	4.500 114.3	9.00 229	10.00 254	22.40 569	18.1 459.7	66.1 30.0
6 DN150	6.625 168.3	10.50 267	12.00 305	30.10 765	24 609.6	100.3 45.5
8 DN200	8.625 219.1	11.50 292	14.00 356	38.00 965	30 762	149.9 68.0
10 DN250	10.750 273.0	13.00 330	17.50 445	44.90 1140	35.2 894	249.1 113.0
12 DN300	12.750 323.9	14.00 356	17.50 445	53.00 1346	40.8 1036.3	330.7 150.0







Size		Dimensions				Weight
Nominal inches DN	Actual Outside Diameter inches mm	E to E inches mm	ØA inches mm	H inches mm	HO inches mm	Approx. (Each) lb kg
2 DN50	2.375 60.3	7.00 178	12.00 305	11.40 290	8.10 206	23.8 10.8
2½	2.875 73.0	7.50 191	12.00 305	11.80 300	8.60 218	24.8 11.3
3 DN80	3.500 88.9	8.00 203	12.00 305	13.00 330	9.80 249	29.9 13.6
4 DN100	4.500 114.3	9.00 229	12.00 305	14.40 366	11.20 284	61.7 28.0
6 DN150	6.625 168.3	10.50 267	12.00 305	18.10 460	14.90 378	95.9 43.5
8 DN200	8.625 219.1	11.50 292	12.00 305	21.50 546	18.20 462	145.5 66.0
10 DN250	10.750 273.0	13.00 330	12.00 305	25.00 635	21.70 551	229.9 104.3
12 DN300	12.750 323.9	14.00 356	12.00 305	28.30 719	25.00 635	321.4 145.8

5.0 PERFORMANCE

Series 771P OS&Y and 772P NRS
Grooved x Grooved
Friction Loss



6.0 NOTIFICATIONS

 WARNING	
    	<ul style="list-style-type: none"> • Read and understand all instructions before attempting to install any Victaulic products. • Always verify that the piping system has been completely depressurized and drained immediately prior to installation, removal, adjustment, or maintenance of any Victaulic products. • Wear safety glasses, hardhat, and foot protection. <p>Failure to follow these instructions could result in death or serious personal injury and property damage.</p>
<ul style="list-style-type: none"> • These products shall be used only in fire protection systems that are designed and installed in accordance with current, applicable National Fire Protection Association (NFPA 13, 13D, 13R, etc.) standards, or equivalent standards, and in accordance with applicable building and fire codes. These standards and codes contain important information regarding protection of systems from freezing temperatures, corrosion, mechanical damage, etc. • The installer shall understand the use of this product and why it was specified for the particular application. • The installer shall understand common industry safety standards and potential consequences of improper product installation. • It is the system designer's responsibility to verify suitability of materials for use with the intended fluid media within the piping system and external environment. • The material specifier shall evaluate the effect of chemical composition, pH level, operating temperature, chloride level, oxygen level, and flow rate on materials to confirm system life will be acceptable for the intended service. <p>Failure to follow installation requirements and local and national codes and standards could compromise system integrity or cause system failure, resulting in death or serious personal injury and property damage.</p>	

7.0 REFERENCE MATERIALS

- [05.01: Victaulic Seal Selection Guide - Elastomeric Seal Construction](#)
- [10.01 Victaulic Fire Protection Certifications/Listings Reference Guide](#)
- [10.72: Victaulic Gate Valves Series 771A, 772A](#)
- [10.92: Victaulic FireLock™ Gate Valves Series 771 and 772](#)
- [24.01: Victaulic Pipe End Preparation](#)
- [26.01: Victaulic Design Data](#)
- [29.01: Victaulic Terms and Conditions of Sale](#)
- [I-100: Victaulic Field Installation Handbook](#)

User Responsibility for Product Selection and Suitability

Each user bears final responsibility for making a determination as to the suitability of Victaulic products for a particular end-use application, in accordance with industry standards and project specifications, as well as Victaulic performance, maintenance, safety, and warning instructions. Nothing in this or any other document, nor any verbal recommendation, advice, or opinion from any Victaulic employee, shall be deemed to alter, vary, supersede, or waive any provision of Victaulic Company's standard conditions of sale, installation guide, or this disclaimer.

Intellectual Property Rights

No statement contained herein concerning a possible or suggested use of any material, product, service, or design is intended, or should be construed, to grant any license under any patent or other intellectual property right of Victaulic or any of its subsidiaries or affiliates covering such use or design, or as a recommendation for the use of such material, product, service, or design in the infringement of any patent or other intellectual property right. The terms "Patented" or "Patent Pending" refer to design or utility patents or patent applications for articles and/or methods of use in the United States and/or other countries.

Note

This product shall be manufactured by Victaulic or to Victaulic specifications. All products to be installed in accordance with current Victaulic installation/assembly instructions. Victaulic reserves the right to change product specifications, designs and standard equipment without notice and without incurring obligations.

Installation

Reference should always be made to the Victaulic installation handbook or installation instructions of the product you are installing. Handbooks are included with each shipment of Victaulic products, providing complete installation and assembly data, and are available in PDF format on our website at www.victaulic.com.

Warranty

Refer to the Warranty section of the current Price List or contact Victaulic for details.

Trademarks

Victaulic and all other Victaulic marks are the trademarks or registered trademarks of Victaulic Company, and/or its affiliated entities, in the U.S. and/or other countries.