



1.0 PRODUCT DESCRIPTION

Available Sizes

- 2 – 8" / 50 – 200 mm

Pipe Material

- Types K, L, M and DWV hard drawn copper tubing

Maximum Working Pressure

- Fitting pressure ratings are equivalent to the pressure ratings of the joints consisting of a Victaulic Style 607 QuickVic™ Rigid Coupling or Style 641 *Vic-Flange* Adapter and Type of copper tubing (see section 7.0 for Reference Materials)

Application

- Connects tubing, provides change in direction and adapts sizes or components
- Full flow, standard radius wrought copper supplied roll grooved or bronze castings with “as cast” CTS grooves
- Exclusively for use with Victaulic Style 607 QuickVic™ Rigid Couplings or Victaulic Style 641 *Vic-Flange* Adapter for Copper

2.0 CERTIFICATION/LISTINGS



Victaulic copper fittings are UL Classified in accordance with NSF/ANSI/CAN 61 for cold +73°F/+23°C and hot +180°F/+82°C potable water service and NSF/ANSI 372 for lead content.

NOTE

- See [publication 02.06](#): Victaulic Approvals for Potable Water Products - ANSI/NSF 61 and ANSI/NSF 372.

ALWAYS REFER TO ANY NOTIFICATIONS AT THE END OF THIS DOCUMENT REGARDING PRODUCT INSTALLATION, MAINTENANCE OR SUPPORT.

3.0 SPECIFICATIONS – MATERIAL

Copper Fittings:

- Wrought copper per ASTM B75 C12200 or ASTM B152 C110001 and ANSI B16.22.
- Bronze sand cast conforming to UNS C89836.

Style 643 Adapter Nipple: Type L hard drawn copper tubing per ASTM B88.

¹ Applies to 6 x 4 No. 650 Concentric Reducer only.

4.0 DIMENSIONS


Elbows, Tee and Cap

No. 610 90° Elbow

No. 611 45° Elbow

No. 620 Tee

No. 660 Cap



Size		No. 610 90° Elbow		No. 611 45° Elbow		No. 620 Tee		No. 660 Cap	
Nominal inches	Actual inches mm	C to E inches mm	Approximate Weight (Each) lb kg	C to E inches mm	Approximate Weight (Each) lb kg	C to E inches mm	Approximate Weight (Each) lb kg	T inches mm	Approximate Weight (Each) lb kg
2	2.125 54.0	2.91 74	0.9 0.4	2.19 56	0.8 0.4	2.69 68	1.1 c 0.5	0.96 24	1.2 c 0.5
2½	2.625 66.7	3.31 84	1.3 0.6	2.31 59	1.1 0.5	3.20 81	1.8 c 0.8	0.96 24	1.4 c 0.6
3	3.125 79.4	3.81 97	4.1 1.9	2.59 66	1.6 0.7	3.52 89	3.2 c 1.5	0.96 24	1.4 c 0.6
4	4.125 104.8	4.75 121	4.3 2.0	3.19 81	3.4 1.5	4.25 108	6.1 c 2.8	0.96 24	2.4 c 1.1
5	5.125 130.2	5.94 151	15.0 c 6.8	3.25 83	10.0 c 4.5	5.94 151	18.5 c 8.4	0.96 24	3.5 c 1.6
6	6.125 155.6	6.94 176	20.0 c 9.1	3.63 92	13.0 c 5.9	6.94 176	25.5 c 11.6	0.96 24	4.2 c 1.9
8	8.125 206.4	7.75 197	26.0 c 11.8	4.25 108	15.6 c 7.1	7.75 197	45.0 c 20.4	-	-


c = Bronze casting; all others, wrought copper.

4.1 DIMENSIONS

Reducing Tee

No. 625 Grv. x Grv. x Grv.

No. 626 Grv. x Grv. x Cup



Size			No. 625 Grv. x Grv. x Grv.			No. 626 Grv. x Grv. x Cup				
Nominal inches	Actual Outside Diameter inches mm		C to E inches mm	C to B inches mm	Approx. Weight (Each) lb kg	C to E inches mm	C to B inches mm	Cup inches mm	Approx. Weight (Each) lb kg	
2 × 2 × ¾	2.125 54.0 × 2.125 54.0 ×	0.875 22.2	—	—	—	2.20 56	1.98 50	0.75 19	0.8 0.3	
		1.125 28.6	—	—	—	2.33 59	2.20 56	0.91 23	0.8 0.4	
		1.375 34.9	—	—	—	2.48 63	2.35 60	0.97 25	0.9 0.4	
		1.625 41.3	—	—	—	2.55 65	2.28 58	1.09 28	0.9 0.4	
		2.125 53.9	3.28 83	3.38 86	1.6 0.7	—	—	—	—	
2½ × 2½ × ¾	2.625 66.7 × 2.625 66.7 ×	0.875 22.2	—	—	—	2.26 57	2.23 57	0.75 19	1.0 0.5	
		1.125 28.6	—	—	—	2.40 61	2.40 61	0.91 23	1.2 0.5	
		1.375 34.9	—	—	—	2.52 64	2.57 65	0.97 25	1.2 0.6	
		1.625 41.3	—	—	—	2.70 69	2.68 68	1.09 28	1.3 0.6	
		2.125 53.9	3.28 83	3.38 86	1.6 0.7	—	—	—	—	
		2.625 66.7	3.25 83	3.50 89	2.4 c 1.1	—	—	—	—	
3 × 3 × ¾	3.125 79.4 × 3.125 79.4 ×	0.875 22.2	—	—	—	2.41 61	2.56 65	0.75 19	1.4 0.6	
		1.125 28.6	—	—	—	2.54 65	2.79 71	0.91 23	1.5 0.7	
		1.375 34.9	—	—	—	2.63 67	2.89 73	0.97 25	1.7 0.8	
		1.625 41.3	—	—	—	2.85 73	3.00 76	1.09 28	1.7 0.8	
		2.125 54.0	3.00 76	3.38 86	2.1 c 1.0	—	—	—	—	
		2.625 66.7	3.25 83	3.50 89	2.4 c 1.1	—	—	—	—	
		3.125 79.4	4.19 106	4.16 106	6.3 c 2.8	—	—	—	—	
4 × 4 × ¾	4.125 104.8 × 4.125 104.8 ×	0.875 22.2	—	—	—	3.04 77	2.97 75	0.75 19	2.8 1.2	
		1.125 28.6	—	—	—	3.10 79	3.22 82	0.91 23	2.9 1.3	
		1.375 34.9	—	—	—	3.25 83	3.47 88	0.97 25	3.0 1.4	
		1.625 41.3	—	—	—	3.35 85	3.65 93	1.09 28	3.2 1.4	
		2.125 54.0	3.66 93	4.13 105	5.3 c 2.4	—	—	—	—	
		2.625 66.7	3.94 100	4.06 103	5.8 c 2.6	—	—	—	—	
		3.125 79.4	4.19 106	4.16 106	6.3 c 2.8	—	—	—	—	
		3.625 92.7	4.49 114	4.46 113	7.3 c 3.3	—	—	—	—	

c = Bronze casting; all others, wrought copper.

4.1 DIMENSIONS (CONTINUED)

Reducing Tee

No. 625 Grv. x Grv. x Grv.

No. 626 Grv. x Grv. x Cup




Size		No. 625 Grv. x Grv. x Grv.			No. 626 Grv. x Grv. x Cup			Approx. Weight (Each)	
Nominal inches	Actual Outside Diameter inches mm	C to E inches mm	C to B inches mm	Approx. Weight (Each) lb kg	C to E inches mm	C to B inches mm	Cup inches mm	Approx. Weight (Each) lb kg	
5 x 5 x 3	5.125 x 5.125 130.2 x 130.2	3.125 79.4	4.63 118	5.4 c 2.5	—	—	—	—	
		4.125 104.8	4.56 116	8.8 c 4.0	—	—	—	—	
6 x 6 x 2½	6.125 x 6.125 155.6 x 155.6	2.625 66.7	5.13 130	6.7 c 3.0	—	—	—	—	
		3.125 79.4	5.19 132	8.1 c 3.7	—	—	—	—	
		4.125 104.8	5.13 130	9.8 c 4.4	—	—	—	—	
		5.125 130.2	5.19 132	11.3 c 5.1	—	—	—	—	

c = Bronze casting; all others, wrought copper.

4.2 DIMENSIONS

Nipple

No. 643 Copper Adapter Nipple





Size		No. 643 Adapter Nipple
Nominal inches	Actual inches mm	E to E inches mm
2	2.125 54.0	2.04 52
	2½	2.625 66.7
3	3.125 79.4	2.04 52
	4	4.125 104.8

4.3 DIMENSIONS

Concentric Reducer

No. 650 Grv. x Grv.

No. 652 Grv. x Cup



Size		No. 650 Grv. x Grv.		No. 652 Grv. x Cup			
Nominal inches	Actual Outside Diameter inches mm	E to E inches mm	Approx. Weight (Each) lb kg	E to E inches mm	Cup inches mm	Approx. Weight (Each) lb kg	
2 × 1	2.125 × 1.125 54.0 × 28.6	—	—	2.70 69	0.91 23	0.5 0.2	
	1 ¼	—	—	3.00 76	0.97 25	0.5 0.2	
	1 ½	—	—	2.94 75	1.09 28	0.5 0.2	
2½ × 1	2.625 × 1.125 66.7 × 28.6	—	—	3.25 83	0.91 23	0.8 0.4	
	1 ¼	—	—	3.52 89	0.97 25	0.6 0.3	
	1 ½	—	—	3.45 88	1.09 28	0.7 0.3	
	2	2.125 54.0	3.29 84	1.0 0.5	3.30 84	1.34 34	0.7 0.3
3 × 1 ½	3.125 × 1.625 79.4 × 41.3	—	—	3.68 93	1.09 28	1.1 0.5	
	2	2.125 54.0	2.50 64	1.0 c 0.4	4.10 104	1.34 34	1.0 0.4
	2 ½	2.625 66.7	3.38 86	0.9 0.4	—	—	
4 × 2	4.125 × 2.125 104.8 × 54.0	4.75 121	2.3 1.0	4.75 121	1.34 34	2.0 0.9	
	2 ½	2.625 66.7	3.00 76	2.0 c 0.9	—	—	
	3	3.125 79.4	3.38 86	2.5 1.1	—	—	
5 × 3	5.125 × 3.125 130.2 × 79.4	3.88 99	6.3 c 2.9	—	—	—	
	4	4.125 104.8	3.38 86	6.3 c 2.9	—	—	
6 × 3	6.125 × 3.125 155.6 × 79.4	4.38 111	6.4 c 2.9	—	—	—	
	4	4.125 104.8	3.88 99	6.5 c 2.9	—	—	
	5	5.125 130.2	3.38 86	6.7 c 3.0	—	—	
8 × 6	8.125 × 6.125 206.4 × 155.6	5.00 127	10.0 c 4.5	—	—	—	

c = Bronze casting; all others, wrought copper.

5.0 PERFORMANCE

Fitting pressure ratings are equivalent to the pressure ratings of the joints consisting of a Victaulic Style 607 QuickVic™ Rigid Coupling or Style 641 Vic-Flange Adapter and Type of copper tubing (see section 7.0 for Reference Materials).

Size	Type K ASTM B88			Type L ASTM B88			Type M ASTM B88			Type DWV ASTM B306		
	Nominal inches Actual Tubing mm	Wall Thickness inches mm	Max. Joint Work. Press. psi kPa	Max. Permis. End Load lb N	Wall Thickness inches mm	Max. Joint Work. Press. psi kPa	Max. Permis. End Load lb N	Wall Thickness inches mm	Max. Joint Work. Press. psi kPa	Max. Permis. End Load lb N	Wall Thickness inches mm	Max. Joint Work. Press. psi kPa
2 54.0	0.083 2.1	300 2065	1065 4737	0.070 1.8	300 2065	1065 4737	0.058 1.5	250 1725	890 3959	0.042 1.1	100 690	354 1575
2½ 66.7	0.095 2.4	300 2065	1625 7228	0.080 2.0	300 2065	1625 7228	0.065 1.7	250 1725	1350 6005	–	–	–
3 79.4	0.109 2.8	300 2065	2300 10231	0.090 2.3	300 2065	2300 10231	0.072 1.8	250 1725	1415 6294	0.045 1.1	100 690	765 3403
4 104.8	0.134 3.4	300 2065	4005 17815	0.110 2.8	300 2065	4005 17815	0.095 2.4	250 1725	3340 14857	0.058 1.5	100 690	1335 5938
5 130.2	0.160 4.1	300 2065	6190 27534	0.125 3.2	300 2065	6190 27534	0.109 2.8	200 1375	4125 18349	0.072 1.8	100 690	2060 9163
6 155.6	0.192 4.9	300 2065	8840 39322	0.140 3.6	300 2065	8840 39322	0.122 3.1	200 1375	5890 26200	0.083 2.1	100 690	2945 13100
8 206.4	0.271 6.9	300 2065	15550 69170	0.200 5.1	300 2065	15550 69170	0.170 4.3	200 1375	10370 46128	0.109 2.8	100 690	5180 23042

NOTE

- Working Pressure and End Load are total, from all internal and external loads, based on the indicated Type of hard drawn copper tubing, standard roll grooved in accordance with Victaulic specifications.

6.0 NOTIFICATIONS

- Victaulic CTS copper connection fittings in 2 – 8"/50 – 200 mm sizes are designed to be joined to roll grooved hard drawn (CTS) copper tubing meeting the requirements of ASTM B88.
- Victaulic Vic-Easy roll grooving tools VE272SFS, VE270FSD, VE268, VE416FSD and VE414MC can be used to roll groove Types K, L, M and DWV copper tubing from 2 – 8"/54.0 – 206.4 mm. The Vic-Easy VE226C can be used for 2 – 6"/54.0 – 155.6 mm copper tubing. The VE226C allows in-place manual grooving of 2 – 6"/54.0 – 155.6 mm copper tubing. Tools must be equipped only with Victaulic rolls designed specifically for grooving copper tube (color coded copper).
- A Go/No-Go Groove Diameter Cable for Copper Tube is available for checking groove diameters. See [publication 24.01](#): Victaulic Pipe Preparation Tools for more information.
- The Victaulic copper connection system is available in British Standard ([publication 22.08](#)); DIN Standard ([publication 22.09](#)); and Australian Standard ([publication 22.10](#)).

⚠ CAUTION

- DO NOT use grooving rolls intended for steel, stainless steel, aluminum, or PVC pipe. Failure to follow this instruction could cause joint leakage, resulting in property damage.**

7.0 REFERENCE MATERIALS

- [22.01: Victaulic Copper Connection Systems for Copper Tubing \(CTS\)](#)
- [22.03: Victaulic Style 641 Vic-Flange Adapter for Copper](#)
- [22.07: Victaulic Copper Testing Data](#)
- [22.08: Victaulic British Standard Copper Products Design](#)
- [22.09: Victaulic DIN Standard Copper Products Design Data](#)
- [22.10: Victaulic Australian Standard Copper Products](#)
- [22.13: Victaulic Style 607 QuickVic™ Rigid Coupling](#)
- [22.44: Victaulic Style 644 Installation-Ready™ Transition Coupling for Potable Water Applications](#)
- [24.01: Victaulic Pipe Preparation Tools](#)
- [I-600: Victaulic Field Assembly and Installation Instruction Handbook for Copper Products](#)

User Responsibility for Product Selection and Suitability

Each user bears final responsibility for making a determination as to the suitability of Victaulic products for a particular end-use application, in accordance with industry standards and project specifications, and the applicable building codes and related regulations as well as Victaulic performance, maintenance, safety, and warning instructions. Nothing in this or any other document, nor any verbal recommendation, advice, or opinion from any Victaulic employee, shall be deemed to alter, vary, supersede, or waive any provision of Victaulic Company's standard conditions of sale, installation guide, or this disclaimer.

Intellectual Property Rights

No statement contained herein concerning a possible or suggested use of any material, product, service, or design is intended, or should be construed, to grant any license under any patent or other intellectual property right of Victaulic or any of its subsidiaries or affiliates covering such use or design, or as a recommendation for the use of such material, product, service, or design in the infringement of any patent or other intellectual property right. The terms "Patented" or "Patent Pending" refer to design or utility patents or patent applications for articles and/or methods of use in the United States and/or other countries.

Note

This product shall be manufactured by Victaulic or to Victaulic specifications. All products to be installed in accordance with current Victaulic installation/assembly instructions. Victaulic reserves the right to change product specifications, designs and standard equipment without notice and without incurring obligations.

Installation

Reference should always be made to the Victaulic installation handbook or installation instructions of the product you are installing. Handbooks are included with each shipment of Victaulic products, providing complete installation and assembly data, and are available in PDF format on our website at www.victaulic.com.

Warranty

Refer to the Warranty section of the current Price List or contact Victaulic for details.

Trademarks

Victaulic and all other Victaulic marks are the trademarks or registered trademarks of Victaulic Company, and/or its affiliated entities, in the U.S. and/or other countries.