



中国船级社
CHINA CLASSIFICATION SOCIETY

证书编号/Certificate No.
WG21PTB00001_03

型式认可证书
CERTIFICATE OF TYPE APPROVAL

兹证明本证书所述制造厂具备按照下列标准的要求生产本证书所列产品的能力和条件。

This is to certify that the manufacturer stated in the certificate meets the requirements of the standards listed below and is available with the ability and conditions to produce the products described in the certificate.

制造厂/Manufacturer

Victaulic Company

地址/Address

4901 Kesslersville Road, Easton, PA 18040, USA

产品名称/Product

管系接头, 附件和阀
Pipe Couplings, Fittings and Valves
机械接头
Mechanical Joint

附加标志/Notations

无/Nil.

认可标准/Approval Standard

1. 中国船级社《钢质海船入级规范》(2018)及其修改通报第3篇第2章
Chapter 2, Part Three of China Classification Society Rules for Classification of Sea-Going Steel Ships 2018 and its Amendments

用于/Intended for

船舶与海上设施/Ships and Offshore Installations

证书有效期至/This Certificate is valid until 2025年02月12日/ Feb. 12, 2025

发证机构 中国船级社温哥华办事处
Issued by CCS Vancouver Office

签发日期 2021年02月05日
Date Feb. 05, 2021

本证书根据中国船级社规范和相关规定签发。所有证书作为一个整体, 必须同时使用。纸质证书每页均须由本社盖章方为有效, 电子证书含数字签名方为有效。本证书复印件无效。任何单位和个人均不应摘录或节选本证书的部分内容。有关方对所持证书的真实性有疑问时, 可以向我社检验机构咨询。This Certificate is issued pursuant to the Rules of the Society and related regulation. All pages of the certificate are taken as a whole and are used simultaneously. No paper certificate page is valid without bearing the stamp of the Society, no electronic certificates is valid without the digital signature, and no copied form of the certificate is regarded as valid. Any part of the certificate is not to be extracted or abridged by any unit or individual in any form. Related parties who are doubted about the authenticity of the certificate may inquire of the Society or its offices.

Form No. T01.

联系方式/Contact Us, 见本社官方网站/See official web site of the Society (<http://www.ccs.org.cn>)



UTN:P021-73734221

产品明细/Product Description

机械接头/Mechanical Joint (M0001)

名称/Name	属性(值)/Value	单位/Unit
产品名称/Product Name	Mechanical Grooved Couplings (Slip-on type)	
型号/Type	Style 005H Firelock Rigid Coupling; Style 07 Zero-Flex Rigid Coupling; Style 77 Standard Flexible Coupling; Style 75 Flexible Coupling; Style 741 Vic-Flange Adapter; Style 750 Reducing Coupling; Style 920 & 920N Mechanical-T Outlet; Style 99 Roust-A-Bout Rigid Coupling	
公称直径/Nominal Diameter	32-200; 40-300; 20-300; 25-200; 50-300; 50x25-200x150; 60.3x21.3-219.1x114.3; 40-200	mm
最大允许工作压力/Maximum Allowable Working Pressure	16	bar
设计温度/Design Temperature	EPDM: 0 to +110 Nitrile: 0 to +82	°C
壳体材料/Casing Material	Housing: Ductile iron Gasket: EPDM; Nitrile	

机械接头/Mechanical Joint (M0002)

名称/Name	属性(值)/Value	单位/Unit
产品名称/Product Name	Grooved End Fittings	
型号/Type	No.10 90 Elbow, No.11 45 Elbow, No.12 22.5 Elbow, No.13 11.25 Elbow, No.20 Tee, No.35 Cross; No.29M Tee with threaded Branch; No.100 and No.110 Long Radius Elbow-1/12 D; No.100 and No.110 Long Radius Elbow-3 D; No.60 Cap, No.40, 43, 43 Nipple; No.R-10 Reducing Base Support Elbows; No.41-ANSI 125, No.45-ANSI 150, No.46-ANSI 300, Flanged Adapter Nipples; No.50 Concentric/No.51 Eccentric Reducers; No.25 and No.29 Reducing Tees; No.52 Reducer Threaded Small; No.53, 54&55 Swaged Nipples; No.18 and 19 Adapter Elbows; No.27 Standpipe Tee; No.21 Bullhead Tee; No.80 Female Threaded Adapter; Style 730 Vic-Strainer; Style 732 Wye Type Vic-Strainer	
公称直径/Nominal Diameter	20-300	mm
最大允许工作压力/Maximum Allowable Working Pressure	16	bar
设计温度/Design Temperature	EPDM: 0 to +110 Nitrile: 0 to +82	°C
壳体材料/Casing Material	Ductile iron; Steel	



机械接头/Mechanical Joint (M0003)

名称/Name	属性(值)/Value	单位/Unit
产品名称/Product Name	Valves	
型号/Type	Series 761 Vic-300 MasterSeal Butterfly Valve; Series 716 Vic-Check Valve; Series 726 Vic-Ball Valve	
公称直径/Nominal Diameter	50-300; 65-300; 40-150	mm
最大允许工作压力/Maximum Allowable Working Pressure	16	bar
设计温度/Design Temperature	EPDM/Fluoroelastomer: 0 to +120 Nitrile: 0 to +82	°C
壳体材料/Casing Material	Ductile iron	

批准的图纸/Approved Drawings

图纸批准号/Drawings Approval No.: NYA99170011, NY04T170021, NY09T00001

产品认可试验报告/Approval Test Report

试验报告编号/Test Report No.: 09-0065
 试验报告日期/Test Report Date: 2009-01-14
 试验单位/Laboratory: Victaulic Engineering Laboratory
 试验单位地址/Test Address: Easton, PA, USA

认可后的产品检验方式/Method of Product Inspection after Approval

按规范只认可不进行产品检验的产品/The product approved only in term of the rules:
 认可后的产品检验由制造厂按本社批准的产品检验计划进行检验, 经检验合格后由制造厂签发合格证明, 并连同该产品的本社认可证书复印件一并交付用户, 制造厂对产品符合公约、法规、本社规范和本社认可的标准规定负责。
 After approval, product inspection should be carried out by the Manufacturer in accordance with the product inspection scheme approved by the Society. Upon satisfactory inspection, and the Quality Certificate issued by the Manufacturer should be provided to the purchaser together with the copy of the approval certificate issued by the Society. The manufacturer should take responsibility for the product being in compliance with the convention, statutory regulation, the Society rules and the standard accepted by the Society.

认可保持条件/Maintenance Requirements of Approval

1. 型式认可后, 如果产品及其重要零部件的设计、所用材料或制造方法有所改变, 且影响到产品的主要特性、特征; 或产品的性能指标有所更改, 且超过认可的范围, 则有关图纸和文件应经检验机构审批。并在检验机构认为必要时, 经本社检验人员见证有关试验和进行检查, 其结果应能证实仍符合认可条件。

After type approval, if there are changes to the design, materials used or manufacturing method of the product and important components and such changes affect major characteristics and properties of the product, or property indexes of the product are changed and exceed the scope of approval, related drawings and documents are to be examined and approved by the concerned survey office. Where deemed necessary by the survey office, the surveyor to the Society will go to witness relevant tests and conduct inspection and the results should be able to demonstrate compliance with the approval conditions.

2. 工厂的质量管理体系应保持有效运行, 并且与认可时一致。如果质量管理体系发生改变, 应经原体系认证机构审核并报本社批准。

The quality management system of the factory shall be ensure effective operation, and shall be the same as the situation of approval. If there are any changes to the quality management system, auditing of the original certification organization for quality management system and the society's approval shall be obtained.

3. 认可证书有效期内, 如果出现可能导致本社取消认可的情况, 工厂应及时采取有效的纠正措施。

Within the validity of the approval certificate, if cases occur that may cause the Society to withdraw the approval, the manufacturer should take corrective actions in a prompt and effective manner.

4. 在认可证书有效期内, 本社检验人员可在未经事先通知的情况下对工厂的产品制造过程进行审核, 以验证产品的生产是否符合业经本社批准的图纸和文件。工厂应予以配合。

Within the validity of the approval certificate, the surveyor to the Society may pay unannounced audit to the manufacturing process of the product in order to confirm whether it is in compliance with the drawings and documents approved by the Society. The factory should provide an active cooperation and necessary for the surveyor.

5. 如果属于获得型式认可B 模式证书, 且无需颁发船用产品证书/等效证明文件的情况, 证书获得者应接受本社每年一次的定期审核, 定期审核日为认可证书期满之日对应的每一周年日, 检查工作应在周年日的前后三个月内进行。

If belong to the situation of the product has type approval mode B certificate, and marine product certificate/equivalent document is not necessary, those who have obtained the certificate should be subject to periodical audit every year. The date of periodical audit shall be each anniversary date which corresponds to the date of expiry of the relevant certificate and the periodical audit shall be done within a time span of three months before and after the annual surveillance date.

备注/Remarks

1. 本证书由原型式认可证书 (No. WG17T00001_01) 换新并替代原证书。

This certificate is renewed from and supersedes the previous Type Approval Certificate No. WG17T00001_01.

2. 产品适用范围/Application of the Product

Marine system: General purpose such as fuel, lube and hydraulic oil system, pneumatic power and control, compressed air, air conditioning, fresh and sea water, sanitary system, etc.

The limitation should comply with the requirements of No.2.5.3 of Ch.2, Part 3 of CCS Rules.

The component selection and installation should follow the manufacturer's instruction.

3. 产品制造厂 /The product manufactory:

a. Victaulic Company

Easton Facility - 4901 Kesslersville Road, Easton, PA 18040, USA

Alburtis Facility - 8023 Quarry Road, Alburtis, PA 18011, USA

b. Victaulic Polska Sp. z o.o.

Ul. Niepodleglosci 8, 66-530 Drezdenko, Poland

c. Victaulic Piping Products (Dalian) Co. Ltd.

No. 13 Tie Shan Dong 2 Road, Dalian Development Area, Dalian 116630, China

4. 本社已审核了产品厂无石棉声明, 但本社的审核不免除产品厂按照合同关系向订货方保证产品无石棉的责任。

The declaration of asbestos-free submitted by manufacturer has been reviewed by the Society.

However, liability of the manufacturer to guarantee the products are asbestos-free to purchaser under contract will not be exempted.

中国船级社温哥华办事处
CCS Vancouver Office

