

SERIES GL-SR/10MM

STANDARD COVERAGE, STANDARD RESPONSE

UPRIGHT, PENDENT & RECESSED PENDENT SPRINKLERS

K-FACTOR: 60 METRIC

GENERAL DESCRIPTION

Globe Series GL-SR sprinklers are Listed Standard Response sprinklers which utilize a 5mm frangible glass bulb as the thermosensitive operating element. These sprinklers are available in upright, pendent, and recessed pendent orientations. They are Listed and Approved as Standard Coverage sprinklers and are to be installed in accordance with the guidelines of the appropriate Installation Standard being mandated by the AHJ (i.e. NFPA 13). These sprinklers are available in various K-factors, temperatures and finishes as shown. Recessed escutcheons are available (See Approvals Tables for appropriate sprinkler/escutcheon combinations and Listings).

OPERATION

Upon exposure to heat such as from a fire, the fluid in the bulb expands, compressing the air bubble within the bulb. When the air bubble can no longer compress, the fluid expansion causes breakage of the glass bulb, resulting in release of the water seat assembly, and discharge of water from the sprinkler.

TECHNICAL DATA

SIN

- Upright: GL4262
- Pendent, Recessed Pendent: GL4252

Approvals

- cULus
- See Approval Tables

Maximum Working Pressure

- 175 psi (12 bar)
- Factory tested to 500 psi (34 bar)

Minimum Operating Pressure


- 7 psi (48 kPa)

Temperature Rating

- See Approval Tables

Materials of Construction

- Frame - bronze • Deflector - brass • Screw - brass
- Lodgement Wire - stainless steel • Bulb seat - copper
- Spring - nickel alloy • Seal - teflon
- Bulb - glass with alcohol based solution, 5mm
- Escutcheon Assembly - carbon steel



FINISHES AND ACCESSORIES

Finishes

- Factory Bronze • Chrome • White Polyester
- Black Polyester - special order

Escutcheons

- Brass • Chrome • White Polyester • Black Polyester

Wrenches

- Standard • Recess • 1/2" NPT

NOTE:

Corrosion resistant coatings, where applicable, are utilized to extend the life of copper alloy sprinklers beyond that which would otherwise be expected when exposed to corrosive atmospheres. Although corrosion resistant coated sprinklers have passed the standard corrosion tests of the applicable approval agencies, the testing is not representative of all possible corrosive atmospheres. Consequently, it is recommended that the end user be consulted with respect to the suitability of these coatings for any given corrosive environment. The effects of ambient temperature, concentration of chemicals, humidity, and gas/chemical velocity, should be considered, as a minimum, along with the corrosive nature of the chemical to which the sprinklers will be exposed.

NOTE:

Users should refer to Globe's web site (www.globesprinkler.com) to ensure that the most recent technical literature is being utilized.

INSTALLATION

NOTICE

Do not install any bulb-type sprinkler if the bulb is cracked or there is loss of liquid from the bulb. Sprinklers should be tightened enough to obtain a leak-tight joint when water pressure is applied and/or hydrostatic test is performed. Sprinklers should not be overtightened as this can result in distortion and subsequent leakage. It is recommended not to exceed 14 ft.-lb. (19.0 Nm) torque for 1/2 inch NPT sprinkler threads.

- Step1.** Sprinklers must be properly oriented.
- Step2.** With pipe thread sealant applied to the pipe threads, hand tighten the sprinkler into the sprinkler fitting. *Note: Do not grasp the sprinkler by the deflector.*
- Step3.** Wrench-tighten the sprinkler using only the appropriate wrench. Wrenches are only to be applied to the sprinkler wrench flats or wrench hex as applicable. *Note: Do not apply wrench to frame arms.*

TABLE A: UPRIGHT SPRINKLER APPROVALS

SIN	GL4262 (1/2)
ORIENTATION	UPRIGHT
K-FACTOR	4.2 (60 metric)
THREAD SIZE	(10mm)
HAZARD	LH
cULus Listed	135°F (57°C) 155°F (68°C) 175°F (79°C) 200°F (93°C) 286°F (141°C) 360°F (182°C)

- (1) cULus LISTED CORROSION RESISTANT WITH POLYESTER COATING.
- (2) cULus LISTED CORROSION RESISTANT WITH WAX COATING FOR 155°F (68°C) & 200°F (93°C) ONLY.




TABLE B: PENDENT SPRINKLER APPROVALS

SIN	GL4252 ^{(1) (2)}
ORIENTATION	PENDENT
K-FACTOR	4.2 (60 metric)
THREAD SIZE	(10mm)
HAZARD	L.H
cULus Listed	135°F (57°C) 155°F (68°C) 175°F (79°C) 200°F (93°C) 286°F (141°C) 360°F (182°C)

(1) cULus LISTED CORROSION RESISTANT WITH POLYESTER COATING.

(2) cULus LISTED CORROSION RESISTANT WITH WAX COATING FOR 155°F (68°C) & 200°F (93°C) ONLY.




TABLE C: RECESSED PENDENT SPRINKLER APPROVALS

SIN	GL4202 ^{(1) (2)}
ORIENTATION	RECESSED PEND.
K-FACTOR	4.2 (60 metric)
THREAD SIZE	10mm
HAZARD	L.H
cULus Listed	135°F (57°C) 155°F (68°C) 175°F (79°C) 200°F (93°C) 286°F (141°C) 360°F (182°C)

(1) cULus LISTED CORROSION RESISTANT SPRINKLER WITH POLYESTER COATING

(2) cULus / LPCB / CE APPROVED WITH 3/4" ADJUSTABLE RECESSED ESCUTCHEON





FIGURE 3: RECESSED ESCUTCHEON

TABLE D: STANDARD ESCUTCHEONS

19mm (3/4") ADJUSTABLE FRICTION FIT RECESSED ESCUTCHEON	
FINISH	10mm (ISO 7/1-R3/8)
Chrome	326231
White Polyester	326233-W

TABLE E: PART NUMBER SELECTION

PART NUMBER
SIN + TEMPERATURE + FINISH



*Note: All combinations may not be available.
Refer to Listing/Approval Tables for available listed combinations.*

CARE AND MAINTENANCE

Prior to installation, it is important to read and follow the "Sprinkler Caution" sheet (GFS-840) included with each box of sprinklers. This sheet is available on Globe's web site (www.globesprinkler.com).

Store sprinklers in a cool, dry place. Exposure to extreme heat will damage the thermal sensing element, possibly resulting in premature activation. Avoid direct sunlight.

Replace any sprinkler that shows any corrosion, damage, or loss of liquid from the glass bulb.

Do not attempt to paint or alter the sprinkler's coating in any manner after leaving the manufacturing plant.

Do not attach wiring, ropes, decorations or fixtures to a sprinkler.

Absence of an escutcheon, used to cover a ceiling hole, may delay sprinkler operation in a fire situation.

It is the owner's responsibility for inspection, testing and maintenance of the fire sprinkler system with all components and devices in accordance with the National Fire Protection Association Pamphlet 25 as well as any other requirements as set forth by the local Authority Having Jurisdiction (AHJ).

ORDERING INFORMATION

SPECIFY:

- SPRINKLER
 - Quantity • SIN • Orientation • Orifice • NPT • Temperature Rating
 - Finish • Part Number (See TABLE E)
- ESCUTCHEON
 - Quantity • Finish • Part Number (See TABLE D)
- WRENCH
 - Quantity • Part Number
 - 1/2" NPT Standard325390
 - 1/2" NPT Recess325391

GLOBE® PRODUCT WARRANTY

Globe agrees to repair or replace any of its manufactured products found to be defective in material or workmanship for a period of one year from date of shipment.

For specific details of our warranty please refer to Price List Terms and Conditions of Sale (Our Price List).

