



# QUICKVIC SD<sup>TM</sup> INSTALLATION-READY<sup>TM</sup> SYSTEM


**MOST EFFICIENT AND ECONOMICAL WAY TO JOIN  
1/2" THROUGH 2" CARBON STEEL PIPING SYSTEMS**

Available in sizes 1/2" – 2" | DN15 – DN50

For use on Schedules 5 – 80 carbon steel pipe

Up to +250°F | +120°C with EPDM gasket

300 psi | 2068 kPa | 21 bar



[victaulic.com](http://victaulic.com) | [quickvicsd.com](http://quickvicsd.com)

PB-QVSD 10293 REV I 10/2020

Victaulic and all other Victaulic marks are the trademarks or registered trademarks of Victaulic Company, and/or its affiliated entities, in the U.S. and/or other countries. All other trademarks listed herein are the property of their respective holders, in the U.S. and/or other countries. The terms "Patented" or "Patent Pending" refer to design or utility patents or patent applications for articles and/or methods of use in the United States and/or other countries.  
© 2020 VICTAULIC COMPANY. ALL RIGHTS RESERVED.

- Plain end pipe connection
- Repositionable and reusable – Reduces material and labor waste
- Patented "Leak-If-Not-Tightened" technology during initial installation; Designed not to seal until coupling/fitting is mechanically secured on the pipe
- Corrosion-resistant, high strength stainless steel retainer
- No loose parts
- Visual verification of proper installation
  - Bolt pad to bolt pad assembly
  - Retainer inspection window
- Product installs with common jobsite tools
- PC3110 Cut & Mark Tool – Provides knurled witness mark to verify proper insertion depth and facilitate post-installation inspection
- Also for use on 6061-T6 aluminum pipe conforming to ASTM B241 (Schedule 40 only)