

# Victaulic **Vortex**<sup>TM</sup>

Hybrid Fire Extinguishing System



# Victaulic Vortex™

## Hybrid Fire Extinguishing System


### THE WORLD'S FIRST HYBRID FIRE EXTINGUISHING SYSTEM

The Victaulic Vortex™ hybrid fire extinguishing system is built on more than 100 years of Victaulic innovation and product development experience; providing the best capabilities of both water mist and inert gas systems.

Ease of design, minimal wetting and advanced fire suppression capabilities all give the *Victaulic Vortex* system the advantage over existing systems.

# HOW IT WORKS

The Victaulic Vortex hybrid fire extinguishing system uses inert gas and water to generate a nitrogen-enriched atmosphere that opposes combustion.




## SAFE ENVIRONMENT

In our environment the air already contains 78% percent nitrogen; the addition of nitrogen dilutes the air, allowing the tiny water particles to absorb the heat, creating an atmosphere that does not support combustion.

## EMITTER DISCHARGE

High velocity and low pressure creates a uniform blend of water and nitrogen; water is introduced to a jet stream of nitrogen at supersonic speed, then delivered with the nitrogen into the protected space.



## ENGINEERED DESIGN

The emitter shape is based on supersonic foil technology. The nitrogen velocity changes rapidly, producing shock waves that atomize the water injected through the emitter.

## Exclusive Features

### ROOM INTEGRITY

With the use of nitrogen and tiny water particles, systems are less reliant on room integrity

### WATER SPARSE PRESENCE

The system delivers as little as 0.26 gallons of water per emitter per minute. Each emitter can protect up to 2,500 ft<sup>3</sup> | 71 m<sup>3</sup>

### SUSTAINABLE DESIGN

Non-toxic agents that keep personnel safe during activation



### BACK ONLINE IN NO TIME

Rapid system recharge that reduces downtime

### EASY CLEANUP

### INDEPENDENT ZONE CONTROL

Multiple zones may share a common water and nitrogen source

### IMMEDIATE ACTIVATION

No delay in system activation

Controlled discharge rates and greater life safety reduce the need for pre-discharge alarms

### EASE OF INTEGRATION

Compatible with fire protection systems within the facility to provide greater design flexibility in retrofit and new construction

## Did You Know?

### ABSORB AND COOL

In larger fires, homogeneous mixtures are more effective, cooling the fire by absorbing the heat and reducing the available oxygen. The heat-absorbing water droplet surface area is 90x greater than that of any standard sprinkler system, providing maximum heat absorption efficiency.



# BUILT FOR PERFORMANCE

## Agency Testing and Evaluations



FM Approved solutions are available:  
Victaulic Vortex™ 1000 for protection of combustion turbines and machinery spaces spaces  
Victaulic Vortex 2000 for protection of wet bench applications and similar processing equipment.

The *Victaulic Vortex* system has been witnessed by Underwriter’s Laboratory and found to extinguish Class A polymeric and wood crib materials and Class B flammable liquid fires effectively.  
The *Victaulic Vortex* system has been witnessed by BRE Global and found to extinguish BS 8489-7 simulated workstation fires.


The EPA has provided a Significant New Alternatives Policy (SNAP) Approval for the *Victaulic Vortex* system, listing the system as a hybrid inert gas, water-based system and an acceptable replacement for clean agents affected by the AIM Act.

The *Victaulic Vortex* system has been tested by both Victaulic and independent laboratories and shown to be effective using fire test protocols contained in water mist and clean agent approval standards.

- By only using the natural materials of water and nitrogen, the *Victaulic Vortex* system:
- is not subject to specific government regulations such as certificates of approval due to Ozone Depletion Potential (ODP).
  - does not require special processes for the replacement of proprietary agents since the materials required for system recharging are readily available.


### RELATIVE AMOUNT OF WATER REQUIRED

GPM | LPM Flow Per Emitter, Nozzle or Sprinkler



### RELATIVE SURFACE AREA OF HEAT EXPOSURE

In² | Cm² Normalized Standard Sprinkler=1



## Environment Impact Comparison

VICTAULIC VORTEX™ HYBRID FIRE EXTINGUISHING SYSTEM	The <10 µm (microns) sized water droplets remove the heat in large fires and aid in the radiative and convective heat blocking. The nitrogen extinguishes small fires in large rooms in naturally ventilated environments.
Halocarbons	Rely on flame temperature reduction due to the thermal characteristics of the agent or disruption of the combustion process. No reduction in radiative or convective heat transfer and the fuel is generally not cooled leading to possible re-ignition. Halogenated Agents may be broken down into acids and other hazardous substances by exposure to high temperatures that may be present in a fire or at heated equipment.
Inert Gases	Rely primarily on oxygen reduction. Limited thermal cooling and no reduction of radiative or convective heat transfer. Fuel is not cooled and re-ignition from hot objects is possible.
High Pressure Water Mist	Water extracts heat from the fire. Steam generated from the fire aids in the radiative and convective heat blocking. Momentum is generally lost within a short distance of the nozzle. More efficient for large fire extinguishment.
Intermediate Pressure Water Mist and Standard Sprinkler Systems	Larger size water droplets are used to soak the fuel source. Steam generated from the fire aids in the radiative and convective heat blocking. Large droplet size and momentum generally make these less efficient for shielded fires.

## Water Characteristics Comparison

	FLOW, GPM PER EMITTER, NOZZLE OR SPRINKLER	DROP SIZE, µm	NOMINAL NOZZLE OPERATING PRESSURE, PSIG
VICTAULIC VORTEX HYBRID FIRE EXTINGUISHING SYSTEM	<=1	<10	25 – 50
CO <sub>2</sub>	Very High Flow	N/A	>600
Halocarbons	Very High Flow	N/A	360–500
Inert Gases	High Flow	N/A	>600
High Pressure Water Mist	2	50 – 100	>500
Intermediate Pressure Water Mist	9	300	175–500
Low Pressure Water Mist	6	<1000	<175
Standard Sprinkler Systems	15	>1000	<175

• Dependent upon system design

# SYSTEM OVERVIEW

	<b>Victaulic Vortex 500</b> Hybrid Fire Extinguishing System	<b>Victaulic Vortex 1000</b> Hybrid Fire Extinguishing System
System Type	Pre-Engineered	Engineered
Approvals	Performance based design EPA SNAP	FM 5580 machinery spaces and combustion turbines EPA SNAP
Typical Applications	Small data center, MCC rooms, and other Class A hazards	Internal combustion engines, generators, gearboxes, transformer vaults, and enclosures with incidental use/flammable liquid storage*
Maximum Coverage	At Sea Level 4,500ft³   127m³	127,525ft³   3,600m³
Maximum Ceiling Height	24.6ft   7.5m	24.6ft   7.5m
Emitter	5/8" Series 954	1/2" Series 953
Emitter Coverage	N/A	2,500ft³   71m³
Zoned System Option	No	Yes

\* Hydrocarbon ignitable liquids of less than two 55 gal (208 L) drums.

Combustion turbines can be protected by Victaulic Vortex™ 1000 or *Victaulic Vortex* 1500 systems.

**Victaulic Vortex™ 1500**  
Hybrid Fire Extinguishing System

Engineered

Performance based design  
EPA SNAP

Combustion turbines,  
machinery spaces, data centers,  
manufacturing equipment, etc.

No maximum

24.6ft | 7.5m  
Second row of emitters  
allowed for higher ceilings

¼", ⅜", ½", ⅝" Series 953 and 954  
in brass, stainless, and PVDF

1,700–2,100ft³ | 48–59m³  
at 500ft | 152m ASL

Yes

**Victaulic Vortex™ 2000**  
Hybrid Fire Extinguishing System

Engineered

FM 5560 wet benches  
and similar equipment  
EPA SNAP

Wet benches and  
similar processing equipment

No maximum

53" | 1.3m

¼" Series 953 PVDF

Approximately  
5ft² | 0.5m²

Yes





# TESTING AND RESEARCH ON HYBRID FIRE EXTINGUISHING SYSTEMS

## The New Standard for Hybrid Fire Extinguishing Systems: NFPA 770

Seven years in the making, NFPA 770 made its official debut in 2020 as the Standard for Hybrid Fire Extinguishing Systems (water and inert gas).

In addition to NFPA and FM standards, there is a substantial amount of research and testing available on Hybrid Fire Extinguishing Systems. Variables recently identified as requiring more research are the effects of altitude, enclosure integrity and fire size on extinguishing time and hybrid media requirements. In 2016, the NFPA Fire Protection Research Foundation established a Project Technical Panel (PTP) to provide oversight for Hybrid Fire Extinguishing System testing. Upon commissioning of this testing, limited data was available regarding fire extinguishing testing at high elevations.

In order to eliminate external variables in relation to room geometry and size, a mobile fire laboratory was constructed using a 40 ft | 12.2 m cargo container as the enclosure. (Figure 1). A Victaulic Vortex™ fire extinguishing system was installed in the container, and the laboratory included allowances for adjusting nozzle placement and the quantity of openings in the enclosure. Tests were conducted by Victaulic at locations with elevations of 500 ft | 152 m Above Sea Level (ASL), 6500 ft | 1981 m ASL and 10,000 ft | 3048 m ASL. Fire tests were conducted using similar test protocol as Underwriters Laboratories UL 2127, Inert Gas Clean Agent Extinguishing System Units, with fuels including heptane and polymers, polypropylene (PP), acrylonitril butadiene styrene (ABS) and polymethyl methacrylate (PMMA). Additional tests were performed at a lower elevation, including extinguishment of wood crib fires, variations to opening size and fire size, and the ability to prevent re-ignition.

Data collected from the mobile laboratory demonstrated that the required amount of hybrid media for extinguishment decreases with elevation. The new data provided a basis for using the Atmospheric Correction Factors (ACF) determined in NFPA 2001, Standard on Clean Agent Fire Extinguishing Systems to adjust the required amount of hybrid media based on the local atmospheric pressure.

Testing has also demonstrated that designing a total flooding Hybrid Fire Extinguishing System for a smaller 68kW heptane fire (Figure 2) resulted in a conservative design when larger fires are considered. In total flooding applications, as fire size increased (utilizing a larger fuel source), extinguishment occurred sooner, based on increased oxygen consumption from the fire and increased oxygen dilution from conversion of water to steam.

The project included tests to evaluate the extinguishment and protection times for Hybrid Fire Extinguishing Systems using different sized openings in the enclosure. Testing of the Victaulic Vortex Hybrid system, in an enclosure with varied opening sizes, demonstrated that a total flooding Hybrid Fire Extinguishing System will provide protection from re-ignition after the fire has been extinguished and the discharge has stopped.

To test protection time of a hybrid system, re-ignition of the fuel was attempted after extinguishment. The ignition source was a spark provided by an oil burner ignition transformer that was used for ignition and re-ignition of the fuel. For the Victaulic Vortex System used for this test series, the maximum recommended opening size of 1.25 ft² | 0.12 m² per nozzle provided 10 minutes of protection time. Smaller opening sizes were capable of providing substantially longer protection times, in some cases exceeding 1 hour of protection.

Outside of this work with the NFPA Fire Protection Research Foundation, research has been conducted on combustion turbines used for power generation. FM 5580, Approval Standard for Hybrid Fire Extinguishing Systems, allows for the approval of Hybrid Fire Protection Systems for the protection of combustion turbines. Combustion turbines operate at very close internal clearances and there is concern that discharging water onto the case can cause rapid cooling and failure. Victaulic, manufacturer of the Victaulic Vortex Hybrid Fire Extinguishing System, has worked with owners and operators of Frame 7 combustion turbine and FT4 Aero-derivative turbines to conduct discharge testing on operating units deployed at power generation facilities. Testing included bringing the unit up to temperature by connecting to the grid and generating electricity, followed by a shutdown and discharge of the Victaulic Vortex Hybrid Fire Extinguishing System. Testing demonstrated that the minimal water discharge of a Hybrid Fire Extinguishing system allowed these systems to be discharged on combustion turbines without damage.



Figure 1



Figure 2



### U.S./World Headquarters

4901 Kesslersville Road  
Easton, PA 18040 USA

▶ [victauliclocations.com](https://victauliclocations.com)

### EMEA

Prijkelstraat 36  
9810 Nazareth, Belgium

### Asia Pacific

Unit 808, Building B  
Hongwell International Plaza  
No.1602 West Zhongshan Road  
Shanghai, China 200235



PB-389 5309 REV I 02/2023

Victaulic and all other Victaulic marks are the trademarks or registered trademarks of Victaulic Company, and/or its affiliated entities, in the U.S. and/or other countries. All other trademarks listed herein are the property of their respective holders, in the U.S. and/or other countries. The terms "Patented" or "Patent Pending" refer to design or utility patents or patent applications for articles and/or methods of use in the United States and/or other countries.

© 2023 VICTAULIC COMPANY. ALL RIGHTS RESERVED.

